

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, Current and voltage are determined by the plug used., nom. voltage: 800 V, nominal current: 23 A, 1st level connection right, connection method: Screw connection, Rated cross section: 2.5 mm², cross section: 0.2 mm² - 4 mm², mounting: NS 35/7,5, NS 35/15, color: gray

Commercial data

Item number	3070435
Packing unit	50 pc
Minimum order quantity	1 pc
Product key	BE511X
Catalog page	Page 536 (C-1-2019)
GTIN	4046356569705
Weight per piece (including packing)	9.662 g
Weight per piece (excluding packing)	9.58 g
Customs tariff number	85369010
Country of origin	PL

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Technical data

Notes

General	Current and voltage are determined by the plug used.
General	
Note	The max. load current must not be exceeded by the total current of all connected conductors.
	The rated insulation voltage when using the module connector is 500 V.
	When using slip-on sleeves, their max. load current in accordance with DIN EN 61210 (Table 7) must be observed.

Product properties

Product type	Feed-through terminal block
Product family	VBSTB
Number of connections	4
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	4
Nominal cross section	4 mm ²

1st level connection right

Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	8 mm
Internal cylindrical gage	A4
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 12 (converted acc. to IEC)
Conductor cross section flexible	0.2 mm ² ... 4 mm ²
Conductor cross section, flexible [AWG]	24 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 4 mm ²
Flexible conductor cross section (ferrule with plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Cross-section with insertion bridge, rigid	2.5 mm ²
Cross-section with insertion bridge, flexible	2.5 mm ²
2 conductors with same cross section, solid	0.2 mm ² ... 1.5 mm ²

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

2 conductors with same cross section, flexible	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
Nominal current	23 A
Maximum load current	30 A (with 4 mm ² conductor cross section)
Nominal voltage	800 V
Nominal cross section	2.5 mm ²

Dimensions

Width	6.2 mm
End cover width	2.2 mm
Height	72 mm
Depth on NS 35/7,5	39.5 mm
Depth on NS 35/15	47 mm

Material specifications

Color	gray
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 4 mm ²	0.48 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2 kV
-----------------------	------

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Result	Test passed
--------	-------------

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 35
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross section/weight	0.2 mm ² / 0.2 kg
	2.5 mm ² / 0.7 kg
	4 mm ² / 0.9 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2022-06
Spectrum	Service life test category 1, class B, body mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	1.857 (m/s ²)/Hz
Acceleration	0.8g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2022-06
Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block




3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Drawings

Circuit diagram



VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block




3070435


<https://www.phoenixcontact.com/pc/products/3070435>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/3070435>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group B	300 V	20 A	30 - 10	-
Use group C	300 V	20 A	30 - 10	-
Use group D	600 V	5 A	30 - 10	-

 EAC Approval ID: RU C-DE.BL08.B.00541				
---	--	--	--	--

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group B	300 V	20 A	30 - 10	-
Use group C	300 V	20 A	30 - 10	-

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Classifications

ECLASS

ECLASS-11.0	27141120
ECLASS-13.0	27250101

ETIM

ETIM 9.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

Accessories


i Note: Applying some accessories below might limit this product.

EB 2- 6 - Insertion bridge

0201155

<https://www.phoenixcontact.com/pc/products/0201155>

Insertion bridge, pitch: 6.2 mm, number of positions: 2, color: gray



i Max. current carrying capacity: 24 A

EB 3- 6 - Insertion bridge

0201142

<https://www.phoenixcontact.com/pc/products/0201142>

Insertion bridge, pitch: 6.2 mm, number of positions: 3, color: gray



i Max. current carrying capacity: 24 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


EB 10- 6 - Insertion bridge

0201139

<https://www.phoenixcontact.com/pc/products/0201139>



Insertion bridge, pitch: 6.2 mm, number of positions: 10, color: gray

 Max. current carrying capacity: 24 A


FBS 1/3-6 - Plug-in bridge

3032321

<https://www.phoenixcontact.com/pc/products/3032321>



Plug-in bridge, pitch: 6.2 mm, number of positions: 3, pin assignment: 1,3, color: red

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 2-6 - Plug-in bridge

3030336

<https://www.phoenixcontact.com/pc/products/3030336>



Plug-in bridge, pitch: 6.2 mm, number of positions: 2, color: red

 Max. current carrying capacity: 32 A


FBS 2-6 BU - Plug-in bridge

3036932

<https://www.phoenixcontact.com/pc/products/3036932>



Plug-in bridge, pitch: 6.2 mm, number of positions: 2, color: blue

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 2-6 GY - Plug-in bridge

3032237

<https://www.phoenixcontact.com/pc/products/3032237>



Plug-in bridge, pitch: 6.2 mm, number of positions: 2, color: gray

 Max. current carrying capacity: 32 A


FBS 3-6 - Plug-in bridge

3030242

<https://www.phoenixcontact.com/pc/products/3030242>



Plug-in bridge, pitch: 6.2 mm, number of positions: 3, color: red

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 3-6 BU - Plug-in bridge

3036945

<https://www.phoenixcontact.com/pc/products/3036945>



Plug-in bridge, pitch: 6.2 mm, number of positions: 3, color: blue

 Max. current carrying capacity: 32 A


FBS 3-6 GY - Plug-in bridge

3032240

<https://www.phoenixcontact.com/pc/products/3032240>



Plug-in bridge, pitch: 6.2 mm, number of positions: 3, color: gray

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 4-6 - Plug-in bridge

3030255

<https://www.phoenixcontact.com/pc/products/3030255>



Plug-in bridge, pitch: 6.2 mm, number of positions: 4, color: red

 Max. current carrying capacity: 32 A


FBS 4-6 BU - Plug-in bridge

3036958

<https://www.phoenixcontact.com/pc/products/3036958>



Plug-in bridge, pitch: 6.2 mm, number of positions: 4, color: blue

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 4-6 GY - Plug-in bridge

3032279

<https://www.phoenixcontact.com/pc/products/3032279>



Plug-in bridge, pitch: 6.2 mm, number of positions: 4, color: gray

 Max. current carrying capacity: 32 A


FBS 5-6 - Plug-in bridge

3030349

<https://www.phoenixcontact.com/pc/products/3030349>



Plug-in bridge, pitch: 6.2 mm, number of positions: 5, color: red

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

FBS 5-6 BU - Plug-in bridge

3036961

<https://www.phoenixcontact.com/pc/products/3036961>



Plug-in bridge, pitch: 6.2 mm, number of positions: 5, color: blue

 Max. current carrying capacity: 32 A


FBS 5-6 GY - Plug-in bridge

3032266

<https://www.phoenixcontact.com/pc/products/3032266>



Plug-in bridge, pitch: 6.2 mm, number of positions: 5, color: gray

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 6-6 - Plug-in bridge

1008238

<https://www.phoenixcontact.com/pc/products/1008238>



Plug-in bridge, One side not fully isolated, pitch: 6.2 mm, number of positions: 6, color: red

 Max. current carrying capacity: 32 A


FBS 1/4-6 - Plug-in bridge

3032512

<https://www.phoenixcontact.com/pc/products/3032512>



Bridge for potential distribution

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 1/5-6 - Plug-in bridge

3032525

<https://www.phoenixcontact.com/pc/products/3032525>



Bridge for potential distribution

 Max. current carrying capacity: 32 A


FBS 1/6-6 - Plug-in bridge

3032538

<https://www.phoenixcontact.com/pc/products/3032538>



Bridge for potential distribution

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 10-6 - Plug-in bridge

3030271

<https://www.phoenixcontact.com/pc/products/3030271>

Plug-in bridge, pitch: 6.2 mm, number of positions: 10, color: red



 Max. current carrying capacity: 32 A


FBS 10-6 BU - Plug-in bridge

3032198

<https://www.phoenixcontact.com/pc/products/3032198>

Plug-in bridge, pitch: 6.2 mm, number of positions: 10, color: blue



 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 10-6 GY - Plug-in bridge

3032253

<https://www.phoenixcontact.com/pc/products/3032253>



Plug-in bridge, pitch: 6.2 mm, number of positions: 10, color: gray

 Max. current carrying capacity: 32 A


FBS 20-6 - Plug-in bridge

3030365

<https://www.phoenixcontact.com/pc/products/3030365>



Plug-in bridge, pitch: 6.2 mm, number of positions: 20, color: red

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block




3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 20-6 BU - Plug-in bridge

3032208

<https://www.phoenixcontact.com/pc/products/3032208>



Plug-in bridge, pitch: 6.2 mm, number of positions: 20, color: blue

 Max. current carrying capacity: 32 A


FBS 50-6 - Plug-in bridge

3032224

<https://www.phoenixcontact.com/pc/products/3032224>



Plug-in bridge, pitch: 6.2 mm, number of positions: 50, color: red

 Max. current carrying capacity: 32 A

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>


FBS 50-6 BU - Plug-in bridge

3032211

<https://www.phoenixcontact.com/pc/products/3032211>



Plug-in bridge, pitch: 6.2 mm, number of positions: 50, color: blue

 Max. current carrying capacity: 32 A

D-TP-VBS - End cover

0851026

<https://www.phoenixcontact.com/pc/products/0851026>

End cover, depth: 40 mm, width: 2.2 mm, height: 80 mm, color: gray



VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

SBS 6:UNBEDRUCKT - Marker card

1007222

<https://www.phoenixcontact.com/pc/products/1007222>



Marker card, Card, white, unlabeled, can be labeled with: Marker pen, mounting type: snapped, snap into flat marker groove, for terminal block width: 6 mm, lettering field size: 6 x 6.1 mm, Number of individual labels: 250

NS 35/ 7,5 PERF 2000MM - DIN rail perforated

0801733

<https://www.phoenixcontact.com/pc/products/0801733>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/ 7,5 UNPERF 2000MM - DIN rail, unperforated

0801681

<https://www.phoenixcontact.com/pc/products/0801681>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

NS 35/ 7,5 WH PERF 2000MM - DIN rail perforated

1204119

<https://www.phoenixcontact.com/pc/products/1204119>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/ 7,5 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204122

<https://www.phoenixcontact.com/pc/products/1204122>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

NS 35/ 7,5 AL UNPERF 2000MM - DIN rail, unperforated

0801704

<https://www.phoenixcontact.com/pc/products/0801704>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/ 7,5 ZN PERF 2000MM - DIN rail perforated

1206421

<https://www.phoenixcontact.com/pc/products/1206421>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

NS 35/ 7,5 ZN UNPERF 2000MM - DIN rail, unperforated

1206434

<https://www.phoenixcontact.com/pc/products/1206434>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

0801762

<https://www.phoenixcontact.com/pc/products/0801762>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

NS 35/ 7,5 CAP - End cap

1206560

<https://www.phoenixcontact.com/pc/products/1206560>

DIN rail end piece, for DIN rail NS 35/7.5



VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/15 PERF 2000MM - DIN rail perforated

1201730

<https://www.phoenixcontact.com/pc/products/1201730>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

NS 35/15 UNPERF 2000MM - DIN rail, unperforated

1201714

<https://www.phoenixcontact.com/pc/products/1201714>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/15 WH PERF 2000MM - DIN rail perforated

0806602

<https://www.phoenixcontact.com/pc/products/0806602>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: white

NS 35/15 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204135

<https://www.phoenixcontact.com/pc/products/1204135>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/15 AL UNPERF 2000MM - DIN rail, unperforated

1201756

<https://www.phoenixcontact.com/pc/products/1201756>



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

NS 35/15 ZN PERF 2000MM - DIN rail perforated

1206599

<https://www.phoenixcontact.com/pc/products/1206599>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated

1206586

<https://www.phoenixcontact.com/pc/products/1206586>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

NS 35/15 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201895

<https://www.phoenixcontact.com/pc/products/1201895>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

NS 35/15 CAP - End cap

1206573

<https://www.phoenixcontact.com/pc/products/1206573>

DIN rail end piece, for DIN rail NS 35/15



NS 35/15-2,3 UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201798

<https://www.phoenixcontact.com/pc/products/1201798>

DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile 2.3 mm, color: silver



VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

ZB 6:UNBEDRUCKT - Zack marker strip

1051003

<https://www.phoenixcontact.com/pc/products/1051003>



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

ZB 6 CUS - Zack marker strip

0824992

<https://www.phoenixcontact.com/pc/products/0824992>



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

ZB 6,LGS:FORTL.ZAHLEN - Zack marker strip

1051016

<https://www.phoenixcontact.com/pc/products/1051016>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 491 ... 500, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6. 15 x 10.5 mm, Number of individual labels: 10

ZB 6,QR:FORTL.ZAHLEN - Zack marker strip

1051029

<https://www.phoenixcontact.com/pc/products/1051029>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 491 ... 500, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6. 15 x 10.5 mm, Number of individual labels: 10

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

ZB 6,LGS:GLEICHE ZAHLEN - Zack marker strip

1051032

<https://www.phoenixcontact.com/pc/products/1051032>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: Identical numbers 1 or 2, etc. up to 100, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

ZB 6,LGS:L1-N,PE - Marker for terminal blocks

1051414

<https://www.phoenixcontact.com/pc/products/1051414>



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

ZB 6,LGS:U-N - Marker for terminal blocks

1051430

<https://www.phoenixcontact.com/pc/products/1051430>



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: U, V, W, N, GND, U, V, W, N, GND, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

UC-TM 6 - Marker for terminal blocks

0818085

<https://www.phoenixcontact.com/pc/products/0818085>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 80

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

UC-TM 6 CUS - Marker for terminal blocks

0824589

<https://www.phoenixcontact.com/pc/products/0824589>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 80

UCT-TM 6 - Marker for terminal blocks

0828736

<https://www.phoenixcontact.com/pc/products/0828736>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 60

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

UCT-TM 6 CUS - Marker for terminal blocks

0829602

<https://www.phoenixcontact.com/pc/products/0829602>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 60

C-SCF 1/2,8X0,5 - Connector

3240152

<https://www.phoenixcontact.com/pc/products/3240152>



Slip-on sleeve, non-insulated, 0.5 ... 1 mm², 2.8 x 0.5

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

C-SCFI 1,5/2,8X0,5 - Connector

3240048

<https://www.phoenixcontact.com/pc/products/3240048>



Slip-on sleeve, red, 0.5 ... 1.5 mm², 2.8 x 0.5

C-SCF 1/2,8X0,8 - Connector

3240153

<https://www.phoenixcontact.com/pc/products/3240153>



Slip-on sleeve, non-insulated, 0.5 ... 1 mm², 2.8 x 0.8

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

C-SCFI 1,5/2,8X0,8 - Connector

3240049

<https://www.phoenixcontact.com/pc/products/3240049>



Slip-on sleeve, red, 0.5 ... 1.5 mm², 2.8 x 0.8

C-SCF 1,5/6,3X0,8 - Connector

3240156

<https://www.phoenixcontact.com/pc/products/3240156>



Slip-on sleeve, non-insulated, 0.5 ... 1.5 mm², 6.3 x 0.8

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

C-SCFI 1,5/6,3X0,8 - Connector

3240052

<https://www.phoenixcontact.com/pc/products/3240052>



Slip-on sleeve, red, 0.5 ... 1.5 mm², 6.3 x 0.8

C-SCF 2,5/6,3X0,8 - Connector

3240159

<https://www.phoenixcontact.com/pc/products/3240159>



Slip-on sleeve, non-insulated, 1.5 ... 2.5 mm², 6.3 x 0.8

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

C-SCFI 2,5/6,3X0,8 - Connector

3240055

<https://www.phoenixcontact.com/pc/products/3240055>



Slip-on sleeve, blue, 1.5 ... 2.5 mm², 6.3 x 0.8

C-SCF 6/6,3X0,8 - Connector

3240160

<https://www.phoenixcontact.com/pc/products/3240160>



Slip-on sleeve, non-insulated, 4 ... 6 mm², 6.3 x 0.8

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

C-SCFI 6/6,3X0,8 - Connector

3240056

<https://www.phoenixcontact.com/pc/products/3240056>



Slip-on sleeve, yellow, 4 ... 6 mm², 6.3 x 0.8

PT/FS 2,8 - Insulating sleeve

1406700

<https://www.phoenixcontact.com/pc/products/1406700>



Insulating sleeve, as touch protection, slide onto the conductor before for 2.8 slip-on sleeves

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

PT/FS 6,3 - Insulating sleeve

0604707

<https://www.phoenixcontact.com/pc/products/0604707>



Insulating sleeve, as touch protection, slide onto the conductor before for 6.3 slip-on sleeves

PAI-4-FIX-5/6 BU - Test adapter

3035975

<https://www.phoenixcontact.com/pc/products/3035975>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

PAI-4-FIX-5/6 OG - Test adapter

3035974

<https://www.phoenixcontact.com/pc/products/3035974>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

PAI-4-FIX-5/6 YE - Test adapter

3035977

<https://www.phoenixcontact.com/pc/products/3035977>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

PAI-4-FIX-5/6 RD - Test adapter

3035976

<https://www.phoenixcontact.com/pc/products/3035976>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

PAI-4-FIX-5/6 GN - Test adapter

3035978

<https://www.phoenixcontact.com/pc/products/3035978>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

PAI-4-FIX-5/6 BK - Test adapter

3035980

<https://www.phoenixcontact.com/pc/products/3035980>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

PAI-4-FIX-5/6 GY - Test adapter

3035982

<https://www.phoenixcontact.com/pc/products/3035982>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

PAI-4-FIX-5/6 VT - Test adapter

3035979

<https://www.phoenixcontact.com/pc/products/3035979>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

PAI-4-FIX-5/6 BN - Test adapter

3035981

<https://www.phoenixcontact.com/pc/products/3035981>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

PAI-4-FIX-5/6 WH - Test adapter

3035983

<https://www.phoenixcontact.com/pc/products/3035983>



4 mm test adapter, for terminal blocks with 5.2 mm and 6.2 mm pitch

PAI-4-N GY - Test adapter

3032871

<https://www.phoenixcontact.com/pc/products/3032871>



4 mm test adapter, for terminal blocks with 5.2 mm, 6.2 mm and 8.2 mm pitch

VBSTB 4-FS (6-2,8-0,8) - Feed-through terminal block



3070435

<https://www.phoenixcontact.com/pc/products/3070435>

SZS 0,6X3,5 - Screwdriver

1205053

<https://www.phoenixcontact.com/pc/products/1205053>



Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com