

354 SERIES PANEL INDICATOR LED



FEATURES

- Ø4.1mm mounting
- Snap-in
- Plastic housing
- Range of LED colour options
- Choice of solder pins or wires

BENEFITS

- · Standard industrial mounting size
- Ease of installation
- · Lightweight solution
- Suitable for status panel indication
- · Flexibility for different applications
- · Outstanding reliability

Marl Part Number	LED Colour	Termination	Typical Voltage DC Vf	Max. Reverse Voltage	Max. Current DC If	Max. Power Dissipation	Typical LED Luminous Intensity @20mA	Typical LED Wavelength λp		Operating Temp Topr *	Storage Temp Tstg
354-305-04	Red Diffused	LED Leads	2.1	5	20	45	2	700	40	-25 to +85	-30 to +100
354-311-04	Yellow Diffused	LED Leads	2	5	30	85	20	590	40	-25 to +85	-30 to +100
354-314-04	Green Diffused	LED Leads	2.1	5	30	80	25	568	40	-25 to +85	-30 to +100
354-320-04	Blue Diffused	LED Leads	4	5	25	150	10	430	40	-25 to +85	-30 to +100
354-305-04-40	Red Diffused	Flying Leads	2.1	5	20	45	2	700	40	-25 to +85	-30 to +100
354-311-04-40	Yellow Diffused	Flying Leads	2	5	30	85	20	590	40	-25 to +85	-30 to +100
354-314-04-40	Green Diffused	Flying Leads	2.1	5	30	80	25	568	40	-25 to +85	-30 to +100
354-320-04-40	Blue Diffused	Flying Leads	4	5	25	150	10	430	40	-25 to +85	-30 to +100
			Vdc	Vdc	mA	mW	mcd	nm	Deg	°C	°C

OPTIONAL FLYING LEAD TERMINATORS

Marl Part No Suffix	Wire Length	Wire Colour	No/Diameter of Conductors	Diameter of Insulation	Wire Specification
354-305-04 -40	305mm	Red - Anode Black - Cathode	11/0.16mm	1.15mm	24AWG

NOTES

All LED components are supplied in anti-static packaging.

* LED Characteristics stated at Ta = 25°C. For operating temperature derating graphs, please refer to sheet 2.

To order please contact us on +44 (0) 1229 582 430 F +44 (0) 1229 585 155 | E sales@marl.co.uk | www.leds.co.uk


y marlleds f marlinternationallimited in company/marl-international-limited





354 SERIES PANEL INDICATOR LED


TECHNICAL CHARACTERISTICS




TECHNICAL DRAWING


Dimensions in mm (typical). Not to scale. Mounting hole to be clean and burr free.


Standard Version





DE-RATING GRAPHS





MATERIALS

 Body
 Nylon 6/6

 Lens
 Epoxy (LED Lens)

 Termination (Standard version)
 LED Leads

 Termination (Flying Leads version)
 Wires, Stripped and Tinned

DESIGN CONSIDERATIONS

Electro-Static Discharge (ESD)

Build up of electro-static discharge occurs in many situations involving people moving and handling products. The range of possible situations is very diverse but voltage levels as high as several thousand volts can and do arise in many individual situations. When an operator charged up to these levels handles a static sensitive device, there is a very probable likelihood that the device will be irreversibly damaged. It is essential that precautions are taken at all stages during manufacture and assembly of these products. Although LEDs were never considered to be static sensitive devices, changes in manufacturing technology and materials used to produce higher intensity products over a large range of the wavelength spectrum have changed this. Marl has an approved system of ESD control from goods in, through production and into final packing and despatch. Marl recommend all users of LED based products follow the guidelines of BS 100015.

Voltage, Current and Temperature

The forward voltage / current value of an LED is dependent upon the ambient temperature of the environment in which it is operated. Therefore, care must be taken to operate the LED at the correct voltage / current values, depending upon the ambient temperature.

Marl should be contacted if the device is to be operated outside the temperature range specified. Marl accept no liability for any product that is operated outside the stated voltage or temperature range.



To order please contact us on +44 (0) 1229 582 430 F +44 (0) 1229 585 155 | E sales@marl.co.uk | www.leds.co.uk

y marlleds f marlinternationallimited in company/marl-international-limited

354 Version DS002/2016. Page 2 of 2