# **SIEMENS**

## Data sheet

## 3LD3250-0TK13

Load disconnector 3LD3, lu 32 A Main switch 3-pole Rated operating capacity for AC-23 A at 400V 11.5kW Front plate mounting Basic switch with Central hole mounting 22.5mm Toggle drive red / yellow 48x48 mm



SENTRON
3LD Switch disconnector
EMERGENCY-STOP switch
1 ON - 0 OFF
selector switch
knob-operated mechanism, red/yellow
No
3
3
fixed mounting
front mounted
50 1/h
690 V
6 kV

Model

Protection class	
Protection class IP	IP65
Protection class IP / on the front	IP65
Dissipation	
Power loss [W] / for rated value of the current / at AC	1.8 W
/ in hot operating state / per pole	
Electricity	
Current / at AC / rated value	32 A
Continuous current / rated value	32 A
Continuous current / of upstream fuse / rated value	32 A
Short-time current resistance (Icw) / at 690 V / limited	500 A
to 1 s / rated value	
Main circuit	
Operating frequency	
• initial value	50 Hz
• Full-scale value	60 Hz
Operating power	
• at AC-23 A / at 400 V / rated value	11.5 kW
• at AC-23 A / at 690 V / rated value	11.5 kW
• at AC-3 / at 400 V / rated value	9.5 kW
• at AC-3 / at 690 V / rated value	9.5 kW
Operating voltage	
• at AC / at 50/60 Hz / rated value	690 V
Auxiliary circuit	0
Number of CO contacts / for auxiliary contacts	0
Number of NC contacts / for auxiliary contacts	0
Number of NO contacts / for auxiliary contacts	0
Operating voltage / of auxiliary contacts / at AC / maximum	500 V
Continuous current / of the auxiliary contact / rated	10 A
value	
Insulation voltage / of the auxiliary switch / rated	500 V
value	
Suitability	
Suitability for use	
Main switch	Yes
switch disconnector	Yes
EMERGENCY OFF switch	Yes
safety switch	Yes
-	Yes
maintenance/repair switch	1 65
Product details	

Product feature / interlock	Yes
Number of bracket locks / maximum	2
Hasp thickness / of bracket locks / minimum	4 mm
Hasp thickness / of bracket locks / maximum	6 mm
Product extension / optional	
motor drive	No
Voltage trigger	No
Short circuit	
Conditional short-circuit current / with line-side fuse	
protection	
● at 690 V / by gG fuse / rated value	6 kA
Number of NC contacts	0
Number of NO contacts	0
Connections	
Type of connectable conductor cross-sections	
<ul> <li>for copper conductor / solid</li> </ul>	1x (2.5 to 16 mm <sup>2</sup> )
<ul> <li>for copper conductor / stranded</li> </ul>	1x (2.5 to 16 mm <sup>2</sup> )
<ul> <li>for auxiliary contacts / solid</li> </ul>	2x (0.75 2.5 mm²), 1x 4 mm²
<ul> <li>for auxiliary contacts / finely stranded / with</li> </ul>	2x (0.75 1.5 mm²), 1x 2.5 mm²
core end processing	0 (0.75 0.5 mm2) 4 ( mm2)
for auxiliary contacts / stranded	2x (0.75 2.5 mm2), 1x 4 mm2
Type of electrical connection	
<ul> <li>for main current circuit</li> </ul>	box terminal
<ul> <li>for auxiliary contacts</li> </ul>	Box terminals
Requirements	
Design of the fuse link	
<ul> <li>for short-circuit protection of the main circuit / required</li> </ul>	fuse gL/gG: 40 A
• for short-circuit protection of the auxiliary switch	fuse gL/gG: 10 A
/ required	
Mechanical Design	60 mm
Height Width	60 mm 36 mm
Depth	30 mm 114 mm
•	
Mounting type	Built-in unit fixed-mounted version
<ul> <li>Mounting type</li> <li>front mounting with 4-hole attachment</li> </ul>	No
	Yes
<ul> <li>front mounting with central attachment</li> </ul>	No
• roll mounting	
• rail mounting Net weight	200 g

Ambient temperature	
<ul> <li>during operation / minimum</li> </ul>	-25 °C
<ul> <li>during operation / maximum</li> </ul>	55 °C
Certificates	
Reference code	
• acc. to DIN EN 61346-2	S
• acc. to DIN EN 81346-2	SF
Declaration of Conformity	



#### Further information

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3250-0TK13

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3LD3250-0TK13

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax\_en.aspx?mlfb=3LD3250-0TK13

CAx-Online-Generator http://www.siemens.com/cax

### **Tender specifications**

http://www.siemens.com/specifications







