

347874-1 ✓ ACTIVE

AMP | Econoseal


TE Internal #: 347874-1

Automotive Seals & Cavity Plugs, Cable Seal, Cavity Diameter .043 in [1.1 mm], Silicone Rubber, Poor, 40, Contains Lubricant, Green, Econoseal

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Seals & Cavity Plugs



Connector Seal Type: **Cable Seal**

Cavity Diameter: **1.1 mm [.043 in]**

Accepts Insulation Diameter Range: **1.6 – 2.4 mm [.062 – .094 in]**

Seal Material: **Silicone Rubber**

Resistance to Hydrocarbons: **Poor**

Features

Product Type Features

Connector Seal Type	Cable Seal
---------------------	------------

Body Features

Seal Material	Silicone Rubber
---------------	-----------------

Primary Product Color	Green
-----------------------	-------

Dimensions

Cavity Diameter	1.1 mm[.043 in]
-----------------	-----------------

Accepts Insulation Diameter Range	1.6 – 2.4 mm[.062 – .094 in]
-----------------------------------	------------------------------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
-----------------------------	----------------

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	10000
--------------------	-------

Packaging Method	Bag
------------------	-----

Other

Resistance to Hydrocarbons	Poor
----------------------------	------

Shore A Hardness	40
------------------	----

Contains Lubricant	Yes
--------------------	-----



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | **Econoseal**



Automotive Connector Caps & Covers (1)



Automotive Connector Locks & Position Assurance(25)



Automotive Housings(66)



Automotive Seals & Cavity Plugs(18)




Automotive Terminals(47)



Insertion & Extraction Tools(7)



Other Automotive Connector Accessories(5)




PCB Headers & Receptacles(4)



Primary Wire(1)

Customers Also Bought




TE Part #344111-1
36W EMS.REC. HSG.ASSY




TE Part #347887-3
2 WAY JUNIOR TIMER CONN.



TE Part #344113-1
Econoseal Receptacles and Tabs




TE Part #284853-1
12 POS FEMALE CONNECTOR ASS'Y



TE Part #1-150504-2
BUTTON CONTACT 20-16 .0158 X .625 TPBR



TE Part #284321-1
12 POS.MQS SHELL FOR STEERING



TE Part #345253-1
ANTI-BACKOUT 2WAY TAB HSGECONO



TE Part #344276-1
2 WAY REC HSG. SIL SEAL ECONO



Documents

Product Drawings

[CABLE SEAL LC SILICON 0.5 T](#)

English

CAD Files

Customer View Model

[ENG_CVM_347874-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_347874-1_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_347874-1_C.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.