SIEMENS

Data sheet 3RM1307-1AA04



Fail-safe reversing starter, 3RM1, 500 V, 0.55 - 3 kW, 1.6 - 7 A, 24 V DC, screw terminals

product brand name	SIRIUS
product category	Motor starter
product designation	Failsafe reversing starters
design of the product	With electronic overload protection and safety-related disconnection
product type designation	3RM1
General technical data	
trip class	CLASS 10A
equipment variant according to IEC 60947-4-2	3
product function	fail-safe reversing starter
 intrinsic device protection 	Yes
 for power supply reverse polarity protection 	Yes
suitability for operation device connector 3ZY12	Yes
insulation voltage rated value	500 V
overvoltage category	III
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
 between main and auxiliary circuit 	500 V
 between control and auxiliary circuit 	250 V
shock resistance	6g / 11 ms
vibration resistance	1 6 Hz, 15 mm; 20 m/s², 500 Hz
operating frequency maximum	1 1/s
mechanical service life (switching cycles) typical	15 000 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	03/01/2017
product function	
direct start	No
reverse starting	Yes
product function short circuit protection	No
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	Class A
conducted interference	
 due to burst according to IEC 61000-4-4 	3 kV / 5 kHz
 due to conductor-earth surge according to IEC 61000-4-5 	4 kV signal lines 2 kV
 due to conductor-conductor surge according to IEC 61000-4-5 	2 kV
 due to high-frequency radiation according to IEC 61000-4-6 	10 V
field-based interference according to IEC 61000-4-3	10 V/m

electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
conducted HF interference emissions according to	Class B for the domestic, business and commercial environments
CISPR11	,
field-bound HF interference emission according to CISPR11	Class B for the domestic, business and commercial environments
Safety related data	<u>,</u>
safety device type according to IEC 61508-2	Type B
Safety Integrity Level (SIL) according to IEC 61508	_ 3
SIL Claim Limit (subsystem) according to EN 62061	SILCL 3
performance level (PL) according to EN ISO 13849-1	е
category according to EN ISO 13849-1	4
stop category according to EN 60204-1	0
Safe failure fraction (SFF)	99.4 %
average diagnostic coverage level (DCavg)	99 %
diagnostics test interval by internal test function maximum	600 s
function test interval maximum	
failure rate [FIT]	_ · ,
 at rate of recognizable hazardous failures (λdd) 	1 400 FIT
 at rate of recognizable hazardous failures (λdu) 	16 FIT
PFHD with high demand rate according to EN 62061	0.00000002 1/h
PFDavg with low demand rate according to IEC 61508	0.000018
MTTFd	75 y
hardware fault tolerance according to IEC 61508	1
T1 value for proof test interval or service life according to IEC 61508	20 y
safe state	Load circuit open
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe
OFF-delay time with safety-related request	
 when switched off via control inputs maximum 	43 ms
when switched off via supply voltage maximum	120 ms
hardware fault tolerance according to IEC 61508 relating to ATEX	0
PFDavg with low demand rate according to IEC 61508 relating to ATEX	0.0005
PFHD with high demand rate according to EN 62061 relating to ATEX Seferty Integrity Level (SII) according to IEC 61509	0.00000005 1/h - SIL2
Safety Integrity Level (SIL) according to IEC 61508 relating to ATEX T1 value for proof test interval or service life	
according to IEC 61508 relating to ATEX	3 y
Main circuit	
number of poles for main current circuit	3
design of the switching contact	Hybrid
adjustable current response value current of the current-dependent overload release	1.6 7 A
minimum load [%]	20 %; from set rated current
type of the motor protection	solid-state
operating voltage rated value	48 500 V
relative symmetrical tolerance of the operating voltage	10 %
operating frequency 1 rated value	50 Hz
operating frequency 2 rated value	60 Hz
relative symmetrical tolerance of the operating frequency	10 %
operational current	
at AC at 400 V rated value	7 A
• at AC-3 at 400 V rated value	7 A
at AC-53a at 400 V at ambient temperature 40 °C rated value	7 A
ampacity when starting maximum	56 A

operating power for 2 phase maters at 400 V at 50 V at	
operating power for 3-phase motors at 400 V at 50 Hz derating temperature	0.55 3 KW 40 °C
Inputs/ Outputs	TO 0
input voltage at digital input	
at DC rated value	24 V
with signal <0> at DC	0 5 V
• for signal <1> at DC	15 30
input current at digital input	16 66
• for signal <1> at DC	8 mA
• with signal <0> at DC	1 mA
number of CO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15 at	3 A
230 V maximum	4.0
operational current of auxiliary contacts at DC-13 at 24 V maximum	1 A
Control circuit/ Control	,
type of voltage of the control supply voltage	DC
control supply voltage at DC rated value	19.2 30 V
relative negative tolerance of the control supply voltage at DC	20 %
relative positive tolerance of the control supply voltage at DC	25 %
control supply voltage 1 at DC rated value	24 V
operating range factor control supply voltage rated value at DC	
• initial value	0.8
full-scale value	1.25
control current at DC	
 in standby mode of operation 	13 mA
when switching on	150 mA
during operation	57 mA
duration of inrush current peak at 24 V	85 ms
power loss [W] in auxiliary and control circuit	
in switching state OFF	
— with bypass circuit	0.35 W
• in switching state ON	4.0=344
— with bypass circuit	1.37 W
Response times	
ON-delay time	65 76 ms
OFF-delay time	30 43 ms
Power Electronics	
operational current	7.0
 at 40 °C rated value at 50 °C rated value 	7 A 6.1 A
at 50 °C rated value at 55 °C rated value	5.2 A
at 60 °C rated value	4.6 A
Installation/ mounting/ dimensions	
mounting position	vertical, horizontal, standing (observe derating)
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail
height	100 mm
width	22.5 mm
depth	141.6 mm
required spacing	
with side-by-side mounting	
— forwards	0 mm
— backwards	0 mm
— upwards	50 mm
— downwards	50 mm
— at the side	0 mm
for grounded parts	
— forwards	0 mm

— backwards	0 mm
— upwards	50 mm
— at the side	3.5 mm
— downwards	50 mm
Ambient conditions	
installation altitude at height above sea level maximum	4 000 m; For derating see manual
ambient temperature	3 3
during operation	-25 +60 °C
during storage	-40 +70 °C
during transport	-40 +70 °C
environmental category during operation according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
relative humidity during operation	10 95 %
air pressure according to SN 31205	900 1 060 hPa
Communication/ Protocol	
protocol is supported	
 PROFINET IO protocol 	No
PROFIsafe protocol	No
product function bus communication	No
protocol is supported AS-Interface protocol	No
Connections/ Terminals	
type of electrical connection	screw-type terminals for main circuit, screw-type terminals for control
for majo compant aircuit	circuit
for main current circuit for cuvilians and control circuit	screw-type terminals
for auxiliary and control circuit wire length for motor unshielded maximum	screw-type terminals 100 m
type of connectable conductor cross-sections	100 111
• for main contacts	
— solid	1x (0,5 4 mm²), 2x (0,5 2,5 mm²)
finely stranded with core end processing	1x (0,5 4 mm²), 2x (0,5 1,5 mm²)
at AWG cables for main contacts	1x (20 12), 2x (20 14)
connectable conductor cross-section for main	17 (20 12), 27 (20 14)
contacts	
 solid or stranded 	0.5 4 mm²
finely stranded with core end processing	0.5 4 mm²
connectable conductor cross-section for auxiliary contacts	
 solid or stranded 	0.5 2.5 mm ²
finely stranded with core end processing	0.5 2.5 mm ²
type of connectable conductor cross-sections	
 for auxiliary contacts 	
— solid	1x (0,5 2,5 mm²), 2x (1,0 1,5 mm²)
— finely stranded with core end processing	1x (0.5 2.5 mm²), 2x (0.5 1 mm²)
at AWG cables for auxiliary contacts	1x (20 14), 2x (18 16)
AWG number as coded connectable conductor cross section	
• for main contacts	20 12
for auxiliary contacts	20 14
UL/CSA ratings	
yielded mechanical performance [hp]	
for single-phase AC motor	
— at 110/120 V rated value	0.25 hp
— at 230 V rated value	0.5 hp
• for 3-phase AC motor	
— at 200/208 V rated value	1 hp
— at 220/230 V rated value	1.5 hp
— at 460/480 V rated value	3 hp
operating voltage at AC	
according to UL rated value	480 V
according to CSA rated value	400 V
Certificates/ approvals	



Confirmation









For use in hazardous locations

Functional Safety/Safety of Machinery

Declaration of Conformity

Test Certificates

other

Railway



Type Examination Certificate



Type Test Certificates/Test Report

Confirmation

Special Test Certific-<u>ate</u>

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RM1307-1AA04


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RM1307-1AA04


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RM1307-1AA04

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RM1307-1AA04&lang=en







last modified: 11/3/2021 🖸