

Mod. 3818HL.B


3818HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE

Medium size watertight case injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Suitable for carrying laptops, small drones, first aid kit, photographic and optical equipment, electronic devices, tools and more.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available



METRIC MM-KG-C°



INTERNAL DIMENSIONS

L LENGTH	380 mm
W WIDTH	270 mm
D DEPTH	180 mm
LID	47 mm
BASE	133 mm


EXTERNAL DIMENSIONS

L LENGTH	420 mm
W WIDTH	340 mm
D DEPTH	202 mm

OTHER DATA

WEIGHT EMPTY	2.49 Kg
WEIGHT WITH FOAM	2.93 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	18.50 lt
BUOYANCY	12.30 Kg/max
OPERATING TEMPERATURE	°C min -33 / max +90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS

L LENGTH	14 15/16 in
W WIDTH	10 5/8 in
D DEPTH	7 1/16 in
LID	1 7/8 in
BASE	5 1/4 in

EXTERNAL DIMENSIONS

L LENGTH	16 9/16 in
W WIDTH	13 3/8 in
D DEPTH	7 15/16 in

OTHER DATA

WEIGHT EMPTY	5.48 lbs
WEIGHT WITH FOAM	6.45 lbs
WEIGHT WITH CUSTOM FOAM	lbs
VOLUME	4.88 gal
BUOYANCY	27.11 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max +194