# **SIEMENS**

### Data sheet

## 3RT2046-1AP00

power contactor, AC-3 95 A, 45 kW / 400 V 1 NO + 1 NC, 230 V AC, 50 Hz 3-pole, 3 NO, Size S3 screw terminal



Figure similar

Product brand name	SIRIUS
Product designation	Power contactor
Product type designation	3RT2
General technical data	
Size of contactor	S3
Product extension	
<ul> <li>function module for communication</li> </ul>	No
Auxiliary switch	Yes
Surge voltage resistance	
<ul> <li>of main circuit rated value</li> </ul>	8 kV
<ul> <li>of auxiliary circuit rated value</li> </ul>	6 kV
maximum permissible voltage for safe isolation	
<ul> <li>between coil and main contacts acc. to EN</li> </ul>	690 V
60947-1	
Protection class IP	
• on the front	IP20
• of the terminal	IP00

Shock resistance at rectangular impulse	
• at AC	6.7 g / 5 ms, 4.0 g / 10 ms
Shock resistance with sine pulse	
● at AC	10.6 g / 5 ms, 6.3 g / 10 ms
Mechanical service life (switching cycles)	
• of contactor typical	10 000 000
• of the contactor with added electronics-	5 000 000
compatible auxiliary switch block typical	
<ul> <li>of the contactor with added auxiliary switch block typical</li> </ul>	10 000 000
Reference code acc. to DIN 40719 extended	к
according to IEC 204-2 acc. to IEC 750	
Reference code acc. to DIN EN 81346-2	Q
Ambient conditions	
Installation altitude at height above sea level	
• maximum	2 000 m
Ambient temperature	
during operation	-25 +60 °C
during storage	-55 +80 °C
/lain circuit	
Number of poles for main current circuit	3
Number of NO contacts for main contacts	3
Operating voltage	
at AC-3 rated value maximum	1 000 V
Operating current	
• at AC-1 at 400 V	
— at ambient temperature 40 °C rated value	130 A
● at AC-1	
— up to 690 V at ambient temperature 40 °C rated value	130 A
— up to 690 V at ambient temperature 60 °C rated value	110 A
— up to 1000 V at ambient temperature 40 °C rated value	70 A
— up to 1000 V at ambient temperature 60 °C rated value	60 A
• at AC-2 at 400 V rated value	95 A
• at AC-3	
— at 400 V rated value	95 A
— at 500 V rated value	95 A
— at 690 V rated value	78 A
• at AC-4 at 400 V rated value	80 A

Connectable conductor cross-section in main circuit	
at AC-1	
• at 60 °C minimum permissible	35 mm <sup>2</sup>
• at 40 °C minimum permissible	50 mm <sup>2</sup>
Operating current for approx. 200000 operating cycles at AC-4	
• at 400 V rated value	42 A
• at 690 V rated value	30 A
Operating current	
• at 1 current path at DC-1	
— at 24 V rated value	100 A
— at 110 V rated value	9 A
— at 220 V rated value	2 A
— at 440 V rated value	0.6 A
— at 600 V rated value	0.4 A
<ul> <li>with 2 current paths in series at DC-1</li> </ul>	
— at 24 V rated value	100 A
— at 110 V rated value	100 A
— at 220 V rated value	10 A
— at 440 V rated value	1.8 A
— at 600 V rated value	1 A
<ul> <li>with 3 current paths in series at DC-1</li> </ul>	
— at 24 V rated value	100 A
— at 110 V rated value	100 A
— at 220 V rated value	80 A
— at 440 V rated value	4.5 A
— at 600 V rated value	2.6 A
Operating current	
<ul> <li>at 1 current path at DC-3 at DC-5</li> </ul>	
— at 24 V rated value	40 A
— at 110 V rated value	2.5 A
— at 220 V rated value	1 A
— at 440 V rated value	0.15 A
— at 600 V rated value	0.06 A
<ul> <li>with 2 current paths in series at DC-3 at DC-5</li> </ul>	
— at 24 V rated value	100 A
— at 110 V rated value	100 A
— at 220 V rated value	7 A
— at 440 V rated value	0.42 A
— at 600 V rated value	0.16 A
• with 3 current paths in series at DC-3 at DC-5	
— at 24 V rated value	100 A

— at 110 V rated value	100 A
— at 220 V rated value	35 A
— at 440 V rated value	0.8 A
— at 600 V rated value	0.35 A
Operating power	
● at AC-1	
— at 230 V rated value	49 kW
— at 230 V at 60 °C rated value	42 kW
— at 400 V rated value	86 kW
— at 400 V at 60 °C rated value	72 kW
— at 690 V rated value	148 kW
— at 690 V at 60 °C rated value	125 kW
• at AC-2 at 400 V rated value	45 kW
• at AC-3	
— at 230 V rated value	22 kW
— at 400 V rated value	45 kW
— at 500 V rated value	55 kW
— at 690 V rated value	75 kW
Operating power for approx. 200000 operating cycles	
at AC-4	
• at 400 V rated value	22 kW
• at 690 V rated value	27.4 kW
Thermal short-time current limited to 10 s	760 A
Power loss [W] at AC-3 at 400 V for rated value of	6.6 W
the operating current per conductor	
No-load switching frequency	5 000 1/h
at AC Operating frequency	
• at AC-1 maximum	900 1/h
	350 1/h
<ul><li>at AC-2 maximum</li><li>at AC-3 maximum</li></ul>	850 1/h
• at AC-4 maximum	250 1/h
Control circuit/ Control	
Type of voltage of the control supply voltage	AC
Control supply voltage at AC	
• at 50 Hz rated value	230 V
Operating range factor control supply voltage rated value of magnet coil at AC	
• at 50 Hz	0.8 1.1
Apparent pick-up power of magnet coil at AC	
• at 50 Hz	296 V·A
Inductive power factor with closing power of the coil	

● at 50 Hz	0.61
Apparent holding power of magnet coil at AC	
• at 50 Hz	19 V·A
Inductive power factor with the holding power of the	_
coil	
• at 50 Hz	0.38
Closing delay	
• at AC	13 50 ms
Opening delay	
• at AC	10 21 ms
Arcing time	10 20 ms
Auxiliary circuit	
Number of NC contacts for auxiliary contacts	
<ul> <li>instantaneous contact</li> </ul>	1
Number of NO contacts for auxiliary contacts	
<ul> <li>instantaneous contact</li> </ul>	1
Operating current at AC-12 maximum	10 A
Operating current at AC-15	
• at 230 V rated value	6 A
• at 400 V rated value	3 A
• at 500 V rated value	2 A
• at 690 V rated value	1 A
Operating current at DC-12	
• at 24 V rated value	10 A
• at 48 V rated value	6 A
● at 60 V rated value	6 A
• at 110 V rated value	3 A
• at 125 V rated value	2 A
• at 220 V rated value	1 A
• at 600 V rated value	0.15 A
Operating current at DC-13	
• at 24 V rated value	10 A
• at 48 V rated value	2 A
● at 60 V rated value	2 A
• at 110 V rated value	1 A
• at 125 V rated value	0.9 A
• at 220 V rated value	0.3 A
• at 600 V rated value	0.1 A
Contact reliability of auxiliary contacts	1 faulty switching per 100 million (17 V, 1 mA)

UL/CSA ratings Full-load current (FLA) for three-phase AC motor

• at 480 V rated value	96 A
• at 600 V rated value	77 A
Yielded mechanical performance [hp]	
<ul> <li>for single-phase AC motor</li> </ul>	
— at 110/120 V rated value	10 hp
— at 230 V rated value	20 hp
<ul> <li>for three-phase AC motor</li> </ul>	
— at 200/208 V rated value	30 hp
— at 220/230 V rated value	30 hp
— at 460/480 V rated value	75 hp
— at 575/600 V rated value	75 hp
Contact rating of auxiliary contacts according to UL	A600 / P600

Short-circuit protection	
Design of the fuse link	
<ul> <li>for short-circuit protection of the main circuit</li> </ul>	
— with type of coordination 1 required	gG: 250 A (690 V, 100 kA), aM: 160 A (690 V, 100 kA), BS88: 200 A (415 V, 80 kA)
— with type of assignment 2 required	gG: 160 A (690 V, 100 kA), aM: 100 A (690 V, 100 kA), BS88: 125 A (415 V, 80 kA)
<ul> <li>for short-circuit protection of the auxiliary switch required</li> </ul>	fuse gG: 10 A
Installation/ mounting/ dimensions	
Mounting position	+/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface
Mounting type	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715
<ul> <li>Side-by-side mounting</li> </ul>	Yes
Height	140 mm
Width	70 mm
Depth	152 mm
Required spacing	
<ul> <li>with side-by-side mounting</li> </ul>	
— forwards	20 mm
— upwards	10 mm
— downwards	10 mm
— at the side	0 mm
<ul> <li>for grounded parts</li> </ul>	
— forwards	20 mm
— upwards	10 mm
— at the side	10 mm
— downwards	10 mm

• for live parts	20 mm
— forwards	20 mm
— upwards	10 mm
— downwards	10 mm
— at the side	10 mm
Connections/Terminals	
Type of electrical connection	
<ul> <li>for main current circuit</li> </ul>	screw-type terminals
<ul> <li>for auxiliary and control current circuit</li> </ul>	screw-type terminals
Type of connectable conductor cross-sections	
• for main contacts	
<ul> <li>— finely stranded with core end processing</li> </ul>	2x (2.5 35 mm²), 1x (2.5 50 mm²)
<ul> <li>at AWG conductors for main contacts</li> </ul>	2x (10 1/0), 1x (10 2)
Connectable conductor cross-section for main	
contacts	
• solid	2.5 16 mm²
• stranded	6 70 mm²
<ul> <li>finely stranded with core end processing</li> </ul>	2.5 50 mm²
Connectable conductor cross-section for auxiliary contacts	
<ul> <li>single or multi-stranded</li> </ul>	0.5 2.5 mm²
<ul> <li>finely stranded with core end processing</li> </ul>	0.5 2.5 mm²
Type of connectable conductor cross-sections	
<ul> <li>for auxiliary contacts</li> </ul>	
— single or multi-stranded	2x (0,5 1,5 mm²), 2x (0,75 2,5 mm²)
<ul> <li>— finely stranded with core end processing</li> </ul>	2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)
<ul> <li>at AWG conductors for auxiliary contacts</li> </ul>	2x (20 16), 2x (18 14)
AWG number as coded connectable conductor cross section	
• for main contacts	10 2
<ul> <li>for auxiliary contacts</li> </ul>	20 14
Safety related data	
B10 value	
<ul> <li>with high demand rate acc. to SN 31920</li> </ul>	1 000 000
Proportion of dangerous failures	
• with low demand rate acc. to SN 31920	40 %
<ul> <li>with high demand rate acc. to SN 31920</li> </ul>	73 %
Failure rate [FIT]	
• with low demand rate acc. to SN 31920	100 FIT
Product function	
• Mirror contact acc. to IEC 60947-4-1	Yes

<ul> <li>positively driven operation acc. to IEC 60947-5-</li> <li>1</li> </ul>	No
T1 value for proof test interval or service life acc. to IEC 61508	20 у
Protection against electrical shock	finger-safe when touched vertically from front acc. to IEC 60529

enincales/appro	ovais				
General Produ	uct Approval			EMC	Declaration c Conformity
ccc	CSA		EHC	C-Tick	EG-Konf.
Test Ostificat		a file a m	Dellever		

Test Certificates	;	other	Railway
Type Test Certific-	Special Test Certi-	Confirmation	Vibration and Shock
ates/Test Report	ficate		

#### urther information

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT2046-1AP00

#### Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2046-1AP00


Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RT2046-1AP00


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RT2046-1AP00&lang=en


#### Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RT2046-1AP00/char

Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RT2046-1AP00&objecttype=14&gridview=view1 of









last modified:

12/13/2018