SIEMENS

Data sheet 3LD3050-0TK11



Load disconnector 3LD3, lu 16 A Main switch 3-pole Rated operating capacity at AC-23 A at 400V 7.5kW Front plate mounting Basic switch with Central hole mounting 22.5mm Toggle drive black 48x48 mm

Model	
Product brand name	SENTRON
Product designation	3LD Switch disconnector
Design of the product	Main switch
Display version / for switch position indicator manual operation	1 ON - 0 OFF
Design of the operating mechanism	selector switch
Design of handle	knob-operated mechanism, black
Type of the driving mechanism / motor drive	No
General technical data	
Number of poles	3
Number of poles / Note	3
Type of device	fixed mounting
Type of switch	front mounted
Operating frequency / maximum	50 1/h
Voltage	
Insulation voltage / rated value	690 V
Surge voltage resistance / rated value	6 kV

Protection class	
Protection class IP	IP65
Protection class IP / on the front	IP65
Dissipation	
Power loss [W] / for rated value of the current / at AC	0.5 W
/ in hot operating state / per pole	
Electricity	
Current / at AC / rated value	16 A
Continuous current / rated value	16 A
Continuous current / of upstream fuse / rated value	16 A
Short-time current resistance (Icw) / at 690 V / limited	500 A
to 1 s / rated value	
Main circuit	
Operating frequency	
• initial value	50 Hz
Full-scale value	60 Hz
Operating power	
• at AC-23 A / at 400 V / rated value	7.5 kW
• at AC-23 A / at 690 V / rated value	7.5 kW
• at AC-3 / at 400 V / rated value	5.5 kW
• at AC-3 / at 690 V / rated value	5.5 kW
Operating voltage	
• at AC / at 50/60 Hz / rated value	690 V
Auxiliary circuit	
Number of CO contacts / for auxiliary contacts	0
Number of NC contacts / for auxiliary contacts	0
Number of NO contacts / for auxiliary contacts	0
Operating voltage / of auxiliary contacts / at AC / maximum	500 V
Continuous current / of the auxiliary contact / rated	10 A
value	
Insulation voltage / of the auxiliary switch / rated	500 V
value	
Suitability	
Suitability for use	
Main switch	Yes
switch disconnector	Yes
EMERGENCY OFF switch	No
safety switch	Yes
maintenance/repair switch	Yes
Product details	

Product feature / interlock	Yes
Number of bracket locks / maximum	2
Hasp thickness / of bracket locks / minimum	4 mm
Hasp thickness / of bracket locks / maximum	6 mm
Product extension / optional	
motor drive	No
 Voltage trigger 	No

Short circuit	
Conditional short-circuit current / with line-side fuse	
protection	
• at 690 V / by gG fuse / rated value	6 kA
Number of NC contacts	0
Number of NO contacts	0

Connections	
Type of connectable conductor cross-sections	
 for copper conductor / solid 	1x (2.5 to 16 mm²)
 for copper conductor / stranded 	1x (2.5 to 16 mm²)
 for auxiliary contacts / solid 	2x (0.75 2.5 mm²), 1x 4 mm²
 for auxiliary contacts / finely stranded / with core end processing 	2x (0.75 1.5 mm²), 1x 2.5 mm²
• for auxiliary contacts / stranded	2x (0.75 2.5 mm2), 1x 4 mm2
Type of electrical connection	
for main current circuit	box terminal
for auxiliary contacts	Box terminals

Requirements	
Design of the fuse link	
 for short-circuit protection of the main circuit / required 	fuse gL/gG: 20 A
for short-circuit protection of the auxiliary switch / required	fuse gL/gG: 10 A

Mechanical Design	
Height	60 mm
Width	36 mm
Depth	114 mm
Mounting type	Built-in unit fixed-mounted version
Mounting type	
 front mounting with 4-hole attachment 	No
 front mounting with central attachment 	Yes
• rail mounting	No
Net weight	200 g

Environmental conditions

Ambient temperature

during operation / minimum

-25 °C

• during operation / maximum

55 °C

Certificates

Reference code

acc. to DIN EN 61346-2

S SF

• acc. to DIN EN 81346-2

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3050-0TK11

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3LD3050-0TK11

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD3050-0TK11

CAx-Online-Generator

http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications







