

3M™ SC-DR Surface Conditioning

Roloc Surface Conditioning Disc



Diam. 25



Diam.50



Diam.75

Product Construction

Mineral and Grit Type A : CRS, MED, VFN

Type S : SFN

Diameter 25 mm
50 mm
75 mm

Available Forms

f



Applications

Materials:
Metals, plastics, lacquers

f

f

Recommendation

f

Recommended for Mold grinding and subsequent smoothing; model building; aircraft construction and maintenance, grinding and smoothing weld seams on appliances; removing paint and rust, touching-up milled surfaces; removing scale and residual sealants

Accessories

Roloc+™ Holder Nr. 1 (25mm), No. 3 (50 mm),
Back-up pad X (PN84993), H (PN94998) or M (75 mm).

3M™ SC-DR Surface Conditioning

Features

Surface conditioning web



Cloth backed



Integrated grinding aid coating



Three dimensional web



Roloc™ fastening system

Advantages

Open construction

Tear resistant

Even suitable for dry applications

Controlled cutting action

Change products or grits faster without tools

Benefits

Anti-loading


Ideal for angle and dual action grinders

Wet and/or dry operations

Will not alter critical tolerances

Saves time and money

Machines



Safety



Quality

3M Plants are ISO 9002 certified.

Product Use: All statements, technical information and recommendations contained in this document are based on tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.



3M Italia SpA
Reperto ASD Abrasivi Industriali
 Via Norberto Bobbio,21
 20069 – Pioltello Milano
 Tel: 02 7035 2529
 Fax: 02 93660172

Data Sheet: SC-DR
 Issued 06/11
 © 3M 2011. All rights reserved.