# **SIEMENS**

Data sheet 3RB3026-1SB0

Overload relay 3...12 A for motor protection Size S0, Class 10E Contactor mounting Main circuit: Screw Auxiliary circuit: Screw Manual-Automatic-Reset



Product brand name	SIRIUS
Product designation	solid-state overload relay
Product type designation	3RB3

General technical data	
Size of overload relay	S0
Size of contactor can be combined company-specific	S0
Power loss [W] total typical	0.6 W
Insulation voltage with degree of pollution 3 rated value	690 V
Surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
<ul> <li>in networks with grounded star point between auxiliary and auxiliary circuit</li> </ul>	300 V
<ul> <li>in networks with grounded star point between auxiliary and auxiliary circuit</li> </ul>	300 V
<ul> <li>in networks with grounded star point between main and auxiliary circuit</li> </ul>	600 V
<ul> <li>in networks with grounded star point between main and auxiliary circuit</li> </ul>	690 V
Protection class IP	

• on the front	IP20
of the terminal	IP20
Shock resistance	15g / 11 ms
• acc. to IEC 60068-2-27	15g / 11 ms; Signaling contact 97 / 98 in position "Tripped": 9g / 11 ms
Thermal current	12 A
Recovery time	
<ul> <li>after overload trip with automatic reset typical</li> </ul>	3 min
<ul> <li>after overload trip with remote-reset</li> </ul>	0 min
<ul> <li>after overload trip with manual reset</li> </ul>	0 min
Type of protection	II (2) G [Ex e] [Ex d] [Ex px] II (2) D [Ex t] [Ex p]
Certificate of suitability relating to ATEX	PTB 09 ATEX 3001
Protection against electrical shock	finger-safe
Reference code acc. to DIN EN 81346-2	F
Ambient conditions	
Installation altitude at height above sea level	
• maximum	2 000 m
Ambient temperature	
during operation	-25 +60 °C
during storage	-40 +80 °C
during transport	-40 +80 °C
Temperature compensation	-25 +60 °C
Relative humidity during operation	10 95 %
Main circuit	
Number of poles for main current circuit	3
Adjustable pick-up value current of the current- dependent overload release	3 12 A
Operating voltage	
• rated value	690 V
• at AC-3 rated value maximum	690 V
Operating frequency rated value	50 60 Hz
Operating current rated value	12 A
Operating power	
<ul> <li>for three-phase motors at 400 V at 50 Hz</li> </ul>	1.5 5.5 kW
• for AC motors at 500 V at 50 Hz	1.5 5.5 kW
• for AC motors at 690 V at 50 Hz	2.2 7.5 kW
Auxiliary circuit	
Design of the auxiliary switch	integrated
Number of NC contacts for auxiliary contacts	1
• Note	for contactor disconnection
Number of NO contacts for auxiliary contacts	1
• Note	for message "tripped"

Number of CO contacts	
• for auxiliary contacts	0
Operating current of auxiliary contacts at AC-15	
● at 24 V	4 A
● at 110 V	4 A
● at 120 V	4 A
● at 125 V	4 A
● at 230 V	3 A
Operating current of auxiliary contacts at DC-13	
● at 24 V	2 A
● at 60 V	0.55 A
● at 110 V	0.3 A
● at 125 V	0.3 A
• at 220 V	0.11 A
Protective and monitoring functions	
Trip class	CLASS 10E
Design of the overload release	electronic
Design of the overload release  IL/CSA ratings	electronic
	electronic
JL/CSA ratings	electronic  12 A
IL/CSA ratings Full-load current (FLA) for three-phase AC motor	
IL/CSA ratings Full-load current (FLA) for three-phase AC motor  • at 480 V rated value	12 A
Full-load current (FLA) for three-phase AC motor  • at 480 V rated value  • at 600 V rated value	12 A 12 A
Full-load current (FLA) for three-phase AC motor  • at 480 V rated value  • at 600 V rated value  Contact rating of auxiliary contacts according to UL	12 A 12 A
Full-load current (FLA) for three-phase AC motor  • at 480 V rated value  • at 600 V rated value  Contact rating of auxiliary contacts according to UL	12 A 12 A
PL/CSA ratings Full-load current (FLA) for three-phase AC motor  • at 480 V rated value  • at 600 V rated value  Contact rating of auxiliary contacts according to UL  Chort-circuit protection  Design of the fuse link	12 A 12 A
Full-load current (FLA) for three-phase AC motor  • at 480 V rated value  • at 600 V rated value  Contact rating of auxiliary contacts according to UL  chort-circuit protection  Design of the fuse link  • for short-circuit protection of the main circuit	12 A 12 A B600 / R300

Mounting positionanyHeight87 mmWidth45 mmDepth84 mm	Installation/ mounting/ dimensions	
Width 45 mm Depth 84 mm	Mounting position	any
Depth 84 mm	Height	87 mm
	Width	45 mm
Demilia describes	Depth	84 mm
Required spacing	Required spacing	
• with side-by-side mounting	<ul> <li>with side-by-side mounting</li> </ul>	
— forwards 0 mm	— forwards	0 mm
— Backwards 0 mm	— Backwards	0 mm
— upwards 0 mm	— upwards	0 mm
— downwards 0 mm	— downwards	0 mm

— at the side	0 mm
• for grounded parts	
— forwards	6 mm
— Backwards	0 mm
— upwards	6 mm
— at the side	6 mm
— downwards	6 mm
• for live parts	
— forwards	6 mm
— Backwards	0 mm
— upwards	6 mm
— downwards	6 mm
— at the side	6 mm

Connections/Terminals	
Product function	
<ul> <li>removable terminal for auxiliary and control circuit</li> </ul>	Yes
Type of electrical connection	
for main current circuit	screw-type terminals
<ul> <li>for auxiliary and control current circuit</li> </ul>	screw-type terminals
Arrangement of electrical connectors for main current circuit	Top and bottom
Type of connectable conductor cross-sections	
• for main contacts	
— solid	2x (1 2.5 mm²), 2x (2.5 10 mm²)
— stranded	2x 10 mm²
— single or multi-stranded	1x (1 10 mm²), 2x (1 10 mm²)
— finely stranded with core end processing	1x (1 6 mm²), 2 x (1 6 mm²), 1x 10 mm²
<ul> <li>at AWG conductors for main contacts</li> </ul>	1x (16 8), 2x (16 8)
Type of connectable conductor cross-sections	
for auxiliary contacts	
— solid	1x (0.5 4 mm²), 2x (0.5 2.5 mm²)
<ul> <li>single or multi-stranded</li> </ul>	1x (0,5 4 mm²), 2x (0,5 2,5 mm²)
— finely stranded with core end processing	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
<ul> <li>at AWG conductors for auxiliary contacts</li> </ul>	1x (20 14), 2x (20 14)
Tightening torque	
• for main contacts with screw-type terminals	2 2.5 N·m
• for auxiliary contacts with screw-type terminals	0.8 1.2 N·m
Design of screwdriver shaft	Diameter 5 to 6 mm
Size of the screwdriver tip	Pozidriv PZ 2
Design of the thread of the connection screw	
• for main contacts	M4

• of the auxiliary and control contacts

М3

- ammilialeatia	n/ Pratacal
Communicatio	

Type of voltage supply via input/output link master No

## Electromagnetic compatibility

#### Conducted interference

- due to burst acc. to IEC 61000-4-4 2 kV (power ports), 1 kV (signal ports) corresponds to degree of severity 3
- due to conductor-earth surge acc. to IEC 2 kV (line to earth) corresponds to degree of severity 3 61000-4-5
- due to conductor-conductor surge acc. to IEC 1 kV (line to line) corresponds to degree of severity 3 61000-4-5
- due to high-frequency radiation acc. to IEC

  10 V in frequency range 0.15 to 80 MHz, modulation 80 % AM with 1 kHz

Field-bound parasitic coupling acc. to IEC 61000-4-3

Electrostatic discharge acc. to IEC 61000-4-2 6 kV contact discharge / 8 kV air discharge

#### Display

### Display version

• for switching status Slide switch

#### Certificates/approvals

### **General Product Approval**

**EMC** 

For use in hazardous locations













Declaration of Conformity

**Test Certificates** 

Marine / Shipping



Type Test Certificates/Test Report

Special Test Certificate







Marine / Shipping

other









Confirmation

#### Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

#### Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RB3026-1SB0

### Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RB3026-1SB0

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/ww/en/ps/3RB3026-1SB0


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RB3026-1SB0&lang=en


### Characteristic: Tripping characteristics, I2t, Let-through current


https://support.industry.siemens.com/cs/ww/en/ps/3RB3026-1SB0/char

Further characteristics (e.g. electrical endurance, switching frequency)
http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RB3026-1SB0&objecttype=14&gridview=view1









last modified: 12/13/2018