## **SIEMENS**

## Data sheet

## 3RH2911-1GA40

AUX.SWITCH BLOCK,FRONT,4NO, CURR.PATH: 1NO, 1NO, 1NO, FOR CONTACTOR RELAYS, SZ S00, SCREW TERMINAL 53 / 54,63 / 64,73 / 74,83 / 84

General technical data:		
product brand name		SIRIUS
Suitability for use		Contactor relay
Protection class IP on the front	_	IP20
Ambient temperature	_	
<ul> <li>during storage</li> </ul>	°C	-55 +80
<ul> <li>during operation</li> </ul>	°C	-25 +60
Mechanical service life (switching cycles) typical	-	10 000 000
Electrical endurance (switching cycles) at AC-15 at 230 V typical		200 000
Contact reliability	_	one incorrect switching operation of 100 million switching operations (17 V, 1 mA)
Contact reliability of auxiliary contacts	_	1 faulty switching per 100 million (17 V, 1 mA)
Insulation voltage with degree of pollution 3 rated value	V	690
Surge voltage resistance rated value	kV	6
Auxiliary circuit:		
Number of NC contacts for auxiliary contacts		
<ul> <li>instantaneous contact</li> </ul>		0

<ul> <li>lagging switching</li> </ul>		0
Number of NO contacts for auxiliary contacts		
<ul> <li>instantaneous contact</li> </ul>		4
<ul> <li>leading contact</li> </ul>		0
Operating current of auxiliary contacts at AC-12		
● at 24 V	A	10
• at 230 V	А	10
• maximum	А	10
Operating current		
<ul> <li>of auxiliary contacts</li> </ul>		
— at AC-14		
— at 125 V	А	6
— at 250 V	А	6
— at AC-15		
— at 24 V	А	6
— at 230 V	А	6
— at 400 V	А	3
• at AC-15 at 690 V rated value	А	1
Operating current	_	
<ul> <li>with 2 current paths in series at DC-12</li> </ul>		
— at 24 V rated value	А	10
— at 60 V rated value	А	10
— at 110 V rated value	А	4
— at 220 V rated value	А	2
— at 440 V rated value	А	1.3
— at 600 V rated value	А	0.65
<ul> <li>with 3 current paths in series at DC-12</li> </ul>		
— at 24 V rated value	А	10
— at 60 V rated value	А	10
— at 110 V rated value	А	10
— at 220 V rated value	А	3.6
— at 440 V rated value	А	2.5
— at 600 V rated value	А	1.8
Operating current		
<ul> <li>of auxiliary contacts at DC-13</li> </ul>		
— at 24 V	А	6
— at 60 V	А	2
— at 110 V	А	1
— at 220 V	А	0.3
with 2 current paths in series at DC-13		
— at 24 V rated value	A	10

— at 60 V rated value	А	3.5
— at 110 V rated value	А	1.3
— at 220 V rated value	А	0.9
— at 440 V rated value	А	0.2
— at 600 V rated value	А	0.1
<ul> <li>with 3 current paths in series at DC-13</li> </ul>		
— at 24 V rated value	А	10
— at 60 V rated value	А	4.7
— at 110 V rated value	А	3
— at 220 V rated value	А	1.2
— at 440 V rated value	А	0.5
— at 600 V rated value	А	0.26

Installation/ mounting/ dimensions:			
Mounting type		snap-on mounting	
Width	mm	36	
Height	mm	37.5	
Depth	mm	43.7	

Connections/ Terminals:			
Type of electrical connection for auxiliary and control		screw-type terminals	
current circuit			
Type of connectable conductor cross-sections			
<ul> <li>for auxiliary contacts</li> </ul>			
— finely stranded			
— with core end processing		2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)	
<ul> <li>at AWG conductors for auxiliary contacts</li> </ul>		2x (20 16), 2x (18 14)	
Safety related data:			
Product function Mirror contact acc. to IEC 60947-4-1		No	
Product function positively driven operation acc. to		Yes	
IEC 60947-5-1			
Note		with 3RH2	

Certificates/ approvals:

General Product	Approval			Declaration of Conformity	Test Certificates
CCC	(SA)	EHC		EG-Konf.	spezielle Prüfbescheinigunge <u>n</u>
Test Certificates	Shipping Ap	proval			
Typprüfbescheinigu ng/Werkszeugnis	ABS	B U R E A U V E R I T A S	DNV DNV	GL GL	Lloyd's Kegister LRS
Shipping Approv	al		other		
PRS	RINA	RMRS	<u>Umweltbestätigur</u>		

## Further information

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system) http://www.siemens.com/industrymall

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RH29111GA40

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RH29111GA40

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RH29111GA40&lang=en





