Technical Specifications

HP E24m G4 FHD USB-C Conferencing Monitor



- 1. Microphones (2)
- 2. Camera Light
- 3. RGB Lens
- 4. IR Lens
- 5. IR LED


Front

- 6. Audio Buttons
- 7. OSD Buttons
- 8. Power LED
- 9. Power Button
- 10. Audio Combo Jack



Technical Specifications

HP E24m G4 FHD USB-C Conferencing Monitor



- 1. Security Cable Slot
- 2. Power Connector
- 3. HDMI 1.4 Port
- 4. DisplayPort[™] 1.2
- 5. USB-C[®] Port (Alt Mode DisplayPort[™] 1.2, power delivery up to 65W)

Back

- 6. DisplayPort[™] 1.2 out
- **7.** RJ45
- 8. USB A Port (2)
- 9. USB A Port (2)



Technical Specifications

Models: 40Z32AA

Panel Specifications	Display Size (Diagonal)	23.8"
	Panel Technology	IPS
	Max Refresh Rate	75 Hz
	Native Resolution	1920 x 1080*
		*Panel is VESA standards compliant.
	Panel Bit Depth	16.7M colors/ 8 bit (6 bit+ 2FRC)
	Aspect Ratio	16:9
	Brightness (Typical)	300 nits
	Contrast Ratio (Static)	1,000 :1
	Dynamic Contrast Ratio	10,000,000:1
	Flicker Free	Yes
	Pixel Pitch	0.2745 (H) ×0.2745(V)
	Pixels Per Inch (PPI)	93 PPI
	Backlight Lamp Life Minimum	30,000
	(To Half Brightness - In Hours)	
	Backlight Type	Edge-lit
	Screen Treatment	Anti-glare
	Hardness	3H
	Haze	25%
	Response Time (Typical)	5ms GtG (with overdrive)
	Horizontal Viewing Angle	178°
	(Typical Cr>10)	
	Vertical Viewing Angle (Typical Cr>10)	178°
	Panel Active Area Metric (W X H)	52.704 x 29.646
	Panel Active Area Imperial (W X H)	20.74 x 11.67
	actual performance may vary either higher or	
Color Gamut Coverage	sRGB	99%
Color Management	Color Space/ Subsampling Support	RGB 4:4:4
_	RGB Channel Adjust	Yes, Gain
	Default Color Temperature	Yes, 6500K
Monitor Specifications	Bezel Type	3-sided Micro Edge
Homed Specifications	Color Of Stand	Silver
	Color Of Head	Black
	Tilt	-5 to +23°
	Swivel	±45°
	Pivot	±90°
	Height Adjust Range	150mm
	Vesa Mounting	100 mm x 100 mm
	Security Lock	Standard Security Lock Slot
	Detachable Stand	Yes
	Warranty	Based on region
	Low Blue Light	Yes, HP Eye Ease (TÜV Low Blue Light Hardware Solution
		certified)
Multimedia		5 MP
mullimeuld	Wohcam	
	Webcam Webcam Features	
	Webcam Webcam Features	Independent tilt -20° to 5°, Windows Hello support
	Webcam Features	Independent tilt -20° to 5°, Windows Hello support (IR sensor), Pop-up privacy
		Independent tilt -20° to 5°, Windows Hello support



	Speaker Output Power Conferencing Hot Keys Certified Collaboration Software Works With Chromebook Certified Display Software	2 x 5W Mic mute, Speaker Mute, Volume Up/Down Zoom Yes HP Display Center*, HP Display Manager *Host PC requires Windows 10. HP Display Center is available on the Microsoft store.
On Screen Display (OSD)	On Screen Display User Controls	Brightness+, Color, Image, Input, Power, Menu, Management, Information, Exit
	Native Resolution	Full HD (1920 x 1080) NOTE: DisplayPort 1.2 or HDMI 1.4 or USB-C 3.1 Gen1 (DP alt mode compatible) required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920x1080 at 60 Hz using one DP, HDMI, or USB-C (DP alt mode).
	Maximum Resolution	1920×1080 @75Hz
	Preset Graphic Modes/Supported Resolutions	640 x 480 @ 60Hz 720 x 400 @ 70 Hz 800 x 600 @ 60 Hz 1024 x 768 @ 60 Hz 1280 x 720 @ 60 Hz 1280 x 800 @ 60 Hz 1280 x 1024 @ 60 Hz 1440 x 900 @ 60 Hz 1600 x 900 @ 60 Hz 1680 x 1050 @ 60 Hz 1920 x 1080 @ 60 Hz 1920 x 1080 @ 75Hz
	Minimum Vertical Scan Rate	50 Hz
	Maximum Vertical Scan Rate	75 Hz
	Minimum Horizontal Scan Rate Maximum Horizontal Scan Rate	30K 85K
	Maximum Pixel Clock	180.0 MHz
	User Programmable Modes	Yes, 10
	User-Assignable Function Buttons	Yes, 3 (7 options)
	AUDIO	Built-in speakers
	Languages	11 (English, Spanish, German, French, Italian, Netherlands, Portuguese, Japanese, T-Chinese and S-Chinese, Russian)
Connector Types	DisplayPort™ DisplayPort™ Out HDMI HDCP USB Tupp, C® Video and Data Tuppafor	1 DisplayPort™ 1.2 1 DisplayPort™ 1.2-out 1 HDMI 1.4 Yes, DisplayPort and HDMI 1 USD Tures C® (Alt Mode DisplayPort IM 1.2, power delivery)
	USB Type-C [®] Video and Data Transfer	1 USB Type C [®] (Alt Mode DisplayPort [™] 1.2, power delivery up to 65W)
	USB- A AUDIO PORT ETHERNET	4 USB-A 1 x 3.5 mm Audio Jack (Audio In/Out Combo) Yes
Special Features	Switch	Menu, Minus ("-")/Brightness, Plus ("+")/Color, OK/Next
	Remote Manageability User Presets User Updateable Firmware	Active Input, Power In-Band MAPT, In-Band WoL, PXE Boot 12 Yes



Power & Operating Specs	Power Supply Power Source Power Consumption- Max Energy Saving/Stand By Mode Power Consumption- Typical	Internal Power Supply 100~240 VAC 50/60 Hz <150w <0.5w <37W
Energy Star Data	Operational Mode at 100 VAC Operational Mode at 115 VAC Operational Mode at 230 VAC	15.9 W 15.9 W 15.9 W
EU Energy Efficiency Class (ERP Lot-5)	On-mode Power Consumption Energy Efficiency Class	19 W A G F
Operating Conditions	Operating Temperature - Celsius Operating Temperature - Fahrenheit Non-Operating Temperature - Celsius Non-Operating Temperature - Fahrenheit Operating Humidity Non-Operating Humidity Operating Altitude Non-Operating Altitude	5° – 35° C 41° – 95° F -34° – 60°C -29° – 140°F 20 – 80% Relative Humidity (non-condensing) 5 – 95 0 – 5,000 m (16,400 ft.) 0 – 12,192 m (40,000 ft.)
Environmental Features and Certifications	Low Halogen Agency Approvals and Certifications	Yes NOTE : External power supplies, power cords, cables and peripherals are not Low Halogen. Service parts obtained after purchase may not be Low Halogen. WW application CE/CB/KC/KCC/E-Standby (KES)/NOM/ICE/TUV-S/ISO 9241-307/ EAC/cTUVus/PSB/ISC/CCC/CEL/CECP/SEPA/TCO/TCO Certified Edge/VCCI/FCC/BSMI/ Vietnam MEPS/Australian-New Zealand MEPS/WEEE/UAE ECAS/Ukraine/South Africa NRCS/BIS/RCM/ TIW, CS/Energy star 8, 0/Maxies, energy/(Dalaws, Energy/TCM)
	Microsoft WHQL Certification Energy Star® Certified EPEAT® Registered China Energy Label	TUV-GS/Energy star 8.0/Mexico energy/Belarus Energy/TGM Win 10 Yes, ENERY STAR [®] EPEAT [®] registered* *Based on US EPEAT [®] registration according to IEEE 1680.1-2018 EPEAT [®] . Status varies by country. Visit http://www.epeat.net for more information CEL, Grade 1
	TCO Certified Edge	Yes
	TCO Certified	Yes
	SmartWay Transport Partnership - NA only	Yes (NA sku)
Contains Recycled Plastics	Contains Recycled Plastics Recyclable Packaging (Box, packing materials)	ABS 85%, 5% Ocean-Bound Plastic 100%* *100% outer box packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Any plastic cushions are made from >90% recycled plastic.



HP E24m G4 FHD USB-C Conferencing Monitor

Unit Product/Package Specifications	Product Dimensions (Unpacked with stand) (W x D x H)	<u>Metric</u> 53.94 x 21.6 x 53.07 cm	<u>Imperial</u> 21.24 x 8.5 x 20.9 in
specifications	Product Dimensions (Packed) (W x D x H)	60.3 x 19.2 x 42.1 cm	23.74 x 7.56 x 16.57 in
	(Packed) (W × D × H) Display Head Dimensions (Unpacked without stand) (W × D × H)	53.94 x 4.7 x 35.56 cm	21.24 x 1.85x 14 in
	Base Area Footprint (w x d mm)	288 x 216 mm	11.34 x 8.50 in
	Bezel Measurements	Bottom: 52 mm	Bottom: 2.05 in
	Product Weight (Unpacked with stand)	7.39 kg	16.29 lb
	Product Weight (Packed)	10.31 kg	22.73 lb
	Product Weight (Head Only)	4.76 kg	10.47 lb
Pallet Information	Pallet Dimensions (L x W x H)	1216 x 970 x 2248 mm	47.87 x 38.19 x 88.5 in
	Pallet Total Weight (L×W×H) Pallet Layers Pallet Product per Layer Total Products per Pallet Container Load, 20-Foot Container Load, 40-Foot Container Load, 40-Foot HighQ	528.5 kg 5 10 50 500 1100 1100	1165.13 lb
What's in the box?	AC power cord (1.83m) 6.2 ft USB C to C Cable (1.8m) 5.9 ft Warranty Product Notice Quick Setup Poster		
User Guide and Warranty Languages	User Guide Languages Warranty Languages	Czech, Danish, Dutch, Engli German, Greek, Hebrew, Hu Kazakh, Korean, Latvian, Li Portuguese (Brazilian), Por Russian, Serbian, Slovak, Sl Thai, Turkey, Ukrainian English US (EN), English AP English UK (EN-GB), Arabic Bosnian (BS), Bulgarian (BG (TW), Croatian (HR), Czech (Estonian (ET), Finnish (FI), F European (FR), German (DE Hungarian (HU), Italian (IT), Korean (KO), Latvian (LV), L Polish (PL), Portuguese, Bra (PT), Romanian (RO), Russia (SK), Slovenian (SL), Spanis	thuanian, Norwegian, Polish, tuguese (Iberian), Romanian, Iovenian, Spanish, Swedish, (EN-AP), English LA (EN-LA), (AR) -17x, Bahasa Indonesia (ID), i), Chinese-S (CN), Chinese-T (CS), Danish (DA), Dutch (NL), French Canadian (FC), French), Greek (EL), Hebrew (HE), Japanese (JA), Kazakh (KK), ithuanian (LT), Norwegian (NO), azilian (BR), Portuguese, Iberian an (RU), Serbian (SR), Slovak h, Castilian (ES-ES), Spanish, edish (SV), Thai (TH), Turkish

Technical Specifications

ENVIRONMENTAL DATA

ENVIRONMENTA Eco-Label Certifications & declarations Sustainable Impact Specifications	 This product has received or is in the process of being labeled with one or more of these marks: IT ECO declaration US ENERGY STAR[®] US Federal Energy Management Program (FE EPEAT^D Gold: registered in the United States, your country. TCO Certified China Energy Conservation Program (CECP) China State Environmental Protection Admin Taiwan Green Mark Korea Eco-label Japan PC Green label* Ocean-bound plastic in Stand 80% post-consumer recycled plastic 	EMP) . See http://www.epeat.net		
	 Low halogen Outside Box and corrugated cushions are 100% sustainably sourced and recyclable 			
System Configuration	The configuration used for the Energy Consumption and Declared Noise Emissions data for the Notebook model is based on a "Typically Configured Notebook".			
Energy Consumption (in accordance with US ENERGY STAR® test			100046 500-	
method) Normal	115VAC, 60Hz	230VAC, 50Hz	100VAC, 50Hz	
Operation (Short idle)	t 15.9 W 15.79 W		N/A	
Sleep Off	0.43 W 0.27 W	0.46 W 0.28 W	N/A N/A	
	Note: Energy efficiency data listed is for an ENERGY STAR® family. HP computers marked with the ENERGY STAR Environmental Protection Agency (EPA) ENERGY STAR does not offer ENERGY STAR® compliant configuratio typically configured PC featuring a hard disk drive, a h Windows® operating system.	[®] Logo are compliant with t R [®] specifications for compu ns, then energy efficiency of	the applicable U.S. Iters. If a model family data listed is for a	
Heat Dissipation* Normal	115VAC, 60Hz	230VAC, 50Hz	100VAC, 50Hz	
Operation (Short idle)	54.38 BTU/hr	54 BTU/hr	N/A	
Sleep	1.47 BTU/hr	1.57 BTU/hr	N/A	
Off	0.92 BTU/hr 0.96 BTU/hr N/A *NOTE: Heat dissipation is calculated based on the measured watts, assuming the service level is attained for one hour. for one hour.			
Longevity and Upgrading	This product can be upgraded, possibly extending its and/or components contained in the	useful life by several years	5. Upgradeable features	



	Spare parts are available throughout the warranty production.	· · · ·			
Additional Information	This product is in compliance with the Res 2011/65/EC.	trictions of Hazardous Substa	ances (RoHS) directive -		
	 This HP product is designed to comply with (WEEE) Directive – 2002/96/EC. This are duct is in compliance with California. 				
	This product is in compliance with Californ Water and Toxic Enforcement Act of 1986).	_		
	This product is in compliance with the IEE www.epeat.net				
	 Plastics parts weighing over 25 grams use ISO1043. 				
	This product is 94.9% recycle-able when		1		
Packaging Materials	External:	PAPER/Corrugated	2273 g		
	Internal:	PLASTIC/Polyethylene high density - HDPE	66 g		
	The plastic packaging material contains at least C				
	The corrugated paper packaging materials contai	ns at least 92% recycled cont	ent.		
RoHS Compliance	HP Inc. complies fully with materials regulations. We were among the first companies to extend the restrictions in the European Union (EU) Restriction of Hazardous Substances (RoHS) Directive to our products worldwide through the HP GSE. HP has contributed to the development of related legislation in Europe, as well as China, India, and Vietnam.				
	We believe the RoHS directive and similar laws play an important role in promoting industry-wide elimination of substances of concern. We have supported the inclusion of additional substances— including PVC, BFRs, and certain phthalates—in future RoHS legislation that pertains to electrical and electronics products.				
	We met our voluntary objective to achieve worldwide compliance with the new EU RoHS requirements for virtually all relevant products by July 2013, and we will continue to extend the scope of the commitment to include further restricted substances as regulations continue to evolve.				
	To obtain a copy of the HP RoHS Compliance Statement, see HP RoHS position statement.				
Material Usage	This product does not contain any of the following HP General Specification for the Environment at http://www.hp.com/hpinfo/globalcitizenship/envi	_	-		
	AsbestosCertain Azo Colorants				
	 Certain Brominated Flame Retardants – may not be used as flame retardants in plastics Cadmium 				
	Chlorinated Hydrocarbons				
	Chlorinated Paraffins				
	Bis(2-Ethylhexyl) phthalate (DEHP) Benzyl buthalate (RBP)				
	 Benzyl butyl phthalate (BBP) Dibutyl phthalate (DBP) 				
	 Dibutyl phthalate (DBP) Diisobutyl phthalate (DIBP) 				
	Formaldehyde				
	Halogenated Diphenyl Methanes				
	 Lead carbonates and sulfates 				
	Lead and Lead compounds				
	Mercuric Oxide Batteries				
	Nickel – finishes must not be used on the external surface designed to be frequently handled or carried by the user.				



	 Ozone Depleting Substances Polybrominated Biphenyls (PBBs) Polybrominated Biphenyl Ethers (PBBEs) Polybrominated Biphenyl Oxides (PBBOs) Polychlorinated Biphenyl (PCB) Polychlorinated Terphenyls (PCT) Polyvinyl Chloride (PVC) – except for wires and cables, and certain retail packaging has been voluntarily removed from most applications. Radioactive Substances Tributyl Tin (TBT), Triphenyl Tin (TPT), Tributyl Tin Oxide (TBTO)
Packaging Usage	 HP follows these guidelines to decrease the environmental impact of product packaging: Eliminate the use of heavy metals such as lead, chromium, mercury and cadmium in packaging materials. Eliminate the use of ozone-depleting substances (ODS) in packaging materials. Design packaging materials for ease of disassembly. Maximize the use of post-consumer recycled content materials in packaging materials. Use readily recyclable packaging materials such as paper and corrugated materials. Reduce size and weight of packages to improve transportation fuel efficiency. Plastic packaging materials are marked according to ISO 11469 and DIN 6120 standards.
End-of-life Management and Recycling	HP offers end-of-life HP product return and recycling programs in many geographic areas. To recycle your product, please go to: http://www.hp.com/go/reuse-recycle or contact your nearest HP sales office. Products returned to HP will be recycled, recovered or disposed of in a responsible manner. The EU WEEE directive (2002/95/EC) requires manufacturers to provide treatment information for each product type for use by treatment facilities. This information (product disassembly instructions) is posted on the Hewlett Packard web site at: http://www.hp.com/go/recyclers. These instructions may be used by recyclers and other WEEE treatment facilities as well as HP OEM customers who integrate and resell HP equipment.
HP, Inc. Corporate Environmental Information	For more information about HP's commitment to the environment: Global Citizenship Report http://www.hp.com/hpinfo/globalcitizenship/gcreport/index.html Eco-label certifications http://www8.hp.com/us/en/hp-information/environment/ecolabels.html ISO 14001 certificates: http://h2O195.www2.hp.com/V2/GetDocument.aspx?docname=c04755842 and http://www.hp.com/hpinfo/globalcitizenship/environment/pdf/cert.pdf
footnotes	 Percentage of ocean-bound plastic contained in each component varies by product Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard. External power supplies, WWAN modules, power cords, cables and peripherals excluded. 100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.



Technical Specifications

Copyright © 2021 HP Development Company, L.P.

The information contained herein is subject to change without notice. The only warranties for HP products are set forth in the express limited warranty statements accompanying such products. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are registered trademarks or trademarks of Microsoft Corporation in the U.S. and/or other countries. ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency.

Summary

Change Log			
November 15, 2021	V1 to V2	Remove	Auto Focus from Webcam Features; Add Environmental Data
December 9, 2021	V2 to V3	Add	WWCB certification