

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0428150012](#)
Status: **Active**
Overview: [Mini-Fit Sr. Power Connectors](#)
Description: [Mini-Fit Sr. Crimp Terminal, Female, 10-12 AWG, Gold \(Au\)](#)

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-42815-001 \(PDF\)](#)
[Product Specification PS-42815-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-42815-001-002 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	42815
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	High Current/Low Force See Product Specification for maximum current rating by circuit size and application., High Current/Low Force See Product Specification for maximum current rating by circuit size and application.
Crimp Quality Equipment	Yes
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.
UPC	800756101095

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Net Weight	1.351/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.30mm max.
Wire Size AWG	10, 12
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	50.0A
-------------------------------	-------


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-42815-001-002
Product Specification	PS-42815-001
Sales Drawing	428150000-SD-000
Test Summary	TS-42815-001



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[42815 Series](#)

Use With

Mini-Fit Sr. Receptacle Housing [42816](#) ,
[43914](#)