## **SIEMENS**

## Data sheet

## 3RW40 46-1BB04



SIRIUS soft starter S3 80 A, 45 kW/400 V, 40 °C 200-480 V AC, 24 V AC/DC Screw terminals

General technical data		
Product brand name	SIRIUS	
Product feature		
<ul> <li>integrated bypass contact system</li> </ul>	Yes	
Thyristors	Yes	
Product function		
<ul> <li>Intrinsic device protection</li> </ul>	Yes	
<ul> <li>motor overload protection</li> </ul>	Yes	
<ul> <li>Evaluation of thermistor motor protection</li> </ul>	No	
• External reset	Yes	
<ul> <li>Adjustable current limitation</li> </ul>	Yes	
• inside-delta circuit	No	
Product component Motor brake output	No	
Reference identifier acc. to DIN EN 61346-2	Q	
Reference indentifier acc. to DIN 40719 extended	G	
according to IEC 204-2 acc. to IEC 750		
Power Electronics		
Product designation	Soft starter	

Operating current		
• at 40 °C rated value	А	80
● at 50 °C rated value	А	73
• at 60 °C rated value	А	66
Mechanical power output for three-phase motors		
• at 230 V		
— at standard circuit at 40 °C rated value	W	22 000
• at 400 V		
— at standard circuit at 40 °C rated value	W	45 000
Yielded mechanical performance [hp] for three-phase AC motor at 200/208 V at standard circuit at 50 °C rated value	hp	20
Operating frequency rated value	Hz	50 60
Relative negative tolerance of the operating frequency	%	-10
Relative positive tolerance of the operating frequency	%	10
Operating voltage at standard circuit rated value	V	200 480
Relative negative tolerance of the operating voltage at standard circuit	%	-15
Relative positive tolerance of the operating voltage at standard circuit	%	10
Minimum load [%]	%	20
Adjustable motor current for motor overload protection minimum rated value	A	43
Continuous operating current [% of le] at 40 °C	%	115
Power loss [W] at operating current at 40 °C during operation typical	W	12
Control electronics		
Type of voltage of the control supply voltage		AC/DC
Control supply voltage frequency 1 rated value	Hz	50
Control supply voltage frequency 2 rated value	Hz	60
Relative negative tolerance of the control supply voltage frequency	%	-10
Relative positive tolerance of the control supply voltage frequency	%	10
Control supply voltage 1 at AC		
• at 50 Hz rated value	V	24
• at 60 Hz rated value	V	24
Relative negative tolerance of the control supply voltage at AC at 60 Hz	%	-20
Relative positive tolerance of the control supply voltage at AC at 60 Hz	%	20
Control supply voltage 1 at DC rated value	V	24

Relative negative tolerance of the control supply voltage at DC	%	-20
Relative positive tolerance of the control supply voltage at DC	%	20
Display version for fault signal		red

Mechanical data		
Size of engine control device		S3
Width	mm	70
Height	mm	170
Depth	mm	190
Mounting type	-	screw and snap-on mounting
Mounting position		With additional fan: With vertical mounting surface +/- 90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back Without additional fan: With vertical mounting surface +/-10° rotatable, with vertical mounting surface +/- 10° t
Required spacing with side-by-side mounting	_	
• upwards	mm	60
• at the side	mm	30
• downwards	mm	40
Wire length maximum	m	300
Number of poles for main current circuit		3

Connections/Terminals		
Type of electrical connection		
<ul> <li>for main current circuit</li> </ul>	:	screw-type terminals
<ul> <li>for auxiliary and control current circuit</li> </ul>	:	screw-type terminals
Number of NC contacts for auxiliary contacts	(	0
Number of NO contacts for auxiliary contacts	1	2
Number of CO contacts for auxiliary contacts		1
Type of connectable conductor cross-sections for		
main contacts for box terminal using the front clamping point		
• solid	:	2x (2.5 16 mm²)
<ul> <li>finely stranded with core end processing</li> </ul>	:	2.5 35 mm²
• stranded	4	4 70 mm²
Type of connectable conductor cross-sections for main contacts for box terminal using the back clamping point		
• solid	:	2x (2.5 16 mm²)
<ul> <li>finely stranded with core end processing</li> </ul>	:	2.5 50 mm²
• stranded		10 70 mm²
Type of connectable conductor cross-sections for main contacts for box terminal using both clamping points		

~

• solid		2x (2.5 16 mm²)
<ul> <li>finely stranded with core end processing</li> </ul>		2x (2.5 35 mm²)
• stranded		2x (10 50 mm²)
Type of connectable conductor cross-sections at AWG conductors for main contacts for box terminal		
<ul> <li>using the back clamping point</li> </ul>		2x (10 1/0)
<ul> <li>using the front clamping point</li> </ul>		2x (10 1/0)
<ul> <li>using both clamping points</li> </ul>		10 2/0
Type of connectable conductor cross-sections for DIN cable lug for main contacts	-	
<ul> <li>finely stranded</li> </ul>		2 x (10 50 mm²)
• stranded		2x (10 70 mm²)
Type of connectable conductor cross-sections for auxiliary contacts	-	
• solid		2x (0.5 2.5 mm²)
<ul> <li>finely stranded with core end processing</li> </ul>		2x (0.5 1.5 mm²)
Type of connectable conductor cross-sections at AWG conductors	_	
• for main contacts		2x (7 1/0)
<ul> <li>for auxiliary contacts</li> </ul>		2x (20 14)
<ul> <li>for auxiliary contacts finely stranded with core end processing</li> </ul>		2x (20 16)
Ambient conditions		
Installation altitude at height above sea level	m	5 000
Environmental category		
<ul> <li>during transport acc. to IEC 60721</li> </ul>		3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
<ul> <li>during storage acc. to IEC 60721</li> </ul>		3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
<ul> <li>during operation acc. to IEC 60721</li> </ul>		3K6 (no formation of ice, no condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
Ambient temperature		
during operation	°C	-25 +60
	°C	-40 +80
<ul> <li>during storage</li> </ul>		
Ouring storage Derating temperature	°C	40

General Product	t Approval			EMC	For use in haz- ardous loca- tions
	(SA)		EHC	C-Tick	K ATEX
Declaration of Conformity	Test Certificates		Shipping App	roval	other
EG-Konf.	Special Test Certi- ficate	Type Test Certific- ates/Test Report	Llovd's Kegister LRS	PRS	Confirmation
Railway Vibration and Shock					

 UL/CSA ratings

 Yielded mechanical performance [hp] for three-phase
 AC motor
 Image: Colspan="2">Contact standard circuit at 50 °C rated value
 hp
 25


 • at 220/230 V
 - at standard circuit at 50 °C rated value
 hp
 25


 • at 460/480 V
 - at standard circuit at 50 °C rated value
 hp
 50


 Contact rating of auxiliary contacts according to UL
 Image: Colspan="2">Mathematical performance [hp] for three-phase

imulation Tool for Soft Starters (STS) ttps://support.industry.siemens.com/cs/ww/en/view/101494917	
formation- and Downloadcenter (Catalogs, Brochures,) ttp://www.siemens.com/industrial-controls/catalogs	
ndustry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW4046-1BB04	
ax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW4	046-1BB04
ervice&Support (Manuals, Certificates, Characteristics, FAQs,)	

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RW4046-1BB04&lang=en







last modified:

10/31/2018