

## Ring ratchet open-end spanner 8 mm x 8 mm (44638)



**wiha** 

Tools that work for you

Wiha Werkzeuge GmbH  
Obertalstraße 3-7 78136 Schonach  
E-Mail: info.de@wiha.com  
Tel.: +49 (0)7722 959-0

Order no.: 44638

Article number: 30308

EAN: 4010995446383

Customs tariff number: 82041100

Increases your efficiency: Fastening without interruption thanks to a finely toothed ring ratchet.  
Increases your efficiency: Improved accessibility in confined spaces thanks to 15° jaw positioning and double hex ring ratchet.

Application: For installation and mounting work.  
Eminently suitable for working in confined spaces.

Opening tightly fastened screws requires great force. With the leverage action from the Wiha ring ratchet open-end spanners, the user can easily open any fastening. The jaw end is also excellently suited for tightening screws and nuts. With 15° jaw positioning, the jaw end is perfect for working in confined spaces. Similarly, when working with the ring ratchet, the user benefits from the fine toothing with 72 teeth, offering a short return angle and highest comfort when working in confined spaces due to the double hex design. By simply turning around its own axis, it can be switched between right and left rotation. Made of high quality chrome vanadium steel, the ring ratchet open-end spanners are distinguished by their longevity and robustness, not the least thanks to their corrosion-resistant and easy to clean surface.

Based on DIN 3113

---

Customs tariff number	82041100
-----------------------	----------

---

Colour	silver
--------	--------

---

Blister packed	No
----------------	----

---

Combination wrench width	8 mm
--------------------------	------

---

Overall length (mm)	136 mm
---------------------	--------

---

VDE article	No
-------------	----

---

Country of origin (ISO 3166-1 Alpha 3)	TWN
--	-----

---

Gewicht VPE in Gramm	37
----------------------	----

---