


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5013340100**
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: 1.00mm Pitch Pico-Clasp Wire-to-Board Connector, Female Crimp Terminal, Tin Plating, 28-32 AWG, Bag

Documents:

3D Model	Product Specification PS-501940-001-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-501334-001-001 (PDF)
Product Specification PS-501331-001-001 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	Crimp Terminals
Series	501334
Application	Signal, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Pico-Clasp Wire-to-Board Connectors
Packaging Alternative	5013340000 (Reel)
Product Name	Pico-Clasp
UPC	822348531097

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	8.600/mg
Packaging Type	Bag
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.80mm max.
Wire Size AWG	28, 30, 32
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Engineering Number	NT501-6746
--------------------	------------

Reference - Drawing Numbers

Crimp Specification	CS-501193-001-001
Packaging Specification	SPK-501334-001-001
Product Specification	PS-501331-001-001, PS-501940-001-001
Sales Drawing	5013340000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

501334 Series

Use With

501330 Crimp Housing