battery type: Lithium Button Cell

battery size: CR2430

chemical system: Lithium Manganese Dioxide

Conditions

nominal voltage: 3.0 V

open circuit voltage: 3.0...3.4 V new battery

2.9...3.4 V after 1 year storage at 20°C

all measurements at 22 ± 2°C ambient

capacity

rated: 300 mAh discharge at 0.4mA constant current; 24hours/day

End Voltage (EV): 2.0V

minimum: 270 mAh discharge at 0.4mA constant current; 24hours/day

EV: 2.0V

Standard discharge time

minimum: 275 h at $3k\Omega$ load (for QC measurement)

EV: 2.0V

Discharge currents

standard: 0.4 mA


max. recommended current


under continuous discharge: 5 mA

max. recommended current

under pulse discharge: 23 mA

Discharge diagrams:






shelf life: 10 years under proper storage conditions (ta: ≤ 22°C; RH: 60 ± 15%)

operating temperature

range: - 20...60 °C

mechanical specifications:



リチウムバンテリー LITHIUM BATTERY CR 2430 3V





blister card dimensions: 56 x 71.5mm

weight: 6g (incl. battery)

nominal weight: 4.3 g

VN-WVNN.

ANSMANN Specifications for model:	CR2430 Lithium Button Cell blister package
data sheet no. / part no.	5020092
supplier no.	702572
author / date	TG / 03.12.2010