

3RB3016-1PB0 OVERLOAD RELAY 1...4 A

Technical / CAx data

Technical Data CAx data

As of 2012-01-30



OVERLOAD RELAY 1...4 A FOR MOTOR PROTECTION
SIZE S00, CLASS 10 CONTACTOR ASS. MAIN CIRCUIT:
SCREW CONN. AUX.CIRCUIT: SCREW CONN. MANUAL-
AUTOM.-RESET

General technical data:

product brand name	SIRIUS	
product designation	solid-state overload relay	
Protection class IP / on the front	IP20	
Insulation voltage / with degree of pollution 3 / rated value	V	690
Installation altitude / at a height over sea level / maximum	m	2,000
Ambient temperature		
• during storage	°C	-40...+80
• during transport	°C	-40...+80
• during operating	°C	-25...+60
Relative humidity		
• during operating phase	/ %	95
EMC immunity to interference		
• according to IEC 60947-1	corresponds to degree of severity 3	
EMC emitted interference		
• according to IEC 60947-1	CISPR 11, environment B (residential area)	
Conductor-bound parasitic coupling BURST		
• according to IEC 61000-4-4	2 kV (power ports), 1 kV (signal ports) corresponds to degree of severity 3	
Conductor-bound parasitic coupling conductor-earth SURGE		
• according to IEC 61000-4-5	2 kV (line to earth) corresponds to degree of severity 3	
Conductor-bound parasitic coupling conductor-conductor SURGE		
• according to IEC 61000-4-5	1 kV (line to line) corresponds to degree of	

Electrostatic discharge	severity 3	
<ul style="list-style-type: none"> according to IEC 61000-4-2 	6 kV contact discharge / 8 kV air discharge	
Field-bound parasitic coupling	10 V/m	
<ul style="list-style-type: none"> according to IEC 61000-4-3 	15g / 11 ms	
Resistance against shock		
Impulse voltage resistance / rated value	kV	6
Active power loss / total / typical	W	0.05
Item designation	F	
<ul style="list-style-type: none"> according to DIN 40719 extendable after IEC 204-2 / according to IEC 750 according to DIN EN 61346-2 	F	
Size of overload relay	S00	
Size of the contactor / can be combined / company-specific	S00	
type of protection	PTB 09 ATEX 3001 Ex II (2) GD	
Type of assignement	2	
Trip class	CLASS 10	

Main circuit:

Number of poles / for main current circuit	3	
Operating voltage / at AC-3 / rated value	690	
<ul style="list-style-type: none"> maximum 	V	690
Operating current / at AC-3 / at 400 V	4	
<ul style="list-style-type: none"> rated value 	A	4
Adjustable response current	1...4	
<ul style="list-style-type: none"> of the current-dependent overload release 	A	1...4
Service power / for three-phase servomotors / at 400 V / at 50 Hz	0.55...1.5	
<ul style="list-style-type: none"> for AC three-phase 	kW	0.55...1.5
Operating current / of the fuse link	20	
<ul style="list-style-type: none"> rated value 	A	20

Auxiliary circuit:

Contact reliability / of the auxiliary contacts	acceptability for PLC control (17 V, 5 mA)	
Number of NC contacts / for auxiliary contacts	1	
Number of NO contacts / for auxiliary contacts	1	
Number of change-over switches / for auxiliary contacts	0	
Operating current / of the auxiliary contacts		
<ul style="list-style-type: none"> at AC-15 at 24 V at 110 V at 120 V at 125 V at 230 V at DC-13 at 24 V at 60 V at 110 V at 125 V at 220 V 	A	4
	A	4
	A	4
	A	4
	A	3
	A	2
	A	1
	A	0.3
	A	0.3
	A	1

Short-circuit:

Design of the fuse link / for short-circuit protection of the auxiliary switch / required	fuse gL/gG: 6 A	
--	-----------------	--

Installation/mounting/dimensions:

Built in orientation	any	
Type of mounting	direct mounting	

Width	mm	45
Height	mm	64.7
Depth	mm	72.5
Distance, to be maintained, to the ranks assembly		
• forwards	mm	0
• backwards	mm	0
• upwards	mm	0
• downwards	mm	0
• sideways	mm	0
Distance, to be maintained, to earthed part		
• forwards	mm	0
• backwards	mm	0
• upwards	mm	0
• downwards	mm	0
• sideways	mm	6
Distance, to be maintained, conductive elements		
• forwards	mm	0
• backwards	mm	0
• upwards	mm	0
• downwards	mm	0
• sideways	mm	6

Connections:

Design of the electrical connection	
• for main current circuit	screw-type terminals
• for auxiliary and control current circuit	screw-type terminals
Product function / removable terminal for auxiliary and control circuit	Yes
Type of the connectable conductor cross-section	
• for main contacts	
• solid	1x (0.5 ... 4 mm ²), 2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 4 mm ²)
• stranded	1x (0.5 ... 1.5 mm ²), 2x (0.5 ... 1.5 mm ²), 1x (0.75 ... 4 mm ²), 2x (0.75 ... 4 mm ²)
• finely stranded	
• with conductor end processing	1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 2.5 mm ²)
• for AWG conductors / for main contacts	1x (20 ... 12), 2x (20 ... 12)
• for auxiliary contacts	
• solid	1x (0.5 ... 4 mm ²), 2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
• finely stranded	
• with conductor end processing	1x (0.5 ... 1.5 mm ²), 2x (0.5 ... 1.5 mm ²), 1x (0.5 ... 2.5 mm ²)
• for AWG conductors / for auxiliary contacts	1x (20 ... 14), 2x (20 ... 14)

Certificates/approvals:

Verification of suitability	UL / CSA
• ATEX	Yes

General Product Approval

<input checked="" type="checkbox"/> CQC	<input checked="" type="checkbox"/> CSA	ROSTEST
---	---	---------

Shipping Approval

<input checked="" type="checkbox"/> ABS (American Bureau of Shipping)	<input checked="" type="checkbox"/> GL (Germanischer Lloyd)	<input checked="" type="checkbox"/> LRS (Lloyds Register of Shipping)
---	---	---

UL/CSA ratings:

Contact rating designation / for auxiliary contacts / according to UL

B600 / R300

Reliability figures:

Protection against electrical shock

finger-safe

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:


<http://www.siemens.com/cax>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RB3016-1PB0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RB3016-1PB0





last change:

Jan 30, 2012