Data Sheet

Within Series Adaptor 53_BNC-75-0-1/133_N



Description

L-adaptor plug/jack BNC plug (male) / BNC jack (female)

Interface standard

Series BNC - Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120

OD.

Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 75~\Omega \\ \text{Interface frequency max.} & 1~\text{GHz} \end{array}$

Mechanical Data

Number of matings 500

Weight 0.0154 kg

Environmental Data

Operating temperature -65 °C to 165 °C 2011/65/EU (RoHS) compliant

Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DCA-00013460

Ordering Information

Single package 53_BNC-75-0-1/133_NE

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.