SIEMENS

Product data sheet

3RV2011-0GA10



CIRCUIT-BREAKER SZ S00, FOR MOTOR PROTECTION, CLASS 10, A-REL. 0.45...0.63A, N-RELEASE8.2A SCREW CONNECTION, STANDARD SW. CAPACITY

General technical data:		
product brand name		SIRIUS
product designation		3RV2 circuit breaker
Size of the circuit-breaker		S00
Trip class		CLASS 10
Protection class IP / on the front		IP20
Degree of pollution		3
Installation altitude / at a height over sea level / maximum	m	2,000
Ambient temperature		
during storage	°C	-50 +80
during operating	°C	-20 +60
during transport	°C	-50 +80
Resistance against shock		25g / 11 ms
Impulse voltage resistance / rated value	kV	6
Insulation voltage / rated value	V	690
Active power loss / total / typical	W	5
Item designation		
 according to DIN 40719 extendable after IEC 204-2 / according to IEC 750 		F
according to DIN EN 61346-2		F

Mechanical operating cycles as operating time	_	
of the main contacts / typical		100,000
of the auxiliary contacts / typical		100,000
Type of the driving mechanism / motor drive		No
Design of the operating mechanism		selector switch
Product function		
overload protection		Yes
phase disturbance recognition		Yes
Product component		
auxiliary switch		No
 undervoltage release mechanism 		No
trip indicator		No
Product extension / optional / motor drive		No
Main circuit:		
Number of poles / for main current circuit		3
Operating voltage / at AC-3 / rated value / maximum	V	690
Operating current / at AC-3 / at 400 V / rated value	А	0.6
Service power / at AC-3		
• at 400 V / rated value	W	180
• at 500 V / rated value	W	180
• at 690 V / rated value	W	250
Frequency of operation / at AC-3 / according to IEC 60947-6-2 / maximum	1/h	15
Arrangement of electrical connectors / for main current circuit		Top and bottom
Adjustable response current		
 of the non-delayed short-circuit release 	А	8.2 8.2
of the current-dependent overload release	А	0.45 0.63
Service power / at AC-3 / at 230 V / rated value	W	90
Continuous current / rated value	А	0.63
Auxiliary circuit:		
Product extension / auxiliary switch		Yes
Number of NC contacts / for auxiliary contacts / instantaneous switching		0
Number of NO contacts / for auxiliary contacts / instantaneous switching		0
Number of change-over switches / for auxiliary contacts		0
Inputs/ Outputs:		
Number of digital inputs		0

Short-circuit:				
Breaking capacity limit short-circuit current (lcu)				
• at 400 V / rated value	А	100,000		
• at 500 V / rated value	А	100,000		
• at 690 V / rated value	А	100,000		
Design of the overcurrent release and short-circuit release		thermomagnetic		
Installation/mounting/dimensions:				
Built in orientation		any		
Type of mounting		screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715		
Width	mm	45		
Height	mm	97		
Depth	mm	91		
Distance, to be maintained, to the ranks assembly				
forwards	mm	0		
backwards	mm	0		
• upwards	mm	50		
downwards	mm	50		
• sidewards	mm	0		
Distance, to be maintained, to earthed part				
forwards	mm	0		
backwards	mm	0		
• upwards	mm	50		
• sidewards	mm	30		
• downwards	mm	50		
Distance, to be maintained, conductive elements				
• forwards	mm	0		
backwards	mm	0		
• upwards	mm	50		
downwards	mm	50		
• sidewards	mm	30		
Connections:				
Product function				
removable terminal for main circuit		No		
removable terminal for auxiliary and control circuit		No		
Design of the electrical connection				
• for main current circuit		screw-type terminals		
Type of the connectable conductor cross-section				
for main contacts				

• solid				2x (0.75	5 2.5 mm²), 2x 4 r	mm²
 finely stran 	ded					
 with con 	ductor end processing			2x (0.5	1.5 mm²), 2x (0.7	′5 2.5 mm²)
 for AWG cond 	luctors / for main contacts			2x (18 .	14), 2x 12	
Certificates/ap	orovals:					
Verification of su	itability			CE / UL	. / CSA	
• für Staubexplo	osionsschutz für Zone 21/2	2		no		
 for gas explos 	ion protection for zone 1/2			no		
General Produc	t Approval				For use in hazard	dous locations
	(SFA	GOST			KEx ATEX	
Test Certificate	S					
other	Special Test Certificate	<u>Type Test</u> Certificates/Test Report				
Shipping Appro	oval					
ABS	GL	Lloyd's Kegister Lrs	PRS		RINA	RMRS
other						
	Declaration of Conformity	other				

Safety:			
B10 value / with high demand rate			
according to SN 31920		50,000	
T1 value / for proof test interval or service life			
according to IEC 61508	а	10	
Failure rate (FIT value) / with low demand rate			
according to SN 31920	FIT	50	
Proportion of dangerous failures			
with low demand rate / according to SN 31920	%	40	
with high demand rate / according to SN 31920	%	40	
Protection against electrical shock		finger-safe	
		, , , , , , , , , , , , , , , , , , ,	

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)

http://www.siemens.com/industrial-controls/mall


CAx-Online-Generator


http://www.siemens.com/cax


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

http://support.automation.siemens.com/WW/view/en/3RV2011-0GA10/all

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RV2011-0GA10







last change:

Mar 27, 2012