SIEMENS

Product data sheet 3SB3801-0DF3



ENCLOSURE FOR COMMAND DEVICES, 22MM, ROUND, ENCLOSURE MATERIAL PLASTIC, YELLOW ENCLOSURE TOP PART, WITH PROTECTIVE COLLAR, 1 COMMAND POINT, A=EM. STOP MUSHROOM PUSHB. RED, 40MM, ROTATE-TO-UNLATCH, 1NC, SCREW TERMINAL, FLOOR MOUNTING, TOP AND BOTTOM 1 X M20 EACH

Enclosure for command and signaling devices with standard equipment
plastic
yellow
1
Yes
Square
Cable routing above, below / left, right, each 1 x M20
Vertical / horizontal
Yes

Actuator / signaling device:			
Design of the operating mechanism	Emergency stop mushroom pushbutton		
Assembling of the commanding and signaling device	A = Emergency stop mushroom pushbutton		
Number of mushroom pushbuttons	1		
Number of indicator lights	0		
Number of pushbuttons	0		
Number of key-operated switches	0		
Material / of the activation element	plastic		
Product component / front ring	No		

Type of unlocking device		rotate-to-unlatch mechanism			
Holder:					
Material / of the holder		Plastic			
Contact block / lampholder					
Number of switching elements		1			
Number of NC contacts / for auxiliary contacts		1			
Number of NO contacts / for auxiliary contacts Number of NO contacts / for auxiliary contacts					
<u> </u>		0			
Number of change-over switches / for auxiliary contacts		0 Von			
Product function / positive opening		Yes			
Number of lampholders		0			
Type of fixing/fixation / for contact blocks		Floor mounting			
Design of electrical connection / of contact blocks, socket, and accessories		Screw-type terminal			
Product component / fluorescent materials		No			
Product extension / optional / fluorescent materials		No			
Accessories:					
Number of backing plates		0			
Number of labeling plates		0			
Product component / holder for 3 switching elements		No			
Product component / holder for 3 switching elements General technical details:		No			
		No AC/DC			
General technical details:					
General technical details: Type of voltage / of the operating voltage					
General technical details: Type of voltage / of the operating voltage Operating voltage	V				
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC	V	AC/DC			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value		AC/DC 5 230			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value		AC/DC 5 230			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC	V	AC/DC 5 230 230			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value	V	AC/DC 5 230 230 5 400			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value	V	AC/DC 5 230 230 5 400			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value • at 60 Hz / at AC	V V V	AC/DC 5 230 230 5 400 400			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value • at 60 Hz / at AC • rated value	V V V	AC/DC 5 230 230 5 400 400 5 300			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value • at 60 Hz / at AC • rated value • 1 / at 60 Hz / for AC / rated value	V V V	AC/DC 5 230 230 5 400 400 5 300			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value • at 60 Hz / at AC • rated value • 1 / at 60 Hz / for AC / rated value Operating current	V V V	AC/DC 5 230 230 5 400 400 5 300			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value • at 60 Hz / at AC • rated value • 1 / at 60 Hz / for AC / rated value Operating current • at AC-12	V V V	AC/DC 5 230 230 5 400 400 5 300 300			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value • at 60 Hz / at AC • rated value • 1 / at 60 Hz / for AC / rated value Operating current • at AC-12 • at 24 V / rated value	V V V V	AC/DC 5 230 230 5 400 400 5 300 300			
General technical details: Type of voltage / of the operating voltage Operating voltage • for DC • rated value • 1 / for DC / rated value • at 50 Hz / at AC • rated value • 1 / at 50 Hz / for AC / rated value • at 60 Hz / at AC • rated value • 1 / at 60 Hz / for AC / rated value Operating current • at AC-12 • at 24 V / rated value • at 48 V / rated value	V V V V	AC/DC 5 230 230 5 400 400 5 300 300			

• at AC-15		
• at 24 V / rated value	Α	6
• at 48 V / rated value	Α	6
• at 110 V / rated value	Α	6
• at 230 V / rated value	Α	6
• at 400 V / rated value	А	3
• at DC-12		
• at 24 V / rated value	Α	10
• at 48 V / rated value	Α	5
• at 110 V / rated value	Α	2.5
• at 230 V / rated value	Α	1
• at DC-13		
• at 24 V / rated value	Α	3
• at 48 V / rated value	Α	1.5
• at 110 V / rated value	Α	0.7
• at 230 V / rated value	Α	0.3
Delivery state / pre-wired on strip terminal		No
Product component / stand/pedestal		No
Resistance against shock		
 for devices without incandescent lamp / according to IEC 60068- 2-27 		<= 50g
Resistance against vibration / according to IEC 60068-2-6		20 200 Hz: 5g
Item designation		
according to DIN EN 61346-2		S
according to DIN 40719 extendable after IEC 204-2 / according		S
to IEC 750		
	N∙m	1
to IEC 750	N⋅m	1
to IEC 750 Tightening torque / of the screws in the bracket / maximum	N·m °C	1 -25 +70
to IEC 750 Tightening torque / of the screws in the bracket / maximum Ambient temperature		
to IEC 750 Tightening torque / of the screws in the bracket / maximum Ambient temperature • during operating	°C	-25 + 70
to IEC 750 Tightening torque / of the screws in the bracket / maximum Ambient temperature • during operating • during storage	°C	-25 +70 -40 +80
to IEC 750 Tightening torque / of the screws in the bracket / maximum Ambient temperature • during operating • during storage Protection class IP	°C	-25 +70 -40 +80 IP65
to IEC 750 Tightening torque / of the screws in the bracket / maximum Ambient temperature • during operating • during storage Protection class IP B10 value / with high demand rate / according to SN 31920 Proportion of dangerous failures / with high demand rate /	°C	-25 +70 -40 +80 IP65 100,000
to IEC 750 Tightening torque / of the screws in the bracket / maximum Ambient temperature • during operating • during storage Protection class IP B10 value / with high demand rate / according to SN 31920 Proportion of dangerous failures / with high demand rate / according to SN 31920 Proportion of dangerous failures / with low demand rate /	°C °C 	-25 +70 -40 +80 IP65 100,000
Tightening torque / of the screws in the bracket / maximum Ambient temperature • during operating • during storage Protection class IP B10 value / with high demand rate / according to SN 31920 Proportion of dangerous failures / with high demand rate / according to SN 31920 Proportion of dangerous failures / with low demand rate / according to SN 31920 Failure rate (FIT value) / with low demand rate / according to SN	°C °C %	-25 +70 -40 +80 IP65 100,000 20

Shape / of the installation hole		round
Mounting diameter	mm	22
Width	mm	85
Height	mm	85
Depth	mm	106

Certificates/approvals:

General Product Approval

Declaration of Conformity

Test Certificates









Special Test Certificate

Shipping Approval









otherConfirmation

Environmental Confirmations

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)

http://www.siemens.com/industrial-controls/mall

Cax online generator:


http://www.siemens.com/cax


 ${\bf Service \& Support~(Manuals,~Certificates,~Characteristics,~FAQs,...)}$

http://support.automation.siemens.com/WW/view/en/3SB3801-0DF3/all

 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ ...)$

 $\underline{\text{http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3801-0DF3}$





last change:

Feb 8, 2013