Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk JUMO Process Control, Inc.

6733 Myers Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com



Data Sheet 602090

Page 1/9

JUMO heatTHERM P300

3-Phase Panel-Mounted Thermostat

Special features

- · Safety temperature limiter (STB) and temperature limiter (TB)
- Max. switching capacity 30 A, AC 480 V
- · Different electrical connections are available
- · Trip-free function
- · Capillary break protection

Brief description

Three-phase thermostats operate according to the principle of thermal expansion.

Thermostats control and monitor thermal processes.

The JUMO heatTHERM P300 is available as a safety temperature limiter (STB) and temperature limiter (TB).

In the event of a malfunction, the STB will set the system being monitored to a safe operating status.



Type 602090, standard

Switching functions

Safety temperature limiter (STB)

If the temperature at the temperature probe exceeds the configured setpoint value, hen the switching mechanics are actuated, the electrical circuit is opened, and the mechanism is mechanically locked.

The unlocking difference denotes the difference between the limit value temperature and the earliest possible unlocking temperature.

The electrical circuit NC opens if the probe cools down into the negative temperature range. The mechanism must be manually unlocked once the temperature rises again.

If the measuring system is destroyed, i. e., if the expansion medium emerges, the pressure in the membrane drops and permanently opens the electrical circuit. It is no longer possible to unlock the mechanism.

With the trip-free function, the temperature switch-off at the limit value – through constant pressing of the reset button – is **not** disabled. With the heatTHERM P300 the contacts are opened (raised) through constant pressing of the reset button.

Temperature limiter (TB)

If the temperature at the temperature probe exceeds the configured setpoint value, hen the switching mechanics are actuated, the electrical circuit is opened, and the mechanism is mechanically locked.

The NC circuit does not open:

- when the sensor cools down into the negative temperature range
- · in case of a capillary break



Type 602090, central mounting M10 × 1 with acorn nut

Approvals and approval marks (see "Technical data")







Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net

Internet: www.jumousa.com



Data Sheet 602090

Page 2/9

Technical data

General Information

Limit value setting	Permanently set	(upward adjustment)						
Capillary	Capillary diameter 1.25 mm Min. bending radius of capillary 5 mm							
Material	Stainless steel (CrNi) Copper (Cu)							
Length	Variable (200 to 5000 mm)							
Temperature probe	Temperature proquest)	Temperature probe diameter: 4 and 6 mm (other temperature probe diameters available upon request)						
Material	Stainless steel (C Copper (Cu)	Stainless steel (CrNi) Copper (Cu)						
	(The temperature	e probe diameter and probe len	gth depend on the c	ontrol range)				
Process connection	See data sheet 6	606710 (standard: plain cylindric	al probe "10")					
Switching point accuracy Type 602090/080	Part no.	Limit value in °C with indication of tolerance	Capillary mm	Probe diameter (d) × L mm				
	60003431	95 (-12)	700	(6) × 85				
	60003432	110 (-15)						
	60003433	360 (-30)		(4) × 85				
		int accuracy is based on the prolue has been undershot by the d						
Max. probe temperature	15% or at least 2	15% or at least 25 K of the limit value						
Average ambient temperature influence	When the ambient temperature on the switching head and/or the capillary deviates from the calibration ambient temperature of 22 °C, a switching point offset occurs. Higher ambient temperature = lower switching point Lower ambient temperature = higher switching point							
Protection type	IP00 according to	DIN EN 60529						
Material of insulating tube	PVC up to 95 °C,							
	others upon request							
Upper part of the housing	Steel sheet, zince	Steel sheet, zinc-plated						
Switching socket	Ceramic							
Fastening	2 M4 screws, spa	acing 28 mm						

Capillary and temperature probe

Rated position (NL)

Protection conductor grounding

Weight

Temperature	Capillary		Temperature probe
Up to 200 °C	Copper (Cu)	Diameter 1.25 mm	Copper (Cu)
Up to 350 °C			Stainless steel (CrNi)
Up to 365 °C (optional)	Stainless steel (CrNi)		

Approx. 200 g, depending on version

Tab connector connection (standard), Screw connection (optional extra code),

Fixing bracket (standard),

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net www.jumo.net Internet:

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860

Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 602090

Electrical data

	Switching capacity AC 40 to 480 V	Overvoltage category	Max. ambient temperature on switching head	Electrical connection	Switching function
Normally closed contact (NC)	0.5 to 20 A $(3.3 \text{ A})^a$ cos ϕ = 1 (0.6)	III	125 °C	Tab connector 6.3 mm	3-pole with 1-pole
	0.5 to 30 A $(5.0 \text{ A})^a$ cos $\varphi = 1 (0.6)$		80 °C	(standard)	normally open contact (NO)
	0.5 to 20 A $(3.3 \text{ A})^a$ cos $\varphi = 1 (0.6)$	_	125 °C	Tab connector 6.3 mm	3-pole without normally open
	0.5 to 30 A $(5.0 \text{ A})^a$ cos $\varphi = 1 (0.6)$	-	80 °C	(standard) with plug adapter up to 4 mm²	contact (NO)
	0.5 to 16 A $(2.6 \text{ A})^a$ cos $\varphi = 1 (0.6)$		125 °C	Screw connection up to 2.5 mm²	
Normally open contact (NO)	0.5 to 2 A $(0.3 \text{ A})^a$ cos $\varphi = 1 (0.6)$	-	-	-	-
Normally closed contact (NC)	(1) 21 31 12 22 32		Normally closed contact (NC) with 1-pole normally open contact (NO)	[] I	31
Min. contact capability	Type of contact	AC/DC	per switching path		
for switching reliability	Silver contact	24 V	0.1 A		
	Gold contact	10 V	0.005 A	-	
Frequency	48 to 63 Hz				
Mode of operation STB	2BFHKLN	With trip-free function			
	2BFKLN	Without trip-free	function		
Pollution degree	2	According to DI	N EN 60730-1		
Protection rating	I				

a Inductive load

Environmental influences

Max. admissible ambient temperature	For transport and storage -30 to +125 °C	
Time constant to 632	< 45 s. measured in water bath < 60 s. measured in oil bath	< 120 s. measured in air

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net www.jumo.net Internet:

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net

Internet: www.jumousa.com



Data Sheet 602090

Approvals and approval marks

VDE	
Testing agency	VDE Offenbach (Germany)
Certificate/certification numbers	40050653
Inspection basis	DIN EN 60730-1, DIN EN 60730-2-9
	The product also fullfills the requirements according to IEC 60730-1.
Valid for	Type 602090/080
UL	
Testing agency	UL Germany
Certificate/certification numbers	E66358
Inspection basis	UL 60730-1, UL 60730-2-9, CAN/CSA E60730-1, CSA E60730-2-9
Valid for	Type 602090/080
EAC ^a	
Testing agency	-
Certificate/certification numbers	0198420
Inspection basis	TR ZU 004/2011 (LVD)
Valid for	Type 602090/080

a Russian documentation upon request

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-6607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33

Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk JUMO Process Control, Inc. 6733 Myers Road

East Syracuse, NY 13057, USA


Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com




Data Sheet 602090

Page 5/9

Dimensions





Electrical connection: tab connector 6.3 mm (standard)

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway

Harlow, Essex, CM20 2DY, UK
Phone: +44 1279 63 55 33
Fax: +44 1279 62 50 29
Email: sales@jumo.co.uk
Internet: www.jumo.co.uk

JUMO Process Control, Inc.


6733 Myers Road

East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 602090


Page 6/9



Electrical connection: screw connection up to 2.5 mm²

3-pole normally closed contact (NC) with plug adapter

Recommended: • for easy cable assembly



Electrical connection: plug adapter up to 4 mm²

The plug adapter is available as an extra code or as an accessory with the part no. 00689177 (2 pieces are required for each device).

JUMO GmbH & Co. KG Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany 36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.


JUMO Instrument Co. Ltd. JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 602090



Electrical connection: tab connector 6.3 mm (standard)

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: +49 661 6003-607 Fax: Email: mail@jumo.net Internet: www.jumo.net

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 +44 1279 62 50 29

Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 602090

Order details

	(1)	Basic type
602090	. ,	JUMO heatTHERM P300 – 3-phase panel-mounted thermostat
	(2)	Basic type extension
007		Temperature limiter (TB), permanently set
080		Safety temperature limiter (STB), permanently set
	(3)	Contact combinations – normally closed contact (NC) and normally open contact (NO)
030		3-pole normally closed contact (NC), without normally open contact (NO)
031		3-pole normally closed contact (NC), with 1 normally open contact (NO)
	(4)	Control range
60		60 °C
365		365 °C
	(5)	Limit value
000		None
	(6)	Switching differential
700		700 mm
1000		1000 mm
		Special length upon request
	(7)	Capillary length
20		CrNi (stainless steel)
40		Cu (copper)
	(8)	Capillary insulating tube length
0		0
170		170 mm
		Special length, specifications in plain text
	(9)	Capillary insulating tube material
00		None
70		PTFE
86		PVC
	(10)	Process connection
10		Plain cylindrical probe
67		Sealing gland M9, nickel-plated brass
69		Sealing gland M14, nickel-plated brass
	(11)	Temperature probe diameter
4		4 mm
6		6 mm
	(12)	Temperature probe material
20		CrNi (stainless steel)
40		Cu (copper)
	(13)	Extra codes
000		None
699		Screw connection up to 2.5 mm ²
710		Central mounting M10 × 1
964		Plug adapter up to 4 mm²
972		Probe und capillary welded

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany 36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: +49 661 6003-607 Fax: Email: mail@jumo.net www.jumo.net Internet:

JUMO Instrument Co. Ltd.

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29

Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6733 Myers Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 602090

	(1)		(2)		(3)		(4)		(5)		(6)		(7)	
Order code		/		-		-		-		-		-		-
Order example	602090	/	080	-	031	-	365	-	000	-	700	-	0	-
			(8)		(9)		(10)		(11)		(12)		(13)	
				-		-		-		-		/		а
			120	_	86	_	10	_	4	_	20	/	972	-

^a List extra codes in sequence and separate using commas.

Stock versions

Order code	Limit value, STB	Capillary length, STB	Process- connection	Part no.
602090/080-031-000-95-000-0-700-20-170-86-10-0-6-20/972	95 °C	700 mm	Plain cylindri- cal probe	60003431
602090/080-031-000-110-000-0-700-20-170-86-10-0-6-20/972	110 °C	700 mm	Plain cylindri- cal probe	60003432
602090/080-031-000-360-000-0-700-20-170-86-10-0-4-20/972	360 °C	700 mm	Plain cylindri- cal probe	60003433