

Features

- Nylon tyres
- Threaded stem
- 20 x 42mm wheels
- Light duty – 50kg
- Levelling castors

RS PRO 42mm Swivel Castor Wheels, 50kg

RS Stock No.: 611-4408



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A 42mm diameter multifunction wheels with levelling castors. They are versatile and are an ideal choice for equipment that needs to be mobile, but when in place is completely firm and stationary.

General Specifications

Rotation	Braked Swivel; Fixed; Swivel
Weight Class	Extra Heavy Duty; Heavy Duty; High Load Capacity
Load Capacity	240kg, 1000lb
Load Capacity / 4pcs	1000kg
Tyre Material	Rubber; Thermoplastic; Polyurethane
Hub Material	Rubber; Cast Iron; Polyurethane
Bracket Material	Pressed Steel
Includes Brake	No; Yes
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Vending machines, Medical appliances, Workstations, Measuring Instruments

Mechanical Specifications

Mounting Type	Threaded Stem
Wheel Diameter	42mm
Wheel / Tread Width	20mm
Overall Height	71mm
Number of Fixing Holes	1
Fixing Hole Size	M8
Hub Bearing Type	None
Thread Size	M8
Stem Size	M8 x 15mm
Hardness of Wheel	70 Shore D
Levelling Extent	10mm

Operation Environment Specifications

Operating Temperature	-10°C to 90°C
-----------------------	---------------

