



ENGLISH

Datasheet

## RS Pro Black Rubber Tyred Wheel ART116A 200MM, 400kg

RS Stock No: **621-9569**



### Product Details

RS Pro rubber castor wheel ART116A in black colour, has diameter of 200 mm and load capacity of 400 kg. It features elastic rubber tyre for non-marking floor surface.

### Features and Benefits

- Solid black rubber tyre, hardness shore 68A
- Excellent smooth and noiseless running
- High resistance to abrasion
- Temperature range: -20 to +70°C

**Specifications:**

Bore Diameter	20 mm
Bore Length	60 mm
Colour	Black
Features	Abrasion Resistant, Quiet Operation
Hub Bearing Type	Ball Bearing
Hub Diameter	60 mm
Hub Material	Aluminium
Load Capacity	400 kg
Tyre Material	Rubber
Tyre Type	Solid
Wheel Diameter	200 mm
Wheel Width	50 mm