

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0643201311**  
**Status:** **Active**  
**Overview:** CMC and CMX Sealed, Hybrid, Modular Connectors  
**Description:** .635mm, 1.50mm, CMC Receptacle, 48 Circuits, Left Wire Output, Black Coding, Mat Sealed

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-98420-002-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-98420-002-CH-001 (PDF)</a>
<a href="#">Product Specification PS-64319-001-001 (PDF)</a>	<a href="#">Application Specification AS-98420-002-FR-001 (PDF)</a>
<a href="#">Application Specification AS-64319-002-001 (PDF)</a>	<a href="#">Application Specification AS-98420-002-SP-001 (PDF)</a>
<a href="#">Application Specification AS-64319-002-CH-001 (PDF)</a>	<a href="#">Packaging Specification PK-64320-001-001 (PDF)</a>
<a href="#">Application Specification AS-64319-002-FR-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-64319-002-SP-001 (PDF)</a>	

**Application tooling part link**

Application Tooling Part Link	63812-1100
Application Tooling Part Link	63824-1200

**General**

Product Family	Crimp Housings
Series	<u>64320</u>
Application	Automotive, Power, Wire-to-Board
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm <sup>2</sup> wire) and 12.0A for 1.50mm Terminal (2.00mm <sup>2</sup> wire), Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm <sup>2</sup> wire) and 12.0A for 1.50mm Terminal (2.00mm <sup>2</sup> wire)

More Detailed Tech Information

Overview	<a href="#">Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses</a>
Product Name	<a href="#">CMC and CMX Sealed, Hybrid, Modular Connectors</a>
UPC	CMC 883906129781

**Physical**

Circuits (maximum)	48
Circuits Detail	8 x 1.5mm & 40 x 0.635mm terminals
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	35.400/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No



Series image - Reference only

**EU ELV**  
**Compliant**

**EU RoHS**  
**Compliant**  
**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**  
**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[64320 Series](#)

**Mates With**

[5007620481](#) 48-Circuit CMC Header, [36638](#) CMC Header

**Use With**

CMC CP Female Terminal [64322](#) , [64323](#).  
Circuit Way Plugs [643251010](#) , [643251023](#).  
CMC Wire Cap [643201301](#). CMC 48 Circuit Header [5007620481](#) , [36638](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Continuity Test Pen Assembly	<a href="#">638121100</a>
Unlocking Tool for CMC and	<a href="#">638241200</a>

Pitch - Mating Interface 2.54mm, 3.70mm  
Polarized to Mating Part Yes  
Stackable No  
Temperature Range - Operating -40° to +125°C

CMX Receptacle  
Connector

**Electrical**

Current - Maximum per Contact 12.0A, 6.0A

**Solder Process Data**

Lead-free Process Capability N/A

**Material Info**

**Reference - Drawing Numbers**

Application Specification AS-64319-002-001, AS-64319-002-CH-001,  
AS-64319-002-FR-001, AS-64319-002-SP-001,  
AS-98420-002-001, AS-98420-002-CH-001,  
AS-98420-002-FR-001, AS-98420-002-SP-001

Packaging Specification PK-64320-001-001

Product Specification PS-64319-001-001

Sales Drawing SD-64320-001-001

This document was generated on 09/18/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**