

COAXIAL TERMINATION, 50 Ohm, PC 2.4, plug (male)

6500_PC24-50-1/199_N

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power



Product configuration		
Interface	Gender	Standard
PC 2.4	plug (male)	

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 50 GHz
VSWR	1.2
Return loss	20.8 dB

Electrical Data (power)	
Average power	2 W at 25 °C ambient temperature. Linearly derated to 0.3 W at 100 °C ambient temperature.
Peak power	100 W, 5 μs pulse width, 1 % duty cycle

Interface and material data		
Interface	PC 2.4 / plug (male)	
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating
Outer conductor	Stainless Steel	Passivated (Plating)
Coupling nut	Stainless Steel	Passivated (Plating)
Piece parts	Material	Plating

Mechanical data	
Weight	0.005 kg

COAXIAL TERMINATION, 50 Ohm, PC 2.4, plug (male)

6500_PC24-50-1/199_N

Environmental data	
Operation temperature	-55 °C ... 100 °C

Ordering Information Table	
Item number	Item description
85218439	6500_PC24-50-1/199_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1738 / Date of publication: 28.11.2023 / uncontrolled copy