

Mod. 4820HL.B


4820HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE

Medium size watertight case, injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Ideal container for travel gear, photographic and video equipment, valuables, outdoor equipment and more.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available



METRIC MM-KG-C°



INTERNAL DIMENSIONS

L LENGTH	480 mm
W WIDTH	370 mm
D DEPTH	205 mm
LID	50 mm
BASE	155 mm


EXTERNAL DIMENSIONS

L LENGTH	520 mm
W WIDTH	440 mm
D DEPTH	230 mm

OTHER DATA

WEIGHT EMPTY	3.33 Kg
WEIGHT WITH FOAM	4.09 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	36.40 lt
BUOYANCY	24.80 Kg/max
OPERATING TEMPERATURE	°C min -33 / max +90

IMPERIAL IN-LBS-F°


INTERNAL DIMENSIONS

L LENGTH	18 7/8 in
W WIDTH	14 9/16 in
D DEPTH	8 1/16 in
LID	1 15/16 in
BASE	6 1/8 in

EXTERNAL DIMENSIONS

L LENGTH	20 1/2 in
W WIDTH	17 5/16 in
D DEPTH	9 1/16 in

OTHER DATA

WEIGHT EMPTY	7.34 lbs
WEIGHT WITH FOAM	9.01 lbs
WEIGHT WITH CUSTOM FOAM	lbs
VOLUME	9.61 gal
BUOYANCY	54.67 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max +194