battery type: Zinc-Air button cell (hearing aid battery)

battery size: A13; PR48 Zinc - Air / Zn-O<sub>2</sub> chemical system:

**Conditions** 

nominal voltage: 1.45 V

open circuit voltage: 1.35...1.45 V new battery (pull off tap min. 30 minutes before measurement)

1.35...1.45 V after 1 year storage at 20°C

capacity all measurements at 22 ± 2°C ambient

discharge at 1.5kΩ load; discharge 24hours/day typical: 310 mAh

End Voltage (EV): 0.9V

minimum: 270 mAh ditto

Standard discharge time

305 h ditto (for QC measurement) minimum:

Discharge current

≤ 2.0 mA standard:

available current: 8.0 mA at 1.1V

impulse load voltage: ≥ 1.1 V measured after 2s load

load resistance  $200\Omega$ 


impedance: ≤4 O measured at 1kHz


Discharge diagram:

ANSI/IEC Hearing Aid **Standard Test** 

145 hours - 2 mA background, 6 mA 100 ms pulse, ANSI/IEC Hearing Aid once every 2 hours, 12 hours/day to 1.05V at 70°F High Power Test (21° C) and 50% RH.

92 hours - 3 mA background, 12 mA 100 ms pulse, once every 2 hours, 12 hours/day to 1.05V at 70°F (21° C) and 50% RH.






shelf life: 4 years under proper storage conditions (ta: ≤ 22°C; RH: 60 ± 15%)

operating temperature

0....50 °C range:

mechanical specifications:

dimensions:









Volume: 0.26 cm<sup>3</sup> Nominal weight: 0.79 g

**Blister card** 

dimensions: 44 x 84 mm

AN-MANN®	ANSMANN Specifications for model:	A13 Zinc Air Battery "mercury free" 6pcs blister package
	data sheet no. / part no.	5013243
	supplier no.	703619
	author / date	TG / 23.03.2015