



SIMATIC ET 200SP, Analog output module, AQ 2x U/I High Feature suitable for BU type A0, A1, Color code CC00, channel diagnostics, 16 bit, +/-0.1%

General information	
Product type designation	AQ 2xU/I HF
HW functional status	from FS04
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC00
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> <li>Isochronous mode</li> </ul>	Yes
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>	V13 / V13
<ul style="list-style-type: none"> <li>STEP 7 configurable/integrated from version</li> </ul>	V5.5 SP3 / -
<ul style="list-style-type: none"> <li>PCS 7 configurable/integrated from version</li> </ul>	V8.1 SP1
<ul style="list-style-type: none"> <li>PROFIBUS from GSD version/GSD revision</li> </ul>	GSD Revision 5
<ul style="list-style-type: none"> <li>PROFINET from GSD version/GSD revision</li> </ul>	GSDML V2.3
Operating mode	
<ul style="list-style-type: none"> <li>Oversampling</li> </ul>	No
<ul style="list-style-type: none"> <li>MSO</li> </ul>	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	45 mA; without load
Current consumption, max.	90 mA; 2 channels current output 20 mA
Power loss	
Power loss, typ.	0.9 W
Address area	
Address space per module	
<ul style="list-style-type: none"> <li>Address space per module, max.</li> </ul>	4 byte; + 1 byte for QI information
Hardware configuration	
Automatic encoding	
<ul style="list-style-type: none"> <li>Mechanical coding element</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Type of mechanical coding element</li> </ul>	Type A
Analog outputs	

Number of analog outputs	2
Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	45 mA
Cycle time (all channels), min.	750 $\mu$ s
<b>Output ranges, voltage</b>	
• 0 to 10 V	Yes; 15 bit
• 1 V to 5 V	Yes; 13 bit
• -5 V to +5 V	Yes; 15 bit incl. sign
• -10 V to +10 V	Yes; 16 bit incl. sign
<b>Output ranges, current</b>	
• 0 to 20 mA	Yes; 15 bit
• -20 mA to +20 mA	Yes; 16 bit incl. sign
• 4 mA to 20 mA	Yes; 14 bit
<b>Connection of actuators</b>	
• for voltage output two-wire connection	Yes
• for voltage output four-wire connection	Yes
• for current output two-wire connection	Yes
<b>Load impedance (in rated range of output)</b>	
• with voltage outputs, min.	2 k $\Omega$
• with voltage outputs, capacitive load, max.	1 $\mu$ F
• with current outputs, max.	500 $\Omega$
• with current outputs, inductive load, max.	1 mH
<b>Destruction limits against externally applied voltages and currents</b>	
• Voltages at the outputs	30 V
<b>Cable length</b>	
• shielded, max.	1 000 m; 200 m for voltage output
<b>Analog value generation for the outputs</b>	
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	16 bit
<b>Settling time</b>	
• for resistive load	0.05 ms
• for capacitive load	0.05 ms; Max. 47 nF and 20 m cable length
• for inductive load	0.05 ms
<b>Errors/accuracies</b>	
Output ripple (relative to output range, bandwidth 0 to 50 kHz), (+/-)	0.02 %
Linearity error (relative to output range), (+/-)	0.03 %
Temperature error (relative to output range), (+/-)	0.003 %/K
Crosstalk between the outputs, max.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to output range), (+/-)	0.03 %
<b>Operational error limit in overall temperature range</b>	
• Voltage, relative to output range, (+/-)	0.2 %
• Current, relative to output range, (+/-)	0.2 %
<b>Basic error limit (operational limit at 25 °C)</b>	
• Voltage, relative to output range, (+/-)	0.1 %
• Current, relative to output range, (+/-)	0.1 %
<b>Isochronous mode</b>	
Execution and activation time (TCO), min.	500 $\mu$ s
Bus cycle time (TDP), min.	750 $\mu$ s
Jitter, max.	5 $\mu$ s
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
Substitute values connectable	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
<b>Diagnoses</b>	
• Monitoring the supply voltage	Yes
• Wire-break	Yes; channel-by-channel, only for output type "current"
• Short-circuit	Yes; channel-by-channel, only for output type "voltage"

<ul style="list-style-type: none"> <li>• Group error</li> <li>• Overflow/underflow</li> </ul>	<p>Yes</p> <p>Yes</p>
<b>Diagnostics indication LED</b>	
<ul style="list-style-type: none"> <li>• Monitoring of the supply voltage (PWR-LED)</li> <li>• Channel status display</li> <li>• for channel diagnostics</li> <li>• for module diagnostics</li> </ul>	<p>Yes; green PWR LED</p> <p>Yes; green LED</p> <p>Yes; red LED</p> <p>Yes; green/red DIAG LED</p>
<b>Potential separation</b>	
<b>Potential separation channels</b>	
<ul style="list-style-type: none"> <li>• between the channels</li> <li>• between the channels and backplane bus</li> <li>• between the channels and the power supply of the electronics</li> </ul>	<p>No</p> <p>Yes</p> <p>Yes</p>
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
<ul style="list-style-type: none"> <li>• horizontal installation, min.</li> <li>• horizontal installation, max.</li> <li>• vertical installation, min.</li> <li>• vertical installation, max.</li> </ul>	<p>-30 °C; &lt; 0 °C as of FS04</p> <p>60 °C</p> <p>-30 °C; &lt; 0 °C as of FS04</p> <p>50 °C</p>
<b>Altitude during operation relating to sea level</b>	
<ul style="list-style-type: none"> <li>• Installation altitude above sea level, max.</li> </ul>	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
<b>Dimensions</b>	
Width	15 mm
Height	73 mm
Depth	58 mm
<b>Weights</b>	
Weight, approx.	31 g
<b>last modified:</b>	1/16/2021 