

SIMATIC ET 200SP, CM PTP communication module for serial connection RS-422, RS-485 and RS-232, freeport, 3964 (R), USS, MODBUS RTU master, slave, max. 250 Kbit/s, suitable for BU type A0, pack quantity: 1 unit

General information	
Product type designation	CM PtP
Firmware version	
<ul style="list-style-type: none"> <li>FW update possible</li> </ul>	Yes
usable BaseUnits	BU type A0
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> <li>STEP 7 configurable/integrated from version</li> <li>PROFIBUS from GSD version/GSD revision</li> <li>PROFINET from GSD version/GSD revision</li> </ul>	STEP 7 V17 or higher  via GSD as of V5.6 HF4 GSD as of Revision 5 GSDML V2.34
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	31 mA
Current consumption, max.	35 mA
Power loss	
Power loss, typ.	0.7 W
Address area	
Address space per module	
<ul style="list-style-type: none"> <li>Inputs</li> <li>Outputs</li> </ul>	8 byte; performance mode: 32 byte 0 byte; performance mode: 32 byte
1. Interface	
Interface types	
<ul style="list-style-type: none"> <li>RS 485</li> <li>RS 422</li> <li>RS 232</li> <li>Design of the connection</li> </ul>	Yes Yes Yes Push-in terminal
Interface types	
RS 232	
<ul style="list-style-type: none"> <li>Transmission rate, max.</li> <li>Cable length, max.</li> <li>RS 232 auxiliary signals</li> </ul>	115.2 kbit/s 15 m RTS, CTS, DTR, DSR, RI, DCD
RS 485	
<ul style="list-style-type: none"> <li>Transmission rate, max.</li> <li>Cable length, max.</li> </ul>	250 kbit/s 1 200 m; 100 to 1200 m, depending on transmission speed
RS 422	
<ul style="list-style-type: none"> <li>Transmission rate, max.</li> <li>Cable length, max.</li> <li>4-wire full duplex connection</li> <li>4-wire multipoint connection</li> </ul>	115.2 kbit/s 1 200 m Yes Yes
Protocols	
Integrated protocols	

<b>Freeport</b>	
— Telegram length, max.	2 kbyte; performance mode: receive data max. 24 byte and send data max. 30 byte
— Bits per character	7 or 8
— Number of stop bits	1 or 2 bit
— Parity	None, even, odd, always 1, always 0, any
<b>3964 (R)</b>	
— Telegram length, max.	2 kbyte; performance mode: receive data max. 24 byte and send data max. 30 byte
— Bits per character	7 or 8
— Number of stop bits	1 or 2 bit
— Parity	None, even, odd, always 1, always 0, any
<b>Modbus RTU master</b>	
— Address area	1 to 247, extended 1 to 65535
— Number of slaves, max.	32
<b>MODBUS RTU slave</b>	
— Address area	1 to 247, extended 1 to 65535
<b>Telegram buffer</b>	
• Buffer memory for telegrams	4 kbyte
• Number of telegrams which can be buffered	255
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
• Hardware interrupt	No
<b>Diagnoses</b>	
• Wire-break	Yes
<b>Diagnostics indication LED</b>	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• for module diagnostics	Yes; green/red DIAG LED
• Receive RxD	Yes; green LED
• Transmit TxD	Yes; green LED
<b>Potential separation</b>	
between backplane bus and interface	Yes
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
<b>Altitude during operation relating to sea level</b>	
• Installation altitude above sea level, max.	5 000 m
<b>Decentralized operation</b>	
to SIMATIC S7-300	Yes
to SIMATIC S7-400	Yes
to SIMATIC S7-1200	Yes
to SIMATIC S7-1500	Yes
to standard PROFINET controller	Yes
<b>Dimensions</b>	
Width	15 mm
Height	73 mm
Depth	58 mm
<b>Weights</b>	
Weight, approx.	30 g
<b>last modified:</b>	5/24/2021 