




— PRODUCT DATA SHEET

W4R Work



W4R Work

PRODUCT DESCRIPTION

Robust, versatile, compact: The Ledlenser W4R Work is a reliable work light for everyday workshop use. The superior Ledlenser light beam ensures precise and powerful illumination of work areas – either broadly via flood light or selectively via a spot LED in the lamp head. Thanks to the integrated magnet and swivelling base, the W4R Work can be flexibly positioned and aligned at any time. The powerful battery can be charged quickly and easily via USB-C and can be replaced if necessary. Other features include a clip for attaching to work clothing or equipment, a nubbed surface for a strong grip and a handy transport lock.

- Compact premium work light with two light sources for wide-area (flood) or spot illumination
- Robust plastic housing with non-slip surface structure
- Flexible mounting and illumination thanks to magnet and swivel mechanism
- Service-replaceable li-ion battery; easily rechargeable via USB-C, with battery and charge level indicator
- Transport lock prevents light from being accidentally turned on

TECHNICAL DATA

| | |
|------------------------------|-----|
| Width [mm] | 28 |
| Depth [mm] | 20 |
| Height [mm] | 163 |
| Weight incl. batteries [g] | 91 |
| Weight without batteries [g] | 68 |
| Focus function | No |
| Primary material | PC |
| Cartridge | No |

POWER SUPPLY

| | |
|--|--|
| Power source type | Rechargeable battery |
| Battery quantity | 1 |
| Battery type | Li-ion |
| Battery replaceable | No |
| Total battery voltage [V] | 3.7 |
| Total battery capacity [mAh] | 760 |
| Total battery energy ² [Wh] | 2.812 |
| Rechargeable | Yes |
| Charging time ⁵ [min] | 120 |
| Energy modes | Constant Light |
| Energy status indicator | Battery Indicator, Charge Indicator, Low Battery Warning |

FURTHER SPECIFICATIONS

| | |
|--------------------------------|------------|
| IP class | IP54 |
| Drop test (drop height) [m] | 1 |
| IK Code [J] | 7 |
| Working temperature range [°C] | -20 to +40 |

LIGHT FUNCTIONS

Low Power, Mid Power, Power

LIGHT SOURCE

| | COB | Spot |
|-----------------------------|--------------|----------------|
| Amount LEDs | 1 | 1 |
| LED type | COB LED | High Power LED |
| Color | White | White |
| Color temperature [K] | 6000 to 7500 | 6000 to 7500 |
| Color rendering index (CRI) | 70 | 70 |

LIGHT VALUES - COB

| ANSI – Constant Light | Boost | Power | Mid Power | Low Power |
|--------------------------------|-------|-------|-----------|-----------|
| Light output ¹ [lm] | | 220 | | 60 |
| Run time ¹ [h] | | 2 | | 9 |

LIGHT VALUES - Spot

| ANSI – Constant Light | Boost | Power | Mid Power | Low Power |
|--------------------------------|-------|-------|-----------|-----------|
| Light output ¹ [lm] | | | 100 | |
| Beam distance ¹ [m] | | | 90 | |
| Run time ¹ [h] | | | 2 | |

SWITCH

Front Switch

FEATURES

Transportation lock , Flicker Free

W4R Work

PACKAGING AND LOGISTICS



PACKAGING INFORMATION

| | |
|-----------------------|---|
| Type of packaging | Box |
| Scope of delivery | 1 set of rechargeable batteries, USB cable |
| Item No. | 502733 |
| Customs tariff number | 8513100000 |
| Color | black |
| MSRP price (€) | 39.90 |

SINGLE PACKAGE

| | |
|---------------------------|----------------|
| Dimensions W x H x D [cm] | 7.2 x 21 x 8.5 |
| Gross weight [g] | 228 |
| GTIN-13 | 4058205030441 |

EXPORT CARTON

| | |
|---------------------------|----------------|
| Unit | 24 |
| Dimensions W x D x H [cm] | 45.5 x 29 x 34 |
| Gross weight [kg] | 6.2 |
| GTIN-13 | 4058205030427 |

W4R Work

PRODUCT SERIES

Robust, versatile and rechargeable: The Ledlenser W-series work lights offer reliable professional light for workshops, construction sites or your next DIY project. From compact clip lights and convenient pen lights to flexible high-end lights: Outstanding Ledlenser light quality and numerous innovative features make the W-series work lights a must-have for every well-stocked tool box.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurement values according to ANSI FL1 in the respective setting. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting, and to battery duration (hours/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If the light is equipped with (a) colored LED(s), the measurement values are given for the white light or the white LED. If the light has different energy modes, the measurement is made based on the "energy saving mode".

2) Calculated capacity value in watt-hours (Wh). This applies to the delivery state of the battery/ies inside the respective item, or for lights with rechargeable battery/ies, to the rechargeable battery/ies inside the product when fully charged.

5) Charging time varies by hardware used.