

SIMATIC ET 200AL, DQ 8x 24 V DC/2 A, 8x M12, Degree of protection IP67



General information	
Product type designation	DQ 8x24VDC/2A
HW functional status	FS03
Firmware version	V1.0.x
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated as of version</li> </ul>	STEP 7 V13 SP1 or higher
<ul style="list-style-type: none"> <li>STEP 7 configurable/integrated as of version</li> </ul>	V5.5 SP4 Hotfix 7 or higher
<ul style="list-style-type: none"> <li>PROFIBUS as of GSD version/GSD revision</li> </ul>	GSD as of Revision 5
<ul style="list-style-type: none"> <li>PROFINET as of GSD version/GSD revision</li> </ul>	GSDML V2.3.1
Supply voltage	
Load voltage 1L+	
<ul style="list-style-type: none"> <li>Rated value (DC)</li> </ul>	24 V
<ul style="list-style-type: none"> <li>permissible range, lower limit (DC)</li> </ul>	20.4 V
<ul style="list-style-type: none"> <li>permissible range, upper limit (DC)</li> </ul>	28.8 V
<ul style="list-style-type: none"> <li>Reverse polarity protection</li> </ul>	Yes; against destruction; load increasing

<b>Load voltage 2L+</b>	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes; against destruction; load increasing
<b>Input current</b>	
Current consumption (rated value)	40 mA; without load
from load voltage 1L+ (unswitched voltage)	4 A; Maximum value
from load voltage 2L+, max.	4 A; Maximum value
<b>Power loss</b>	
Power loss, typ.	4 W
<b>Digital outputs</b>	
Number of digital outputs	8
• in groups of	4; 2 load groups for 4 outputs each
Short-circuit protection	Yes; per channel, electronic
• Response threshold, typ.	2.8 A
Limitation of inductive shutdown voltage to	2L+ (-47 V)
<b>Switching capacity of the outputs</b>	
• on lamp load, max.	10 W
<b>Load resistance range</b>	
• lower limit	12 $\Omega$
• upper limit	4 k $\Omega$
<b>Output voltage</b>	
• for signal "1", min.	L+ (-0.8 V)
<b>Output current</b>	
• for signal "1" rated value	2 A
• for signal "1" permissible range, max.	2 A; with inductive load to IEC 60947-5-1, DC-13 / AC-15
• for signal "0" residual current, max.	0.5 mA
<b>Switching frequency</b>	
• with resistive load, max.	100 Hz
• with inductive load, max.	0.1 Hz; 0.25 Hz at 25 °C
• on lamp load, max.	1 Hz
<b>Total current of the outputs</b>	
• Current per group, max.	4 A; For inductive load max. 2 channels per group
<b>Cable length</b>	
• unshielded, max.	30 m
<b>Interrupts/diagnostics/status information</b>	
Substitute values connectable	Yes; channel by channel, parameterizable
<b>Alarms</b>	
• Diagnostic alarm	Yes; Parameterizable
<b>Diagnostic messages</b>	

<ul style="list-style-type: none"> <li>• Short-circuit</li> </ul>	Yes; Outputs to ground; module by module
<b>Diagnostics indication LED</b>	
<ul style="list-style-type: none"> <li>• Channel status display</li> </ul>	Yes; green LED
<ul style="list-style-type: none"> <li>• for module diagnostics</li> </ul>	Yes; green/red LED
<ul style="list-style-type: none"> <li>• For load voltage monitoring</li> </ul>	Yes; green LED
<b>Potential separation</b>	
between the load voltages	Yes
<b>Potential separation channels</b>	
<ul style="list-style-type: none"> <li>• between the channels, in groups of</li> </ul>	4
<ul style="list-style-type: none"> <li>• between the channels and backplane bus</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• between the channels and the power supply of the electronics</li> </ul>	No; 4 channels are non-isolated and 4 channels are isolated from supply voltage 1L+
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)
<b>Degree and class of protection</b>	
IP degree of protection	IP65/67
<b>Standards, approvals, certificates</b>	
Suitable for safety-related tripping of standard modules	Yes; From FS01
<b>Highest safety class achievable for safety-related tripping of standard modules</b>	
<ul style="list-style-type: none"> <li>• Performance level according to ISO 13849-1</li> </ul>	PL d
<ul style="list-style-type: none"> <li>• Category according to ISO 13849-1</li> </ul>	Cat. 3
<ul style="list-style-type: none"> <li>• SILCL according to IEC 62061</li> </ul>	SILCL 2
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
<ul style="list-style-type: none"> <li>• min.</li> </ul>	-30 °C
<ul style="list-style-type: none"> <li>• max.</li> </ul>	55 °C
<b>Connection method</b>	
Design of electrical connection for the inputs and outputs	M12, 5-pole
Design of electrical connection for supply voltage	M8, 4-pole
<b>ET-Connection</b>	
<ul style="list-style-type: none"> <li>• ET-Connection</li> </ul>	M8, 4-pin, shielded
<b>Dimensions</b>	
Width	45 mm
Height	159 mm
Depth	40 mm
<b>Weights</b>	
Weight, approx.	192 g

last modified:

02/04/2020