

FEATURES

- Variety of metric sizes available
- Ideal for hand or machine use
- Manufactured from HSS for durability and heat resistance
- ISO standard

RS PRO HSS M30 Second, Straight Flute Threading Tap, 130 mm Length

RS Stock No.: 522-7676



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Threading Taps



Product Description

Introducing RS PRO HSS straight flute thread taps, a selection of high quality and professional threading taps ideal for cutting thread (tapping) by hand or machine, into drilled holes in materials such as metal and wood.

General Specifications

Thread Size	M30
Туре	Threading Tap
Pitch	1.5mm
Thread Standard	Metric Fine
Number of Pieces	1
Standard	ISO 529
Applications	Construction, DIY, Plumbing, Workshops, Renovations

Mechanical Specifications

Overall Length	130mm
Material	HSS
Shank Diameter	19.9mm
Square Length	15.8mm
Tapping Drill Size	28.5mm
Maximum Thread Length	41mm
Major Diameter	30.00mm
Minor Diameter	28.160mm
Thread Depth	0.920mm
Clearance Drill	31.0mm





RS	Manufacturers	Size	d1	L1	L	а
Code	Code		(mm)	(mm)	(mm)	(mm)
522-7676	21-505-802	M30	19.9	41	130	15.8

RS Code	Size	Pitch (mm)	,	Minor Dia (mm)		Tapping Drill	Clearance Drill
522-7676	M30	1.50	30.00	28.160	0.920	28.5	31.0

