



General information	
Product type designation	SM 1231, AI 4x16 bit RTD
Supply voltage	
Rated value (DC)	Yes
<ul style="list-style-type: none"> <li>24 V DC</li> </ul>	
Input current	
Current consumption, typ.	40 mA
from backplane bus 5 V DC, typ.	80 mA
Power loss	
Power loss, typ.	1.5 W
Analog inputs	
Number of analog inputs	4; Resistance thermometer
permissible input voltage for voltage input (destruction limit), max.	±35 V
Technical unit for temperature measurement adjustable	Degrees Celsius/degrees Fahrenheit
Input ranges	
<ul style="list-style-type: none"> <li>Voltage</li> </ul>	No

• Current	No
• Thermocouple	No
• Resistance thermometer	Yes; Resistance-type transmitter: Pt10, Pt50, Pt100, Pt200, Pt500, Pt1000, Ni100, Ni120, Ni200, Ni500, Ni1000, Cu10, Cu50, Cu100, LG-Ni1000
• Resistance	Yes; 150 Ω, 300 Ω, 600 Ω
<b>Input ranges (rated values), resistance thermometer</b>	
• Cu 10	Yes
• Input resistance (Cu 10)	10 Ω
• Ni 100	Yes
• Input resistance (Ni 100)	100 Ω
• Ni 1000	Yes
• Input resistance (Ni 1000)	1 000 Ω
• LG-Ni 1000	Yes
• Input resistance (LG-Ni 1000)	1 000 Ω
• Ni 120	Yes
• Input resistance (Ni 120)	120 Ω
• Ni 200	Yes
• Input resistance (Ni 200)	200 Ω
• Ni 500	Yes
• Input resistance (Ni 500)	500 Ω
• Pt 100	Yes
• Input resistance (Pt 100)	100 Ω
• Pt 1000	Yes
• Input resistance (Pt 1000)	1 000 Ω
• Pt 200	Yes
• Input resistance (Pt 200)	200 Ω
• Pt 500	Yes
• Input resistance (Pt 500)	500 Ω
<b>Input ranges (rated values), resistors</b>	
• 0 to 150 ohms	Yes
• 0 to 300 ohms	Yes
• 0 to 600 ohms	Yes
<b>Thermocouple (TC)</b>	
<b>Temperature compensation</b>	
— parameterizable	No
<b>Analog value generation for the inputs</b>	
Measurement principle	integrating
<b>Integration and conversion time/resolution per channel</b>	
• Resolution with overrange (bit including sign), max.	15 bit; + sign
• Integration time, parameterizable	No

- Interference voltage suppression for interference frequency f1 in Hz

85 dB at 50 / 60 / 400 Hz

### Errors/accuracies

Temperature error (relative to input range), (+/-) 25 °C ±0.1%, to 55 °C ±0.2% total measurement range

Repeat accuracy in steady state at 25 °C (relative to output range), (+/-) 0.05 %

Interference voltage suppression for  $f = n \times (f1 \pm 1 \%)$ , f1 = interference frequency

- Common mode interference, min. 120 dB

### Interrupts/diagnostics/status information

Alarms Yes

Diagnostics function Yes; Can be read out

#### Alarms

- Diagnostic alarm Yes

#### Diagnostic messages

- Monitoring the supply voltage Yes
- Wire-break Yes

#### Diagnostics indication LED

- for status of the inputs Yes
- for maintenance Yes

### Degree and class of protection

Degree of protection acc. to EN 60529

- IP20 Yes

### Standards, approvals, certificates

CE mark Yes

CSA approval Yes

FM approval Yes

RCM (formerly C-TICK) Yes

### Ambient conditions

#### Free fall

- Fall height, max. 0.3 m; five times, in product package

#### Ambient temperature during operation

- min. -20 °C
- max. 60 °C
- horizontal installation, min. -20 °C
- horizontal installation, max. 60 °C
- vertical installation, min. -20 °C
- vertical installation, max. 50 °C

#### Ambient temperature during storage/transportation

- min. -40 °C
- max. 70 °C

Air pressure acc. to IEC 60068-2-13

• Operation, min.	795 hPa
• Operation, max.	1 080 hPa
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
<b>Relative humidity</b>	
• Operation at 25 °C without condensation, max.	95 %
<b>Pollutant concentrations</b>	
• SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
<b>Connection method</b>	
required front connector	Yes
<b>Mechanics/material</b>	
Enclosure material (front)	
• Plastic	Yes
<b>Dimensions</b>	
Width	45 mm
Height	100 mm
Depth	75 mm
<b>Weights</b>	
Weight, approx.	220 g
<b>last modified:</b>	01/02/2019