



All dimensions are in mm; tolerances according to ISO 2768 m-H

**Interface**

According to IEC 60169-17, MIL-PRF-39012, DIN EN 122200

**Documents**

Panel piercing B 3

**Material and plating**

**Connector parts**

- Center contact
- Outer contact
- Body
- Dielectric
- Gasket

**Material**

- CuBe
- Brass
- Brass
- PTFE
- NBR

**Plating**

- AuroDur®, gold plated
- Flash white bronze over silver(e.g. Optargen®)
- Flash white bronze over silver(e.g. Optargen®)

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF\_35/08.13/6.1

TNC 50 Ω

ADAPTOR  
JACK - JACK

**56K501-K00N5**

**Electrical data**

Impedance 50 Ω  
 Frequency DC to 10 GHz  
 Return loss ≥ 30 dB @ DC to 2.5 GHz  
 ≥ 20 dB @ 2.5 GHz to 6 GHz  
 Insertion loss ≤ 0.05 x √ f [GHz] dB, DC to 6 GHz  
 Insulation resistance ≥ 5 GΩ  
 Center contact resistance ≤ 1.5 mΩ  
 Outer contact resistance ≤ 1 mΩ  
 Test voltage (at sea level) 1500 V rms  
 Working voltage (at sea level) 500 V rms  
 Power handling (at 20 °C, sea level, VSWR 1.0) 80 W @ 2 GHz

**Mechanical data**

Mating cycles ≥ 500  
 Center contact captivation: axial ≥ 15 N  
 Coupling test torque ≤ 1.7 Nm  
 Recommended torque 0.46 Nm to 0.69 Nm

**Environmental data**

Temperature range -25 °C to +110 °C  
 Thermal shock MIL-STD-202, Method 107, Condition B  
 Corrosion MIL-STD-202, Method 101, Condition B  
 Vibration MIL-STD-202, Method 204, Condition B  
 Shock MIL-STD-202, Method 213, Condition G  
 Moisture resistance MIL-STD-202, Method 106  
 Degree of protection (mated pair) IEC 60529, IP 68 (assembled in housing)  
 RoHS compliant

**Tooling**

N/A

**Suitable cables**

N/A

**Weight**

Weight 22.1 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Inge Mühlauer	10.08.04	Sa. Krautenbacher	19.03.14	d00	14-0352	T. Krojer	19.03.14

Rosenberger Hochfrequenztechnik GmbH & Co. KG  
 P.O.Box 1260 D-84526 Tittmoning Germany  
 www.rosenberger.de

Tel. : +49 8684 18-0  
 Fax : +49 8684 18-499  
 Email : info@rosenberger.de

Page  
 2 / 2