





FEATURES

- Ø8.0mm mounting
- Nickel plated brass housing
- Range of LED colour options
- · Choice of solder pins or wires

BENEFITS

- Standard industrial mounting size
- · Suitable for harsh environments
- Suitable for status panel indication
- Flexibility for different applications
- · Outstanding reliability

Marl Part Number	LED Colour	Typical Voltage DC Vf	Max. Reverse Voltage	Max. Current DC If	Max. Power Dissipation	Typical LED Luminous Intensity @20mA	Typical LED Wavelength λp	Viewing Angle 2 O 1/2	Operating Temp Topr *	Storage Temp Tstg
573-502-04	HE Red Diffused	2	5	30	80	25	625	45	-25 to +85	-30 to +100
573-505-04	Red Diffused	2.1	5	20	45	2	700	45	-25 to +85	-30 to +100
573-511-04	Yellow Diffused	2	5	30	85	25	590	45	-25 to +85	-30 to +100
573-514-04	Green Diffused	2.1	5	30	80	25	568	45	-25 to +85	-30 to +100
573-520-04	Blue Diffused	4	5	25	150	15	430	45	-25 to +85	-30 to +100
		Vdc	Vdc	mA	mW	mcd	nm	Deg	°C	°C

OPTIONAL FLYING LEAD TERMINATORS

Marl Part No Suffix	Wire Length	Wire Colour	No/Diameter of Conductors	Diameter of Insulation	Wire Specification
573-505-04 -40	305mm	Red - Anode Black - Cathode	11/0.16mm	1.43mm	24AWG

NOTES

All LED components are supplied in anti-static packaging.

* LED Characteristics stated at Ta = 25°C. For operating temperature derating graphs, please refer to sheet 2.

To order please contact us on +44 (0) 1229 582 430 F +44 (0) 1229 585 155 | E sales@marl.co.uk | www.leds.co.uk

y marlleds f marlinternationallimited in company/marl-international-limited



573 Version DS008/2016. Page 1 of 2




573 SERIES PANEL INDICATOR LED


TECHNICAL CHARACTERISTICS

Series	Panel Cutout	Min. Mounting Centres	Min Max. Panel Thickness	Nut mounting torque
573	8.0	17.0	1.2 - 3.5	0.35
	mm	mm	mm	Nm

TECHNICAL DRAWING

Dimensions in mm (typical). Not to scale. Mounting hole to be clean and burr free.






Stainless Steel

Mounting Hole **DE-RATING GRAPHS**

+



Body Brass, Nickel-Plated Epoxy (LED Lens) Lens Termination (Standard version) I FD Leads Termination (Flying Leads version) Wires, Stripped and Tinned

DESIGN CONSIDERATIONS

Electro-Static Discharge (ESD)

Build up of electro-static discharge occurs in many situations involving people moving and handling products. The range of possible situations is very diverse but voltage levels as high as several thousand volts can and do arise in many individual situations. When an operator charged up to these levels handles a static sensitive device, there is a very probable likelihood that the device will be irreversibly damaged. It is essential that precautions are taken at all stages during manufacture and assembly of these products. Although LEDs were never considered to be static sensitive

devices, changes in manufacturing technology and materials used to produce higher intensity products over a large range of the wavelength spectrum have changed this. Marl has an approved system of ESD control from goods in, through production and into final packing and despatch. Marl recommend all users of LED based products follow the guidelines of BS 100015.

Voltage, Current and Temperature

Lock Washer

The forward voltage / current value of an LED is dependent upon the ambient temperature of the environment in which it is operated. Therefore, care must be taken to operate the LED at the correct voltage / current values, depending upon the ambient temperature.

Marl should be contacted if the device is to be operated outside the temperature range specified. Marl accept no liability for any product that is operated outside the stated voltage or temperature range.



w marlleds f marlinternationallimited in company/marl-international-limited

