6ES7531-7PF00-0AB0

Data sheet



SIMATIC S7-1500 analog input module AI 8xU/R/RTD/TC HF, 16 bit resolution, up to 21 bit Resolution at RT and TC, accuracy 0.1%, 8 channels in groups of 1; common mode voltage: 30 V AC/60 V DC, Diagnostics; Hardware interrupts Scalable temperature measuring range, thermocouple type C, Calibrate in RUN; Delivery including infeed element, shield bracket and shield terminal: Front connector (screw terminals or push-in) to be ordered separately

General information	
Product type designation	AI 8xU/R/RTD/TC HF
HW functional status	FS01
Firmware version	V1.1.0
FW update possible	Yes
Product function	
 I&M data 	Yes; I&M0 to I&M3
 Isochronous mode 	No
 Prioritized startup 	Yes
 Measuring range scalable 	Yes
 Scalable measured values 	No
Adjustment of measuring range	No
Engineering with	
 STEP 7 TIA Portal configurable/integrated from version 	V14 / -
 STEP 7 configurable/integrated from version 	V5.5 SP3 / -
 PROFIBUS from GSD version/GSD revision 	V1.0 / V5.1
PROFINET from GSD version/GSD revision	V2.3 / -
Operating mode	
 Oversampling 	No
• MSI	Yes
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	55 mA; with 24 V DC supply
Power	
Power available from the backplane bus	0.85 W
Power loss	
Power loss, typ.	1.9 W
Analog inputs	
Number of analog inputs	8; Plus one additional RTD (reference) channel
For voltage measurement	8; Plus one additional RTD (reference) channel
For resistance/resistance thermometer	8; Plus one additional RTD (reference) channel
	·

measurement	
For thermocouple measurement	8; Plus one additional RTD (reference) channel
permissible input voltage for voltage input (destruction	20 V
limit), max.	
Constant measurement current for resistance-type transmitter, typ.	150 Ohm, 300 Ohm, 600 Ohm, Cu10, Cu50, Cu100, Ni10, Ni100, Ni120, Ni200, Pt10, Pt50, Pt100, Pt200 climate: 1 mA; 6 kOhm, Ni500, Ni1000, LG-Ni1000, Pt200 standard, Pt500, Pt1000, PTC: 0.25 mA
Technical unit for temperature measurement adjustable	Yes; °C/°F/K
Input ranges (rated values), voltages	
• 0 to +5 V	No
• 0 to +10 V	No
• 1 V to 5 V	No
• -1 V to +1 V	Yes
— Input resistance (-1 V to +1 V)	10 ΜΩ
• -10 V to +10 V	No
• -2.5 V to +2.5 V	No
• -25 mV to +25 mV	Yes
— Input resistance (-25 mV to +25 mV)	10 ΜΩ
• -250 mV to +250 mV	Yes
— Input resistance (-250 mV to +250 mV)	10 ΜΩ
• -5 V to +5 V	No
• -50 mV to +50 mV	Yes
— Input resistance (-50 mV to +50 mV)	10 ΜΩ
● -500 mV to +500 mV	Yes
— Input resistance (-500 mV to +500 mV)	10 ΜΩ
• -80 mV to +80 mV	Yes
— Input resistance (-80 mV to +80 mV)	10 ΜΩ
Input ranges (rated values), currents	
• 0 to 20 mA	No
• -20 mA to +20 mA	No No
4 mA to 20 mA Input ranges (reted values), thermosouples.	No
Input ranges (rated values), thermocouples • Type B	Yes
— Input resistance (Type B)	10 ΜΩ
Type C	Yes
— Input resistance (Type C)	10 ΜΩ
• Type E	Yes
— Input resistance (Type E)	10 ΜΩ
• Type J	Yes
— Input resistance (type J)	10 ΜΩ
• Type K	Yes
Input resistance (Type K)	10 ΜΩ
• Type L	No
• Type N	Yes
Input resistance (Type N)	10 ΜΩ
• Type R	Yes
— Input resistance (Type R)	10 ΜΩ
• Type S	Yes
— Input resistance (Type S)	10 ΜΩ
• Type T	Yes
— Input resistance (Type T)	10 ΜΩ
Type TXK/TXK(L) to GOST	Yes
 Input resistance (Type TXK/TXK(L) to GOST) 	10 ΜΩ
Input ranges (rated values), resistance thermometer	
• Cu 10	Yes; Standard/climate
— Input resistance (Cu 10)	10 ΜΩ
Cu 10 according to GOST	Yes; Standard/climate
1 1 1 1 (O 10 II 1 O 00T)	10 ΜΩ
 Input resistance (Cu 10 according to GOST) 	10 19122
Input resistance (Cu 10 according to GOST) Cu 50	Yes; Standard/climate

- Input resistance (Cu 50 according to GOST) $10~\text{M}\Omega$ Yes: Standard/climate • Cu 100 - Input resistance (Cu 100) 10 MO • Cu 100 according to GOST Yes; Standard/climate Input resistance (Cu 100 according to GOST) 10 MO • Ni 10 Yes; Standard/climate Input resistance (Ni 10) 10 MΩ • Ni 10 according to GOST Yes; Standard/climate - Input resistance (Ni 10 according to GOST) 10 MΩ Yes; Standard/climate • Ni 100 - Input resistance (Ni 100) 10 MΩ Ni 100 according to GOST Yes; Standard/climate — Input resistance (Ni 100 according to GOST) 10 MO • Ni 1000 Yes; Standard/climate - Input resistance (Ni 1000) • Ni 1000 according to GOST Yes: Standard/climate Input resistance (Ni 1000 according to GOST) $10 \ M\Omega$ • LG-Ni 1000 Yes; Standard/climate - Input resistance (LG-Ni 1000) 10 MO • Ni 120 Yes: Standard/climate - Input resistance (Ni 120) 10 MΩ • Ni 120 according to GOST Yes; Standard/climate Input resistance (Ni 120 according to GOST) 10 MΩ • Ni 200 Yes; Standard/climate 10 MO - Input resistance (Ni 200) • Ni 200 according to GOST Yes; Standard/climate - Input resistance (Ni 200 according to GOST) 10 MΩ • Ni 500 Yes; Standard/climate 10 MΩ - Input resistance (Ni 500) Ni 500 according to GOST Yes; Standard/climate Input resistance (Ni 500 according to GOST) 10 MΩ • Pt 10 Yes; Standard/climate Input resistance (Pt 10) 10 MO Pt 10 according to GOST Yes; Standard/climate — Input resistance (Pt 10 according to GOST) $10 \ M\Omega$ Yes; Standard/climate - Input resistance (Pt 50) 10 MΩ Yes: Standard/climate • Pt 50 according to GOST — Input resistance (Pt 50 according to GOST) 10 MO • Pt 100 Yes: Standard/climate Input resistance (Pt 100) 10 MΩ • Pt 100 according to GOST Yes; Standard/climate - Input resistance (Pt 100 according to GOST) 10 MΩ Yes; Standard/climate • Pt 1000 - Input resistance (Pt 1000) 10 MO • Pt 1000 according to GOST Yes: Standard/climate - Input resistance (Pt 1000 according to GOST) 10 MO • Pt 200 Yes; Standard/climate - Input resistance (Pt 200) $10 \ M\Omega$ • Pt 200 according to GOST Yes; Standard/climate Input resistance (Pt 200 according to GOST) $10~\text{M}\Omega$ • Pt 500 Yes; Standard/climate - Input resistance (Pt 500) 10 MO Pt 500 according to GOST Yes; Standard/climate - Input resistance (Pt 500 according to GOST) 10 MΩ Input ranges (rated values), resistors • 0 to 150 ohms Yes Input resistance (0 to 150 ohms) 10 MΩ • 0 to 300 ohms Yes - Input resistance (0 to 300 ohms) 10 MO

• 0 to 600 ohms	Yes
— Input resistance (0 to 600 ohms)	10 ΜΩ
• 0 to 3000 ohms	No
• 0 to 6000 ohms	Yes
— Input resistance (0 to 6000 ohms)	10 ΜΩ
• PTC	Yes
— Input resistance (PTC)	10 ΜΩ
Thermocouple (TC)	
Temperature compensation	
— parameterizable	Yes
 internal temperature compensation 	Yes
 external temperature compensation via RTD 	Yes
 Compensation for 0 °C reference point temperature 	Yes; fixed value can be set
— Reference channel of the module	Yes; 9th channel that can be used as a genuine 9th RTD channel regardless of the parameterization of the other channels, or that can be used for compensation in the case of TC measurement
Cable length	
• shielded, max.	800 m; at U; 200 m at R/RTD/TC
Analog value generation for the inputs	
Integration and conversion time/resolution per channel	
 Resolution with overrange (bit including sign), max. 	21 bit; For measuring mode RTC and TC when using the function "Scalable temperature measuring range" (32 bit REAL format); 16 bit for measuring mode R and U; 16 bit for all measuring modes when using the S7 format (16 bit INTEGER)
 Integration time, parameterizable 	Yes
Integration time (ms)	Fast mode: 2.5 / 16.67 / 20 / 100 ms, standard mode: 7.5 / 50 / 60 / 300 ms
 Basic conversion time, including integration time (ms) 	Fast mode: 4 / 18 / 22 / 102 ms; Standard mode: 9 / 52 / 62 / 302 ms
 additional conversion time for wire-break monitoring 	Thermocouples, 150 Ohm, 300 Ohm, 600 Ohm, Cu10, Cu50, Cu100, Ni10, Ni100, Ni120, Ni200, Pt10, Pt50, Pt100: 4 ms; 6 kOhm, Ni500, Ni1000, LG-Ni1000, Pt200, Pt500, Pt1000: 13 ms
 Interference voltage suppression for interference frequency f1 in Hz 	400 / 60 / 50 / 10 Hz
Basic execution time of the module (all channels released)	Corresponds to the channel with the highest basic conversion time
Smoothing of measured values	
 parameterizable 	Yes
Step: None	Yes
Step: low	Yes
Step: Medium	Yes
Step: High	Yes
Encoder	
Connection of signal encoders	
• for voltage measurement	Yes
• for current measurement as 2-wire transducer	No
• for current measurement as 4-wire transducer	No
 for resistance measurement with two-wire connection 	Yes
• for resistance measurement with three-wire	Yes; All measuring ranges except PTC; internal compensation of the
connection	cable resistances
 for resistance measurement with four-wire connection 	Yes; All measuring ranges except PTC
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.02 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, max.	-80 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.02 %
Temperature error of internal compensation	±1,5 °C
Operational error limit in overall temperature range	
• Voltage, relative to input range, (+/-)	0.1 %

 Resistance, relative to input range, (+/-) 	0.1 %
 Resistance thermometer, relative to input range, (+/- 	Cuxxx Standard: ±0.5 K, Cuxxx Klima: ±0.5 K, Ptxxx Standard: ±1 K,
)	Ptxxx Klima: ±0.5 K, Nixxx Standard: ±0.5 K, Nixxx Klima: ±0.3 K
 Thermocouple, relative to input range, (+/-) 	Type B: > 600 °C ±2 K, Type E: > -200 °C ±1 K, Type J: > -210 °C ±1 K, Type K: > -200 °C ±2 K, Type N: > -200 °C ±2 K, Type R: > 0 °C ±2 K,
	Type S: > 0 °C ±2 K, Type T: > -200 °C ±1 K, Type C: ±4 K, Type
	TXK/TXK(L): ±1 K
Basic error limit (operational limit at 25 °C)	
 Voltage, relative to input range, (+/-) 	0.05 %
 Resistance, relative to input range, (+/-) 	0.05 %
 Resistance thermometer, relative to input range, (+/- 	Cuxxx Standard: ±0.3 K, Cuxxx Klima: ±0.2 K, Ptxxx Standard: ±0.5 K,
The agree a couple of the literature and the literature (1)	Ptxxx Klima: ±0.2 K, Nixxx Standard: ±0.3 K, Nixxx Klima: ±0.15 K
 Thermocouple, relative to input range, (+/-) 	Type B: > 600 °C ±1 K, Type E: > -200 °C ±0.5 K, Type J: > -210 °C ±0.5 K, Type K: > -200 °C ±1 K, Type R: > 0 °C
	±1 K, Type S: > 0 °C ±1 K, Type T: > -200 °C ±0.5 K, Type C: ±2 K,
	Type TXK/TXK(L): ±0.5 K
Interference voltage suppression for f = n x (f1 +/- 1 %), f1 =	
 Series mode interference (peak value of interference < rated value of input range), min. 	80 dB; in the Standard operating mode, 40 dB in the Fast operating mode
Common mode voltage, max.	60 V DC/30 V AC
Common mode interference, min.	80 dB
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	100
Diagnostic alarm	Yes
Limit value alarm	Yes; two upper and two lower limit values in each case
Diagnoses	- 11
Monitoring the supply voltage	Yes
Wire-break	Yes; Only with TC, R, RTD
Overflow/underflow	Yes
Diagnostics indication LED	
RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
 Monitoring of the supply voltage (PWR-LED) 	Yes; green LED
 Channel status display 	Yes; green LED
 for channel diagnostics 	Yes; red LED
for module diagnostics	Yes; red LED
Potential separation	
Potential separation channels	
 between the channels 	Yes
 between the channels, in groups of 	1
 between the channels and backplane bus 	Yes
 between the channels and the power supply of the electronics 	Yes
Permissible potential difference	
between different circuits	60 V DC/30 V AC; insulation rated for 120 V AC basic insulation:
between unierent circuits	between the channels and the supply voltage L+; between the channels
	and the backplane bus; between the channels
Isolation	
Isolation tested with	2 000 V DC between the channels and the supply voltage L+; 2 000 V
	DC between the channels and the backplane bus; 2 000 V DC between
	the channels; 707 V DC (type test) between the supply voltage L+ and the backplane bus
Standards, approvals, certificates	
Suitable for applications according to AMS 2750	Yes; Declaration of Conformity, see online support entry 109757262
Suitable for applications according to 74We 2799	Yes; Based on AMS 2750 E
Ambient conditions	
Ambient temperature during operation	
horizontal installation, min.	0 °C
horizontal installation, max.	60 °C
vertical installation, min.	0 °C
vertical installation, max.	40 °C
Dimensions	

Width	35 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	290 g
Other	
Note:	for the R/RDT three-wire measurement, the conductor compensation is made alternating with the measurement; this then requires two module cycles for a measured value
last modified:	4/29/2021 🖸