

Product type designation

Antenna ANT 30

RF300/RF200/MOBY E antenna ANT 30 PVC, cable length 3 m
 IP65, -25 to +70 °C, M30x 58 mm, max. limit distance: 24mm
 (depending on MDS)



Suitability for operation	RF250R / RF350R / RF350M / MOBY E
Wireless frequencies	
Transmission frequency / Rated value	13.56 MHz
Electrical data	
Type of electrical connection / of the antenna	M8, 4-pin
Design of plug-in connection	male
Mechanical data	
Material	Crastin
Color	Pastel turquoise
Tightening torque / of the screw for securing the equipment / maximum	3 N·m
Mounting distance	0 m
<ul style="list-style-type: none"> relating to metal surfaces / recommended / minimum 	
Permitted ambient conditions	
Ambient temperature	-25 ... +70 °C
<ul style="list-style-type: none"> during operation 	

<ul style="list-style-type: none"> • during storage 	-40 ... +85 °C
<ul style="list-style-type: none"> • during transport 	-40 ... +85 °C
Protection class IP	IP67, front
Shock resistance	according to EN 60721-3-7 Class 7M2
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²

Design, dimensions and weight

Depth	58 mm
Diameter	30 mm
Net weight	180 g
Mounting type	2 plastic nuts M30 x 1.5
Wire length / of antenna cable	3 m

Standards, specifications, approvals

Certificate of suitability	CE, FCC, IC, cULus, Ex approval only together with 6GT2801-4AB10
----------------------------	--

Further Information / Internet Links

Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL <https://support.industry.siemens.com/cs/ww/en/view/67384964>
- to website: Industrial communication <http://www.siemens.com/ident/rfid>
- to website: Industry Mall <https://mall.industry.siemens.com>
- to website: Information and Download Center <http://www.siemens.com/industry/infocenter>
- to website: Image database <http://automation.siemens.com/bilddb>
- to website: CAx Download Manager <http://www.siemens.com/cax>
- to website: Industry Online Support <https://support.industry.siemens.com>

last modified:

01/12/2019