

Fuse monitor T55 380 V to 415 V 3 AC With transparent cap



Model	
Product brand name	SETRON
Product designation	Fuse monitor
Design of the product	Fuse monitor
General technical data	
Response time	50 ms
Size of fuse link	others
Electrical endurance (switching cycles) / typical	1 500 000
Determinants / for climatic applicability / acc. to IEC 60068-1	20/45/4
Voltage	
Surge voltage resistance / rated value	4 000 V
Supply voltage frequency / rated value	
• minimum	50 Hz
• maximum	400 Hz
Main circuit	
Operating voltage / rated value	250 V
Operating current / rated value	4 A

Control supply voltage / at AC / rated value	250 V
--	-------

Accessories

accessories	others
Number of terminals / with cross-head screw	1

Connections

Type of connectable conductor cross-sections	Rigid / max. 2 × 2.5 mm ² ; flexible, with end sleeve min. 1 x 0.5 mm ²
--	---

Environmental conditions

Ambient temperature	
<ul style="list-style-type: none"> • minimum • maximum 	<ul style="list-style-type: none"> -20 °C 45 °C

Certificates

Declaration of Conformity	other
---------------------------	-------



[Environmental Confirmations](#)

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT3170>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT3170>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT3170

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

