SIEMENS

Data sheet 5TT4202-0

switching relay with 2 NO, contact for 230V AC 16A control 230V AC



Figure similar

Model		
Product brand name	SENTRON	
Product designation	Switching relays	
Design of the product	With 2 NO contacts	
Design of the switching function	2 NO	
General technical data		
Operating range factor / of control voltage_1	0.8	
Electrical endurance (switching cycles)	50 000	
Galvanic isolation / between magnet coil and contact	Yes	

Operating range factor / or control voltage_r	0.0
Electrical endurance (switching cycles)	50 000
Galvanic isolation / between magnet coil and contact	Yes
Switching voltage / of the contacts / at AC / minimum	10 V
Switching current / at AC / per contact / minimum	100 mA
Power loss [V•A] / of magnet coil / with pulse / rated	3 V·A
value	

Voltage	
Control voltage / at AC / rated value / maximum	230 V
Surge voltage resistance / rated value	4 kV
Supply voltage	400 V

0 1 1			
Supply voltage	400 \/		
Supply voltage / minimum	400 V		
Type of voltage / of the supply voltage	AC		
Protection class			
Protection class IP	IP20, with connected conductors		
Switching capacity			
Switching capacity apparent power			
 for uncompensated fluorescent lamp load 	400 V·A		
Switching capacity current / at cos phi 0.6	16 A		
Switching capacity active power / with filament lamp load	1 200 W		
Dissipation			
Power loss [W]			
 for rated value of the current / at AC / in hot operating state / per pole 	1 W		
• at 16 A / per contact / rated value	1 W		
• of magnet coil / with pulse / rated value	2.4 W		
Main circuit			
Operating frequency / rated value	50 Hz		
Operating voltage / at AC / rated value / maximum	400 V		
Operating current			
• rated value	16 A		
• at cos phi 0.6 1 / rated value	16 A		
Control current			
Type of voltage			
• of control voltage_1	AC		
Control voltage			
• _1 / initial value	230 V		
• _1 / Full-scale value	230 V		
Control voltage frequency			
• _1 / initial value	50 Hz		
• _1 / Full-scale value	50 Hz		
Operating range factor / of control voltage_2	1.1		
Product function			
Product function / direct operation	Yes		
Inputs Outputs			
Relay design	partially electronic		
Number			
Number of terminals / with cross-head screw	1		

Number of NC contacts	0
Number of NO contacts	2
Number of CO contacts	0

Connections

Connectable conductor cross-section

- for flexible conductor / with core end processing
 - minimum 1 mm²
 - maximum 6 mm²
- for rigid conductor
 - minimum 1 mm²
 - maximum 6 mm²

Mechanical Design	
Width of opening / of the contacts	1.2 mm
Mounting position	any
Installation depth	90 mm
Number of width units	1
Mounting type	DIN rail
Required spacing / for live parts	6 mm

Environmental conditions

Ambient temperature

- minimum -10 °C
- maximum 40 °C

Certificates

General Product Approval	Declaration of	Test Certificates
	Conformity	





Miscellaneous



Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT4202-0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/5TT4202-0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT4202-0

CAx-Online-Generator

http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications

