

product type designation



MDS D560 transponder

transponder MDS D560 for RF200/RF300 Gen2 ISO pill FUJITSU MB89R112, 8192-byte FRAM user memory 16x 3 mm (DxH); minimum order quantity 50 units.

suitability for operation | RF200, RF300

radio frequencies

| | |
|---|--|
| operating frequency / rated value | 13.56 MHz |
| range / maximum | 160 mm; range is reader dependent: observe http://support.automation.siemens.com/WWW/view/en/67384964 |
| protocol / with radio transmission | ISO 15693 |
| transfer rate / with radio transmission / maximum | 26.5 kbit/s |
| product feature / multitag-capable | Yes |

electrical data

| | |
|------------------------------------|----|
| product component / backup battery | No |
|------------------------------------|----|

memory

| | |
|--|---|
| type of memory | FRAM |
| storage capacity / of the user memory | 8192 byte |
| type of memory organization | UID (fixed code) 8 bytes, user memory 8192 bytes, configuration memory 40 bytes |
| number of read cycles / at ambient temperature < 40 °C / maximum | 1000000000000 |
| number of write cycles / at ambient temperature < 40 °C / maximum | 1000000000000 |
| data retention time / at ambient temperature < 40 °C / not less than | 10 y |
| property of memory | Block-by-block write protection of the user memory |
| type of transponder chip used | Fujitsu MB89R112 |

mechanical data


| | |
|--|-------|
| material | PPS |
| color | beige |
| mounting distance / relating to metal surfaces / recommended / minimum | 10 mm |

ambient conditions

| | |
|---|--|
| ambient temperature | -20 ... +85 °C |
| <ul style="list-style-type: none"> during read/write access outside the read/write area during storage | -40 ... +90 °C |
| protection class IP | IP68 |
| shock resistance | According to DIN EN 60721-3-7 Class 7 M3 |
| shock acceleration | 400 m/s ² |
| vibrational acceleration | 100 m/s ² |

design, dimensions and weights

| | |
|--------|------|
| height | 3 mm |
|--------|------|

| | |
|--|---|
| diameter | 16 mm |
| net weight | 3 g |
| fastening method | patching, gluing |
| product features, product functions, product components / general | |
| product feature | |
| • printable | No |
| standards, specifications, approvals | |
| certificate of suitability | |
| • IECEX | No |
| MTBF | 228 y |
| accessories | |
| accessories | Mounting support and spacer |
| further information / internet-Links | |
| Internet-Link | |
| • to web page: selection aid TIA Selection Tool | https://support.industry.siemens.com/cs/ww/en/view/67384964 |
| • to website: Industrial communication | http://www.siemens.com/ident/rfid |
| • to website: Industry Mall | https://mall.industry.siemens.com |
| • to website: Information and Download Center | http://www.siemens.com/industry/infocenter |
| • to website: Image database | http://automation.siemens.com/bilddb |
| • to website: CAx-Download-Manager | http://www.siemens.com/cax |
| • to website: Industry Online Support | https://support.industry.siemens.com |
| last modified: | 11/4/2021  |