

product type designation



RF330T transponder

SIMATIC RF300 Transponder RF330T button, 32 byte FRAM, IP68, -25 to +85 °C, D= 30x 8 mm, in and on metal can be used, minimum order quantity 10 units.

suitability for operation	RF300
radio frequencies	
operating frequency / rated value	13.56 MHz
range / maximum	52 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964
protocol / with radio transmission	RF300-specific
transfer rate / with radio transmission / maximum	106 kbit/s
product feature / multitag-capable	Yes
electrical data	
product component / backup battery	No
memory	
type of memory	FRAM / EEPROM
storage capacity / of the user memory	32765 byte
type of memory organization	UID (fixed code) 4 bytes, user memory 32765 bytes, OTP memory 20 bytes
number of read cycles / at ambient temperature < 40 °C / maximum	1000000000
number of write cycles / at ambient temperature < 40 °C / maximum	1000000000
data retention time / at ambient temperature < 40 °C / not less than	10 y
property of memory	Block-by-block write protection of the OTP memory
mechanical data	
material	PPS
color	black
tightening torque / of the screw for securing the equipment / maximum	1.2 N·m
mounting distance / relating to metal surfaces / recommended / minimum	0 mm
ambient conditions	
ambient temperature	
• during read/write access	-25 ... +85 °C
• outside the read/write area	-40 ... +100 °C
• during storage	-40 ... +100 °C
protection class IP	IP68/IPx9K
shock resistance	According to DIN EN 60721-3-7 Class 7 M3
shock acceleration	500 m/s ²
vibrational acceleration	200 m/s ²
design, dimensions and weights	

height	8 mm
diameter	30 mm
net weight	15 g
fastening method	M4 countersunk screw
product features, product functions, product components / general	
product feature	
• silicon-free	Yes
• printable	No
standards, specifications, approvals	
certificate of suitability	
• IECEx	No
MTBF	1200 y
accessories	
accessories	mounting hood
further information / internet-Links	
Internet-Link	
• to web page: selection aid TIA Selection Tool	https://support.industry.siemens.com/cs/ww/en/view/67384964
• to website: Industrial communication	http://www.siemens.com/ident/rfid
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	6/1/2021 