

product type designation

RF382R reader

SIMATIC RF300 Reader RF382R (ISO scan mode) RS 422/232 interface
IP67, -25 to +70 °C, 160x 80x 41 mm with integrated special antenna .



suitability for operation

RF300 and ISO 15693 Transponder (MDS Dxxx), lateral antenna field, for serial connection to control systems (Scan Mode)

radio frequencies

operating frequency / rated value	13.56 MHz
range / maximum	75 mm; Range adjustable in reader via transmission power, range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964
protocol / with radio transmission	RF300-specific, ISO 15693, ISO 18000-3
transfer rate / with radio transmission / maximum	106 kbit/s
product feature / multitag-capable	No

electrical data

transfer rate / at the point-to-point connection / serial / maximum	115.2 kbit/s
transmission time / for user data <ul style="list-style-type: none"> • for read access / per byte / typical 	0.13 ms

interfaces

standard for interfaces / for communication	RS422/RS232
type of electrical connection	M12, 8-pin

mechanical data

material	PA 12
color	anthracite
mounting distance / relating to metal surfaces / recommended / minimum	0 mm

supply voltage, current consumption, power loss

supply voltage <ul style="list-style-type: none"> • at DC / rated value • at DC 	24 V 20.4 ... 28.8 V
consumed current / at DC <ul style="list-style-type: none"> • at 24 V / typical 	0.16 A

ambient conditions

ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport 	-25 ... +70 °C -40 ... +85 °C -40 ... +85 °C
protection class IP	IP67
shock resistance	EN 60721-3-7 Class 7 M2
shock acceleration	500 m/s ²
vibrational acceleration	200 m/s ²

design, dimensions and weights

width	80 mm
height	41 mm
depth	160 mm
net weight	0.6 kg
fastening method	4 x M5 screws
wire length	
• with RS 232 interface / maximum	30 m
• for RS 422 interface / maximum	1000 m
product features, product functions, product components / general	
display version	3-color LED
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	Radio acc. to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, cULus
certificate of suitability	
• IECEx	No
MTBF	109 y
further information / internet-Links	
Internet-Link	
• to web page: selection aid TIA Selection Tool	https://support.industry.siemens.com/cs/ww/en/view/67384964
• to website: Industrial communication	http://www.siemens.com/ident/rfid
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	12/18/2020 