# **SIEMENS**

## **Data sheet**

## 6GT2811-6AA10-0AA0

### product type designation



### Reader RF680R ETSI

SIMATIC RF600 Reader RF680R ETSI; interface Ethernet M12, PROFINET M12, 4 antennas, 4 dig. inputs/ 4 dig. outputs, 24 V DC; IP65; -25 to +55  $^{\circ}$ C; without accessories and antennas.

suitability for operation

RF600 Transponder, for direct connection to Ethernet, PROFINET, EtherNet/IP or PROFIBUS via communication module, OPC UA server integrated

	integrated	
radio frequencies		
operating frequency	865 868 MHz	
transmit power	3 2000 mW	
effective radiated power		
for each external antenna / maximum	2000 mW	
range / maximum	8 m; Extended ranges possible, see RF600 System Manual, Range table: http://support.automation.siemens.com/WW/view/en/67384964	
protocol / with radio transmission	EPCglobal Class 1 Gen 2 V2 / ISO/IEC 18000-62/-63	
transfer rate / with radio transmission / maximum	400 kbit/s	
product feature / multitag-capable	Yes	
electrical data		
transmission time / for user data		
<ul><li>for write access / per byte / typical</li></ul>	2 ms	
<ul><li>for read access / per byte / typical</li></ul>	0.15 ms	
interfaces		
number of external antennas	4	
standard for interfaces / for communication	Ethernet, PROFINET, OPC UA, EtherNet/IP, RS422	
type of electrical connection		
<ul><li>for external antenna(s)</li></ul>	RP-TNC	
<ul> <li>for supply voltage</li> </ul>	M12, 8-pin, connector	
<ul> <li>for communications interface</li> </ul>	2 x M12 4-pin D-coded, M12 8-pin (RS422)	
at the digital inputs/outputs	M12, 12-pin, female connector	
number of digital inputs	4	
number of digital outputs	4	
mechanical data		
material	Aluminum, Pocan	
color	silver, TI-Grey	
mounting distance / relating to metal surfaces / recommended / minimum	0 mm	
supply voltage, current consumption, power loss		
supply voltage		
<ul><li>at DC / rated value</li></ul>	24 V	
• at DC	20 30 V	
consumed current / at DC		
<ul><li>at 24 V / typical</li></ul>	0.38 A	
• at 24 V / maximum	2 A	

ambient conditions	
ambient temperature	
during operation	-25 +55 °C
during storage	-40 +85 °C
during transport	-40 +85 °C
ambient condition / for operation	With operating temperature below -20 °C: Warming-up time at least 10 minutes
protection class IP	IP65
shock resistance	EN 60068-2-27, EN 60068-2-6
shock acceleration	500 m/s <sup>2</sup>
vibrational acceleration	200 m/s²
resistance to mechanical stress	The maximum stress of shock and vibration acceleration is guaranteed only in combination with the VESA mount
design, dimensions and weights	
width	258 mm
height	258 mm
depth	80 mm
net weight	2.4 kg
fastening method	Vesa 100 with 4 x M4 screws, top-hat rail 35 mm, profile rail S7-300, S7-1200 or S7-1500
wire length	
of antenna wire / minimum	1 m
<ul><li>of antenna wire / maximum</li></ul>	40 m
product features, product functions, product components	/ general
display version	two LED rows with 8 and 9 LEDs
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function / of the PROFINET IO device / is supported / H-Sync forwarding	No
protocol / is supported	
• LLDP	Yes
PROFINET IO protocol	Yes
• TCP/IP	Yes
• SNMP v1	Yes
• SNMP v2	No
SNMP v3	No
• DCP	Yes
EtherNet/IP protocol	Yes
• OPC UA	Yes
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	wireless according to RED directive, CE, IEC 60950, OPC UA: embedded UA Server Profile
certificate of suitability	
• IECEx	No
MTBF	28 y
accessories	
accessories	up to 4 external antennas, set for mounting on top-hat rail or profile rail
further information / internet-Links	
Internet-Link	
to web page: selection aid TIA Selection Tool	https://support.industry.siemens.com/cs/ww/en/view/67384964
to website: Industrial communication	http://www.siemens.com/ident/rfid
to website: Industry Mall	https://mall.industry.siemens.com
to website: Information and Download Center	http://www.siemens.com/industry/infocenter
to website: Image database	http://automation.siemens.com/bilddb
to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	12/18/2020 <b>©</b>