SIEMENS

Product data sheet



CIRCUIT BREAKER 230/400V 10KA, 1-POLE, C, 16A, D=70MM

Similar to image

Technical data:					
Type of mounting		Quick assembly system			
type of voltage		AC/DC			
Height	mm	90			
Width	mm	18			
Depth	mm	76			
mounting position		any			
Mounting depth	mm	70			
Current / for AC / rated value	А	16			
Tripping characteristic class		C			
Supply voltage					
for AC / rated value	V	400			
 with single-phase operation / with AC / rated value 	V	230			
• with multi-phase operation / with AC / rated value	V	400			
Switching capacity current					
• in accordance with IEC 60947-2 / rated value	kA	20			
• with DC / in accordance with IEC 60947-2 / rated value	kA	15			
acc. to EN 60898 / rated value	kA	10			
Breaking capacity short-circuit current (lcn)					


• with DC / in accordance with EN 60898-2	kA	10
• with AC / in accordance with UL 1077 and CSA C22.2 No.235	kA	5
Active power loss / at rated value current / with AC / in warm operating state / per pole	W	1.2
Number of pitch units for width		1
Product feature / sealable		Yes
Degree of pollution		3
Ambient temperature	°C	-25 +55
Ambient temperature		
during storage	°C	-40 +75
Position / of power supply cord	-	Any
Product property / properties for main switches in accordance with EN 60204-1	-	Yes
Mechanical operating cycles as operating time / typical		20,000
Overvoltage class		3
Product equipment / touch-protection		Yes
Resistance against shock / according to IEC 60068-2-27		150m/s ² at 11ms half-sine
Insulation voltage		
 with single-phase operation / with AC / rated value 	V	250
 with multi-phase operation / with AC / rated value 	V	440
AWG number		
 as encoded connectable conductor cross-section 		14 4
Section de conducteur raccordable		
• solid	mm²	0.75 35
• multibrin	mm²	0.75 35
finely stranded		
with wire end processing	mm²	0.75 25
Product component		
combined terminal top		Yes
combined terminal bottom		Yes
Tightening torque		
with screw-type terminals	N∙m	2.5 3
Tightening torque (Ibf-in)		
with screw connection	lbf∙in	22 26
Product feature		
 [not supplied - silicon-free] 		Yes
halogen-free		Yes
Number of test cycles / for environmental testing / in accordance with IEC 60068-2-30		6
Item designation / according to DIN EN 61346-2		F

Certificates/appro	ovals:				
General Product A	Approval				
	GOST		KETI		
Declaration of Conformity	Test Certificates				
EG-Konf.	Special Test Certificate				
Shipping Approva	al				other
BUREAU VERITAS		G L Constant	Llovd's Register LRS	RINA	other
Further informati	on:				
	ownloadcenter (Catalo com/lowvoltage/catalogs				
Industry Mall (Onlin http://www.siemens.org	ne ordering system) com/lowvoltage/mall				
	Manuals, Certificates, (ation.siemens.com/WW/				
	oduct images, 2D dim	ension drawings, 3D		it diagrams,)	

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY4116-7

CAx-Online-Generator

http://www.siemens.com/cax



last change:

Apr 15, 2013