SIEMENS

Product data sheet



CIRCUIT BREAKER 400V 10KA, 2-POLE, C, 2A, D=70MM

Similar to image

Technical data:						
Type of mounting		Quick assembly system				
type of voltage		AC/DC				
Height	mm	90				
Width	mm	36				
Depth	mm	76				
mounting position		any				
Mounting depth	mm	70				
Current / for AC / rated value	А	2				
Tripping characteristic class		С				
Supply voltage						
• for AC / rated value	V	400				
• with multi-phase operation / with AC / rated value	V	400				
Switching capacity current						
• in accordance with IEC 60947-2 / rated value	kA	35				
• with DC / in accordance with IEC 60947-2 / rated value	kA	15				
acc. to EN 60898 / rated value	kA	10				
Breaking capacity short-circuit current (lcn)						
• with DC / in accordance with EN 60898-2	kA	10				

• with AC / in accordance with UL 1077 and CSA C22.2 No.235	kA	5
Active power loss / at rated value current / with AC / in warm operating state / per pole	W	0.9
Number of pitch units for width	_	2
Product feature / sealable	_	Yes
Degree of pollution	_	3
Ambient temperature	°C	-25 +55
Ambient temperature	_	
during storage	°C	-40 +75
Position / of power supply cord	_	Any
Product property / properties for main switches in accordance with EN 60204-1	_	Yes
Mechanical operating cycles as operating time / typical		20,000
Overvoltage class	_	3
Product equipment / touch-protection	_	Yes
Resistance against shock / according to IEC 60068-2-27		150m/s ² at 11ms half-sine
Insulation voltage	_	
• with multi-phase operation / with AC / rated value	V	440
AWG number	_	
 as encoded connectable conductor cross-section 		14 4
Section de conducteur raccordable		
• solid	mm²	0.75 35
• multibrin	mm²	0.75 35
finely stranded		
with wire end processing	mm²	0.75 25
Product component		
combined terminal top		Yes
combined terminal bottom	_	Yes
Tightening torque		
with screw-type terminals	N∙m	2.5 3
Tightening torque (Ibf-in)		
with screw connection	lbf∙in	22 26
Product feature		
[not supplied - silicon-free]		Yes
halogen-free		Yes
Number of test cycles / for environmental testing / in accordance with IEC 60068-2-30		6
Item designation / according to DIN EN 61346-2		F

Certificates/approvals:

General Product Approval					Declaration of Conformity
	GOST				EG-Konf.
Test Certificates	Shipping Approval				
Special Test Certificate	B U R E A U VERITAS		GL	Lloyd's Register	RINA
other					

. . .

other

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)


http://www.siemens.com/lowvoltage/mall


Service&Support (Manuals, Certificates, Characteristics, FAQs,...) http://support.automation.siemens.com/WW/view/en/5SY4202-7/all

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY4202-7

CAx-Online-Generator

http://www.siemens.com/cax





last change:

Apr 15, 2013