

## **MLFB-Ordering data**

6SL3210-5BB17-5UV1



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :	
Consignment no.	:
Project :	

Rated data		General tech. specifications	
Input		Power factor λ	0.72
Number of phases	1 AC	Offset factor $\cos\phi$	0.95
Line voltage	200 240 V -15 % +10 %	Efficiency η	0.98
Line frequency	47 63 Hz	Ambient conditions	
Output		Cooling	convection cooling
Number of phases	3 AC	Installation altitude	1000 m (3281 ft)
Rated voltage	230 V	Ambient temperature	
Rated power (HO)	0.75 kW / 1.00 hp	Operation	-10 60 °C (14 140 °F)
Rated power (LO)	0.75 kW / 0.75 hp	Storage	-40 70 °C (-40 158 °F)
Rated current (HO)	4.20 A	Relative humidity	
Rated current (LO)	4.20 A	Max. operation	95 %
		Communication	
		Communication	USS, Modbus RTU
Pulse frequency	8.00 kHz	Standards	
Output frequency	0 550 Hz	Compliance with standards	CE, cULus, C-Tick (RCM), KC
		CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3

#### **Overload capability**

### Low Overload (LO)

110 % rated output current for 60 s, cycle time 300 s

#### High Overload (HO)

150 % rated output current for 60 s, cycle time 300 s



# **MLFB-Ordering data**

### 6SL3210-5BB17-5UV1



Figure similar

Mechanical data		Connections	
Mounting position Wall mounting / side-by-side mounting		Max. motor cable leng	yth
		Shielded	25 m (82 ft)
Degree of protection IP20 / U	JL open type	Unshielded	50 m (164 ft)
Size FSAB			
Net weight 0.90 kg	ı ( 1.98 lb )		
<b>Width</b> 68.0 m	m ( 2.68 in )		
Height 142.0 r	nm ( 5.59 in )		
<b>Depth</b> 127.8	nm ( 5.03 in )		
Inputs / outputs		]	
tandard digital inputs		_	
Number	4		
Digital outputs			
Number as relay changeover contact	1		
Number as transistor	1		
analog inputs			
Number	2 (Can be used as additional digital input)		
nalog outputs			
Number	1		