

FEATURES

- Better bending / compression strength
- Greater elasticity
- Higher dielectric strength
- Non-flammable
- Resistant to chemicals

RS PRO, 2 Way, 6 AWG, Ceramic Non-Fused Terminal Block, 450V

RS Stock No.: 703-3861



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS PRO, this ceramic bodied non-fused terminal block presents a reliable and cost-effective solution to wire-to-wire connections in high-temperature environments. The terminal block is direct-mount and so does not require the use of a DIN Rail. Instead, it features two galvanized mounting screws that allow mounting to any surface.

General Specifications

Fused	No
Contact Material	Brass
Termination Method	Screw Down
Contact Plating	Nickel
Colour	White
Number of Ways	2
Inserts	Nickel plated bras
Housing	Ceramic (Glazed Option)
Screws	Galvanised Steel
Applications	Thermocouple wiring, External line wiring, Interfacing heater accessories

Electrical Specifications

Current Rating	30A
Voltage Rating	450V



Mechanical Specifications

Cable CSA	16mm²
Wire Size	6 AWG
Height	22mm
Width	27mm
Length	31mm


Operation Environment Specifications

Minimum Operating Temperature	-40°C
Maximum Operating Temperature	500°C (Housing), 350°C (Inserts)
Short-time temperature	800°C

Approvals

Standards Met	CE (BS EN 60998)





RS CODE		CURRENT	RATED VOLTAGE	DIMENSIONS (mm)							
		RANGE		W	L	Φ1	Ф2	D	d	Н	
703-3846	4 mm ²	5-32A	450V	18	21	3.2	4.5	12	8	16	
703-3855	4 mm ²	5-32A	450V	18	33	3.2	4.5	12	8	16	
703-3858	10 mm ²	15-57A	450V	21	24	4.3	4.8	14	10	20	
703-3852	10 mm ²	15-57A	450V	21	36	4.3	4.8	14	10	20	
703-3861	16 mm²	30-76A	450V	27	31	6.1	5.0	17	12	22	
703-3864	16 mm ²	30-76A	450V	27	48	6.1	5.0	17	12	22	
Cross Section:	rated for rigid w i.e. 6mm ² is 4m Ф1 wire entry ho Ф2 fixing hole d	m²) ole diameter	if for flexible wi	ire, it	sho	uld b	e rec	duce	ed on	ie-step,	