Technical Specifications

HP P32u G5 QHD USB-C Monitor




Front

Power Button

2. LED Power

Technical Specifications

HP P32u G5 QHD USB-C Monitor



- 1. Joypad OSD button
- 2. Master Power Switch
- 3. Power Connector
- 4. Security Cable Slot

Back

- 5. HDMI 1.4 Port
- **6.** DisplayPort™ 1.2
- 7. SuperSpeed USB Type-C® 5Gbps signaling rate
- 8. SuperSpeed USB Type-A 5Gbps signaling rate (3)

Technical Specifications

Model: 64W51AA

Panel SpecificationsDisplay Size (Diagonal)31.5 inch

Panel TechnologyIPSMax Refresh Rate75 HzNative Resolution2560 x 1440

Panel Bit Depth8 bitAspect Ratio16:9Brightness (Typical)350 nitsContrast Ratio (Static)1000:1Dynamic Contrast Ratio8M:1

Flicker FreeYes (TÜV certified)Pixel Pitch0.27 mm x 0.27 mm

Pixels Per Inch (PPI) 93 PPI

Display Colors Up to 1.07 billion colors supported

30k

Backlight Lamp Life Minimum (To Half

Brightness - In Hours)

Backlight TypeEdge-litScreen TreatmentAnti-glareHardness3H

Haze 25%

Response Time (Typical) 5ms GtG (with overdrive)

Horizontal Viewing Angle (Typical

Cr>10)

Vertical Viewing Angle (Typical Cr>10) 178°

Panel Active Area Metric (W x H) 69.81 x 39.27 cm

Panel Active Area Metric (W x H) 69.81 x 39.27 cm
Panel Active Area Imperial (W x H) 27.48 x 15.46 in

NOTE: Performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

Color sRGB 99%

Color Management Color Space/ Subsampling Support RGB 4:4:4, YCBCR 4:4:4, YCBCR 4:2:2

RGB Channel Adjust Yes, Gain

Default Color Temperature Standard (6500K)

Monitor Specifications BEZEL TYPE 3-sided borderless

COLOR OF STAND

COLOR OF HEAD

TILT

Height Adjust Range

Black

-5 to +20°

100 mm

Vesa Mounting 100 mm x 100 mm

Security Lock Standard Security Lock Slot

Detachable Stand Yes

Warranty 3/3/0 for LA, NA, EMEA, APJ (3/3/3 in select APJ Countries)

Low Blue Light Yes (TÜV certified)

Speaker Output Power 2 x 2 W

Management Software HP Display Center, HP Display Manager*



Technical Specifications

*Host PC requires Windows 10. HP Display Center is available on

the Microsoft store.

On Screen Display (OSD)

On Screen Display Brightness+, Color, Image, Input, Power, Menu,

Management, Information, Exit

Native Resolution QHD (2560 x 1440)

NOTE: DisplayPort 1.2 & HDMI 1.4 required to drive panel at its

native resolution.

The video card of the connected PC must be capable of

supporting 2560 x 1440 at 60 Hz with 8-bit color using one HDMI

or DP.

Maximum Resolution 2560 x 1440 (QHD)

Preset Graphic Modes/Supported 720 x 400 @ 70Hz Resolutions 640 x 480 @ 60Hz

640 x 480 @ 75Hz(Digital port only)

800 x 600 @ 60Hz

800 x 600 @ 75Hz(Digital port only)

1024 x 768 @ 60Hz

1024 x 768 @ 75Hz(Digital port only)

1280 x 720 @ 60 Hz 1280 x 800 @ 60 Hz 1280 x 1024 @ 60 Hz

1280 x 1024 @ 75 Hz(Digital port only)

1440 x 900 @ 60 Hz 1600 x 900 @ 60 Hz 1680 x 1050 @ 60 Hz 1920 x 1080 @ 75 Hz 1920 x 1200 @ 60 Hz 2560 x 1440 @ 75 Hz

Minimum Vertical Scan Rate 48 Hz **Maximum Vertical Scan Rate** 75 Hz **Minimum Horizontal Scan Rate** 30 KHz **Maximum Horizontal Scan Rate** 120 KHz **Maximum Pixel Clock** 310 MHz **User Programmable Modes** Yes,10

User-Assignable Function Buttons Yes, 4 (7 options) **Audio** Built-in speakers*

*Volume bar will only sync between HP Display Center and OS

when connecting via USB-C cable.

Languages 11(English, French, German, Italian, Dutch, Spanish,

Japanese, Portuguese, Russian, Traditional Chinese, and

Simplified Chinese)

DisplayPort™ 1 DisplayPort™ 1.2 **Connector Types**

HDMI 1 HDMI 1.4

HDCP Yes, DisplayPort and HDMI

USB Type-C® Video Input & Data 1 SuperSpeed USB Type-C® 5Gbps signaling rate (Up to **Transfer** 65W USB Power Delivery, Alt Mode DisplayPort™ 1.2) **USB-A** 3 SuperSpeed USB Type-A 5Gbps signaling rate

Technical Specifications

Specs

Class (ErP LOT-5)

Special Features SWITCH Monitor Power button

> Next Active Input / Up button Brightness / Down button Information / Left button Color / Right button Menu / Enter button

Internal

User Presets 20

Power & Operating Power Supply

> 100 - 240 VAC 50/60 Hz **Power Source**

Power Consumption- Max 160W **Energy Saving/Stand By Mode** 0.5W **Power Consumption - Typical** 35W

Energy Star Data 24W Operational Mode at 100 VAC

Operational Mode at 115 VAC 24W Operational Mode at 230 VAC 24W

EU Energy Efficiency On-mode Power Consumption for 25W

> Standard Dynamic Range (SDR) **ErP LOT5 Energy Efficiency Class for**

Standard Dynamic Range (SDR)

Operating Conditions Operating Temperature - Celsius 5°-35°C

> **Operating Temperature - Fahrenheit** 41° - 95°F Non-Operating Temperature - Celsius -40° - 65°C Non-Operating Temperature --40° - 149°F

Fahrenheit

Operating Humidity 20 - 80% Relative Humidity (non-condensing)

A F G

Non-Operating Humidity 5 - 95%

Operating Altitude 0 – 5,000 m (16,400 ft.) **Non-operating Altitude** 0 - 12,192 m (40,000 ft.)

Certifications and Low Halogen Yes* **Compliances**

*External power supplies, WWAN modules, power cords, cables

and peripherals excluded.

Agency Approvals and Certifications WW application

CE/CB/EUP Lot 6 and Lot 26/Erp/RoHS/TUV-

Bauart/cTUVus/FCC/ ICES/ CEC/Energy Star/TCO/TCO Edge /China CCC/CEL/CECP/SEPA/Korea KC/Korea KCC/Korea e-Standby/VCCI/PSE/RCM/Australia MEPS/India BIS/Taiwan BSMI/Mexico NOM/Mexico energy/South Africa NRCS LoA and energy/Argentina S-

Mark/Singapore PSB/Cambodia ISC/EAC/EAEU

RoHS/UAE/UAE RoHS/ ISO 9241-307/Low blue light/ Flicker Free/Vietnam MEPS/Ukraine Energy/ Ukraine CoC

Microsoft WHQL Certification Win 11, Win 10, Win 8, Win 7

ENERGY STAR® Certified Yes

EPEAT® Registered

EPEAT® registered* Regions need to verify by country



*Based on US EPEAT® registration according to IEEE 1680.1-

QuickSpecs

Technical Specifications

	China Energy Label	*Based on US EPEA1* registrat 2018 EPEAT*. Status varies by http://www.epeat.net for mo CEL Grade 1	country. Visit	
	TCO Certified Edge	Yes		
	TCO Certified	Yes		
	SmartWay Transport Partnership - NA only	Yes (NA sku)		
Contains Recycled Plastics	Contains Recycled Plastics	85% ITE-derived closed loop plastic* *Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard. Outside Box and corrugated cushions are 100%		
	Recyclable Packaging (Box, packing			
	materials)	sustainably sourced and recyclable * *100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.		
		<u>Metric</u>	<u>Imperial</u>	
Unit Product/Package Specifications	Product Dimensions (Unpacked with stand) (W x D x H)	71.44 x 22.53 x 56.97 cm	28.13 x 8.87 x 22.43 in	
	Product Dimensions (Packed) (W x D x H)	82.8 x 16.3 x 52.4 cm	32.6 x 6.42x 20.63 in	
	Display Head Dimensions (Unpacked without stand) (W x D x H)	71.44 x 5.4 x 42.2 cm	28.13 x 2.13 x 16.69 in	
	Base Area Footprint (w x d mm)	195.9 x 213 mm	7.71 x 8.39 in	
	Bezel Measurements (Unpacked with stand) (W x D x H)	Bottom 22.3 mm	Bottom 0.88	
	Product Weight (Unpacked with stand)	8.29 kg	18.28 lb	
	Product Weight (Packed)	11.66 kg	25.71 lb	
	Product Weight (Head Only)	6.8 kg	14.99 lb	
Pallet Information	Pallet Dimensions	Slip Sheet:	Slip Sheet:	
	(L x W x H mm)	1153 x 837 x 2111 mm (20 ft & 40 ft & 40 HQ) Pallet: 1150 x 385 x 2239 mm	45.39 x 32.95 x 83.11 inch (20 ft & 40 ft & 40 HQ) Pallet: 45.28 x15.16 x 88.15 inch	
	Pallet Total Weight	(20 ft & 40 ft & 40 HQ) Slip Sheet: 330 kg (20 ft & 40 ft & 40 HQ) Pallet: 350 kg (20 ft & 40 ft & 40 HQ)	(20 ft & 40 ft & 40 HQ) Slip Sheet: 728 lb (20 ft & 40 ft & 40 HQ) Pallet: 772 lb (20 ft & 40 ft & 40 HQ)	
	Pallet Layers	7 layers per pallet		
	Pallet Product per Layer	4 per layer (slip sheet & pall	et)	



Technical Specifications

Total Products per Pallet Container Load, 20-Foot Container Load, 40-Foot Container Load, 40-Foot HighQ 28 sets (slip sheet & pallet) 392 sets (slip sheet and pallet) 784 sets (slip sheet and pallet) 784 sets (slip sheet and pallet)

Vietnamese (VI)

What's in the box?

AC power cord (1.83m) 6 ft USB 3.1 C-C cable (1.8m) 5.9ft QUICK SETUP POSTER

Doc kit Warranty card

User Guide and Warranty Languages **User Guide Languages**

Warranty Languages

Arabic, Bahasa Indonesia, Bulgarian, Chinese-S, Chinese-T, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hebrew, Hungarian, Italian, Japanese, Kazakh, Korean, Latvian, Lithuanian, Norwegian, Polish, Portuguese (Brazilian), Portuguese (Iberian), Romanian, Russian, Serbian, Slovak, Slovenian, Spanish, Swedish, Thai, Turkey, Ukrainian English US (EN), English AP (EN-AP), English LA (EN-LA), English UK (EN-GB), Arabic (AR) -17x, Bahasa Indonesia (ID), Bosnian (BS), Bulgarian (BG), Chinese-S (CN), Chinese-T (TW), Croatian (HR), Czech (CS), Danish (DA), Dutch (NL), Estonian (ET), Finnish (FI), French Canadian (FC), French European (FR), German (DE), Greek (EL), Hebrew (HE), Hungarian (HU), Italian (IT), Japanese (JA), Kazakh (KK), Korean (KO), Latvian (LV), Lithuanian (LT), Norwegian (NO), Polish (PL), Portuguese, Brazilian (BR), Portuguese, Iberian (PT), Romanian (RO), Russian (RU), Serbian (SR), Slovak (SK), Slovenian (SL), Spanish, Castilian (ES-ES), Spanish, Latin America (ES-MX), Swedish (SV), Thai (TH), Turkish (TR), Ukrainian (UK),

Technical Specifications

ENVIRONMENTAL DATA

ENVIRONMENTAL DATA				
Eco-Label Certifications	This product has received	or is in the process of being	g certified to the following approvals and may be	
& declarations	labeled with one or more of these marks:			
	IT ECO declaration			
	US ENERGY STAR®			
	US Federal Energy Management Program (FEMP)			
	EPEAT® Gold registered in the United States. See http://www.epeat.net for registration			
	status in your cou	-		
	TCO Certified Edge			
	China Energy Conservation Program (CECP)			
	China State Environmental Protection Administration (SEPA)			
	Taiwan Green Mark			
	Korea Eco-label	114		
	Japan PC Green label*			
Sustainable Impact	• 85% ITE – derived closed	loop plastic		
Specifications	• 75% recycled metal • Low halogen			
	Recycled Plastic cushions	Outside Box and corrugated cushions are 100% sustainably sourced and recyclable Described Blacking such in a second such in the second s		
System Configuration			and Doclared Noise Emissions data for the	
System Configuration	The configuration used for the Energy Consumption and Declared Noise Emissions data for the Notebook model is based on a "Typically Configured Notebook".			
	Notebook model is based (on a Typically Configured	Hotebook .	
Energy Consumption				
(in accordance with US				
ENERGY STAR® test	445046 600	220114 5 7011	1001105 7011	
Mermal Operation (Chart	115VAC, 60Hz 22.99 W	230VAC, 50Hz 23.01 W	100VAC, 50Hz 22.89 W	
Normal Operation (Short idle)				
Normal Operation (Long idle)	22.99 W	23.01 W	22.89 W	
Sleep	0.29 W	0.3 W	0.28 W	
Off	0.23 W	0.24 W	0.22 W	
	family. HP computers mar Environmental Protection family does not offer ENER	ked with the ENERGY STAR Agency (EPA) ENERGY STA RGY STAR® compliant confi PC featuring a hard disk dri	compliant product if offered within the model Logo are compliant with the applicable U.S. R® specifications for computers. If a model gurations, then energy efficiency data listed is ve, a high efficiency power supply, and a	
Heat Dissipation*	115VAC, 60Hz	230VAC, 50Hz	100VAC, 50Hz	
Normal Operation (Short idle)	78.6 BTU/hr	78.7 BTU/hr	78.3 BTU/hr	
Normal Operation (Long idle)	78.6 BTU/hr	78.7 BTU/hr	78.3 BTU/hr	
Sleep	1.0 BTU/hr	1.0 BTU/hr	1.0 BTU/hr	
Off	0.8 BTU/hr	0.8 BTU/hr	0.8 BTU/hr	
	*NOTE: Heat dissipation is attained for one hour.	calculated based on the m	easured watts, assuming the service level is	

Technical Specifications

Longevity and Upgrading	This product can be upgraded, possibly extending its useful life by several years. Upgradeable		
Longevity and opgrading	features and/or components contained in the		
	·		
	Spare parts are available throughout the warranty period and or for up to "5" years after the end of		
	production.		
Additional Information	This product is in compliance with the Restrictions of Hazardous Substances (RoHS) directive		
	- 2011/65/EC.		
	This HP product is designed to comply with the Waste Electrical and Electronic Equipment		
	(WEEE) Directive – 2002/96/EC.		
	 This product is in compliance with California Proposition 65 (State of California; Safe Drinking Water and Toxic Enforcement Act of 1986). 		
		product is in compliance with the IEEE 1680 (EPEAT) stand	lard at the Gold level, see
		v.epeat.net	
		tics parts weighing over 25 grams used in the product are	marked per ISO11469 and
		043. product is 96.9% recycle-able when properly disposed of a	at and of life
	11115	product is 30.3% recycle-able when property disposed of	at end of the.
Packaging Materials	External:	PAPER/Corrugated	2925 g
	Internal:	PLASTIC/EPE (Expanded Polyethylene)	39 g
		PLASTIC/LDPE(Polyethylene high density)	4 g
	The plastic packaging material contains at least 0.0% recycled content.		
RoHS Compliance		ted paper packaging materials contains at least 90% recyc lies fully with materials regulations. We were among the fi	
	restrictions in the European Union (EU) Restriction of Hazardous Substances (RoHS) Directive to our products worldwide through the HP GSE. HP has contributed to the development of related legislation in Europe, as well as China, India, and Vietnam. We believe the RoHS directive and similar laws play an important role in promoting industry-wide elimination of substances of concern. We have supported the inclusion of additional substances—including PVC, BFRs, and certain phthalates—in future RoHS legislation that pertains to electrical and electronics products.		
	We met our voluntary objective to achieve worldwide compliance with the new EU RoHS requirements for virtually all relevant products by July 2013, and we will continue to extend the scope of the commitment to include further restricted substances as regulations continue to evolve.		
	To obtain a copy of the HP RoHS Compliance Statement, see HP RoHS position statement.		
Material Usage	This product does not contain any of the following substances in excess of regulatory limits (refer to the HP General Specification for the Environment at http://www.hp.com/hpinfo/globalcitizenship/environment/supplychain/gen_specifications.html):		
	 Asbestos Certain Azo Colorants Certain Brominated Flame Retardants – may not be used as flame retardants in plastics Cadmium Chlorinated Hydrocarbons Chlorinated Paraffins Bis(2-Ethylhexyl) phthalate (DEHP) Benzyl butyl phthalate (BBP) Dibutyl phthalate (DBP) Diisobutyl phthalate (DIBP) Formaldehyde 		



Technical Specifications

	Halogenated Diphenyl Methanes
	Lead carbonates and sulfates
	Lead and Lead compounds
	Mercuric Oxide Batteries
	Nickel – finishes must not be used on the external surface designed to be frequently
	handled or carried by the user.
	Ozone Depleting Substances
	Polybrominated Biphenyls (PBBs)
	Polybrominated Biphenyl Ethers (PBBEs)
	Polybrominated Biphenyl Oxides (PBBOs)
	Polychlorinated Biphenyl (PCB)
	Polychlorinated Terphenyls (PCT)
	Polyvinyl Chloride (PVC) — except for wires and cables, and certain retail packaging has been
	voluntarily removed from most applications.
	Radioactive Substances
	Tributyl Tin (TBT), Triphenyl Tin (TPT), Tributyl Tin Oxide (TBTO)
	- modely thir (1517), implicitly thir (1117), impactly thir oxide (1516)
Packaging Usage	HP follows these guidelines to decrease the environmental impact of product packaging:
	Eliminate the use of heavy metals such as lead, chromium, mercury and cadmium in
	packaging materials.
	Eliminate the use of ozone-depleting substances (ODS) in packaging materials.
	Design packaging materials for ease of disassembly.
	Reduce size and weight of packages to improve transportation fuel efficiency. Reduce size and weight of packages to improve transportation fuel efficiency.
	Plastic packaging materials are marked according to ISO 11469 and DIN 6120 standards.
End-of-life Management	HP offers end-of-life HP product return and recycling programs in many geographic areas. To recycle
and Recycling	your product, please go to: http://www.hp.com/go/reuse-recycle or contact your nearest HP sales
and necycling	office. Products returned to HP will be recycled, recovered or disposed of in a responsible manner.
	officer routers returned to the wild be recycled, recovered of disposed of in a responsible manner.
	The EU WEEE directive (2002/95/EC) requires manufacturers to provide treatment information for
	each product type for use by treatment facilities. This information (product disassembly
	instructions) is posted on the Hewlett Packard web site at: http://www.hp.com/go/recyclers. These
	instructions may be used by recyclers and other WEEE treatment facilities as well as HP OEM
	customers who integrate and re-sell HP equipment.
HP, Inc. Corporate	For more information about HP's commitment to the environment:
Environmental	
Information	Global Citizenship Report
	http://www.hp.com/hpinfo/globalcitizenship/gcreport/index.html
	Eco-label certifications
	http://www8.hp.com/us/en/hp-information/environment/ecolabels.html
	ISO 14001 certificates:
	http://h20195.www2.hp.com/V2/GetDocument.aspx?docname=c04755842
	and
	http://www.hp.com/hpinfo/globalcitizenship/environment/pdf/cert.pdf

Technical Specifications

footnotes

- Percentage of ocean-bound plastic contained in each component varies by product
- Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.
- External power supplies, WWAN modules, power cords, cables and peripherals excluded.
- 100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.
- Fiber cushions made from 100% recycled wood fiber and organic materials.
- Plastic cushions are made from >90% recycled plastic.
- Recycled metal is expressed as a percentage of the total weight of the metal according to ISO 14021 definitions for metal parts over 25 grams

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are registered trademarks or trademarks of Microsoft Corporation in the U.S. and/or other countries. ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency.



Summary

Change Log		
	V1 to V2	

