**Technical Specifications** 

### **HP P27 G5 FHD Monitor**




1. Power Button

**Front** 

2. LED Power

### **Technical Specifications**

### **HP P27 G5 FHD Monitor**



- 1. Joypad OSD button
- 2. Security Cable Slot
- 3. Power Connector

#### Back

- 4. DisplayPort<sup>™</sup> 1.2
- **5.** HDMI 1.4 Port
- 6. VGA Port

#### **Technical Specifications**

Model: 64X69AA

Panel SpecificationsDisplay Size (Diagonal)27 inchPanel TechnologyIPS

Max Refresh Rate 75Hz

Native ResolutionFHD (1920 x 1080)Panel Bit Depth8 bit (6 bit + FRC)

Aspect Ratio16:9Brightness (Typical)250 nitsContrast Ratio (Static)1000:1Dynamic Contrast Ratio8M:1

Flicker FreeYes (TÜV certified)Pixel Pitch0.31 x 0.31Pixels Per Inch (PPI)82 PPI

**Display Colors** Up to 16.7 million colors supported

30

**Backlight Lamp Life Minimum (To Half** 

Brightness - In Hours)

Backlight Type Edge-lit
Screen Treatment Anti-glare
Hardness 3H

Haze 25%
Response Time (Typical) 5ms GtG (with overdrive)

**Horizontal Viewing Angle (Typical** 

Cr>10)

Vertical Viewing Angle (Typical Cr>10) 178°

Panel Active Area Metric (W x H) 59.79 x 33.61 cm Panel Active Area Imperial (W x H) 23.54 x 13.23 in

**NOTE:** Performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

Color NTSC 72%

Color Management Color Space/ Subsampling Support RGB 4:4:4, YCBCR 4:4:4, YCBCR 4:2:2

**RGB Channel Adjust** Yes, Gain

**Default Color Temperature** Standard (6500K)

Monitor Specifications Bezel Type 3-sided borderless

 Color Of Stand
 Black

 Color Of Head
 Black

 Tilt
 Yes, -5~+20°

 Vesa Mounting
 100 mm x 100 mm

Security Lock Standard Security Lock Slot

**Detachable Stand** Yes

Warranty 3/3/0 for LA, NA, EMEA, APJ (3/3/3 in select APJ Countries)

**Low Blue Light** Yes (TÜV certified)

Management Software HP Display Center, HP Display Manager\*

\*Host PC requires Windows 10. HP Display Center is available on

the Microsoft store.

#### **Technical Specifications**

On Screen	Display
(OSD)	

**On Screen Display** Brightness+, Color, Image, Input, Power, Menu,

Management, Information, Exit

**Native Resolution** FHD (1920 x 1080)

NOTE: DisplayPort 1.2 & HDMI 1.4 required to drive panel at its

native resolution.

The video card of the connected PC must be capable of

supporting 1920x1080 at 60 Hz with 8-bit color using one HDMI

or VGA.

**Maximum Resolution** 

**Preset Graphic Modes/Supported** Resolutions

1920 x 1080 (FHD) 640 x 480 @ 60Hz 640 x 480 @ 75Hz 720 x 400 @ 70 Hz 800 x 600 @ 60 Hz 800 x 600 @ 75 Hz 1024 x 768 @ 60 Hz

1024 x 768 @75 Hz 1280 x 720 @ 60 Hz 1280 x 800 @ 60 Hz 1280 x 1024 @ 60 Hz 1280 x 1024 @ 75 Hz 1440 x 900 @ 60 Hz 1600 x 900 @ 60 Hz 1680 x 1050 @ 60 Hz 1920 x 1080 @ 60 Hz

1920 x 1080 @ 75 Hz

**Minimum Vertical Scan Rate** 48 Hz **Maximum Vertical Scan Rate** 75 Hz **Minimum Horizontal Scan Rate** 30.0 kHz **Maximum Horizontal Scan Rate** 86.0 kHz **Maximum Pixel Clock** 180.0 MHz **User Programmable Modes** Yes, 10

**User-Assignable Function Buttons** Yes, 4 (6 options)

11 (English, Spanish, German, French, Italian,

Languages Netherlands, Portuguese, Japanese, T-Chinese, S-Chinese

and Russian)

**Connector Types** 

DisplayPort™ 1 DisplayPort™ 1.2

**HDMI** 1 HDMI 1.4

**HDCP** Yes, DisplayPort and HDMI

**VGA** 1 VGA

**Special Features** 

**SWITCH Monitor Power button** 

> Next Active Input / Up button Brightness / Down button Information / Left button Color / Right button

Menu / Enter button

**User Presets** 11 (VGA) / 16 (HDMI and DP)

#### **Technical Specifications**

Power & Operating Power Supply Internal

**Specs Power Source** 100 – 240 VAC 50/60 Hz

Power Consumption- Max35 WEnergy Saving/Stand By Mode0.5 WPower Consumption - Typical25 W

Energy Star Data Operational Mode at 100 VAC 15.7W

Operational Mode at 115 VAC 15.7W
Operational Mode at 230 VAC 15.7W

EU Energy Efficiency On-mode Power Consumption for Class (ErP LOT-5) Standard Dynamic Range (SDR)

Standard Dynamic Range (SDR)

ErP LOT5 Energy Efficiency Class for

Standard Dynamic Range (SDR)

Operating Conditions Operating Temperature - Celsius  $5^{\circ} - 35^{\circ}$ C Operating Temperature - Fahrenheit  $41^{\circ} - 95^{\circ}$ F

Non-Operating Temperature - Celsius  $-40^{\circ} - 65^{\circ}$ C Non-Operating Temperature -  $-40^{\circ} - 149^{\circ}$ F

**Fahrenheit** 

**Operating Humidity** 20 – 80% Relative Humidity (non-condensing)

20

Non-Operating Humidity 5 – 95%

Operating Altitude 0-5,000 m (16,400 ft.)Non-operating Altitude 0-12,192 m (40,000 ft.)

Certifications and Compliances

Low Halogen Yes\*

\*External power supplies, WWAN modules, power cords,

cables and peripherals excluded.

**Agency Approvals and Certifications** WW application

UAE/EUP Lot6 and Lot26/ Eup Lot5/ Energy Star/ TCO
Edge/ TCO/ Australia MEPS/ Vietnam MEPS/ CEC/ Bauart/
China CCC/ cTUVus/ Korea KC/ Korea KCC/ Korea eStandby/ CB(62368-1&60950)/ ISO9241-307/
CE/FCC/VCCI/RCM/C-TICK/IC/ India BIS/ Taiwan BSMI/
Mexico NOM/ South Africa Energy Efficiency/ Argentina SMark/ Singapore PSB/ Cambodia ISC/ EAC//Mexico Energy

/CEL/Ukraine(DOC&COC)/NRCS/Ukraine energy

Microsoft WHQL Certification Win 11, Win 10, Win 8, Win 7

ENERGY STAR® Certified

EPEAT® Registered

EPEAT® registered\*

Regions need to verify by country

\*Based on US EPEAT® registration according to IEEE 1680.1-2018 EPEAT®. Status varies by country. Visit

http://www.epeat.net for more information.

China Energy LabelCEL Grade 2TCO Certified EdgeYes

TCO Certified Yes

SmartWay Transport Partnership - NA only Yes (NA sku)

### **Technical Specifications**

Contains Recycled Plastics	Contains Recycled Plastics  Recyclable Packaging (Box, packing materials)	85% ITE-derived closed loop plastic*  *Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.  Molded Paper Pulp Cushion inside box is 100% sustainably sourced and recyclable*  *100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.	
		<u>Metric</u>	<u>Imperial</u>
Unit Product/Package Specifications	Product Dimensions (Unpacked with stand) (W x D x H)	61.1 x 19.03 x 43.84 cm	24.05 x 7.49 x 17.25 in
Specifications	Product Dimensions (Packed) (W x D x H)	68.5 x 13.7 x 42.5 cm	26.97 x 5.39 x 16.73 in
	<b>Display Head Dimensions</b> (Unpacked without stand) (W $\times$ D $\times$ H)	61.1 x 5.71 x 36.55 cm	24.05 x 2.25 x 14.39 in
	Base Area Footprint (w x d mm)	178 x 180 mm	7.00 x 7.08 in
	<b>Bezel Measurements</b> (Unpacked with stand) (W x D x H)	Bottom: 21.7 mm	Bottom: 0.85 in
	Product Weight (Unpacked with stand)	5.08 kg	11.19 lb
	Product Weight (Packed)	7.64 kg	16.85 lb
	Product Weight (Head Only)	4.43 kg	9.77 lb
Pallet Information	Pallet Dimensions	Slip Sheet:	Slip Sheet:
	(L x W x H mm)	1106 x 695 x 2150 mm (20ft & 40ft & 40HQ) Pallet: 1106 x 695 x 2250 mm (20ft & 40ft & 40HQ)	43.54 x 27.36 x 84.65 inch (20ft & 40ft & 40HQ) Pallet: 43.54 x 27.36 x 88.58 inch (20ft & 40ft & 40HQ)
	Pallet Total Weight	Slip Sheet: 305.6kg (20ft & 40ft & 40HQ) Pallet: 313.6kg (20ft & 40ft & 40HQ)	Slip Sheet: 673.9 (20ft & 40ft & 40HQ) Pallet: 691.6 (20ft & 40ft & 40HQ)
	Pallet Layers	5 layers per pallet	
	Pallet Product per Layer Total Products per Pallet	8 per layer	
	Container Load, 20-Foot	40 sets per pallet (40 ft) 640 sets (slip sheet and palle	ot)
	Container Load, 40-Foot	1360 sets (slip sheet and pall	
	Container Load, 40-Foot HighQ	1360 sets (slip sheet & pallet	
What's in the box?	AC power cord (1.83m) 6 ft VGA cable (1.8m) 5.9 ft (Japan Only)		



#### **Technical Specifications**

DP cable (1.8m) 5.9 ft (Japan and EMEA AF SKUs Only) HDMI 1.4 cable (1.8m) 5.9ft Warranty Doc kit Quick Setup Poster

User Guide and Warranty Languages

**User Guide Languages** 

**Warranty Languages** 

Arabic, Bahasa Indonesia, Bulgarian, Chinese-S, Chinese-T, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hebrew, Hungarian, Italian, Japanese, Kazakh, Korean, Latvian, Lithuanian, Norwegian, Polish, Portuguese (Brazilian), Portuguese (Iberian), Romanian, Russian, Serbian, Slovak, Slovenian, Spanish, Swedish, Thai, Turkey, Ukrainian English US (EN), English AP (EN-AP), English LA (EN-LA), English UK (EN-GB), Arabic (AR) -17x, Bahasa Indonesia (ID), Bosnian (BS), Bulgarian (BG), Chinese-S (CN), Chinese-T (TW), Croatian (HR), Czech (CS), Danish (DA), Dutch (NL), Estonian (ET), Finnish (FI), French Canadian (FC), French European (FR), German (DE), Greek (EL), Hebrew (HE), Hungarian (HU), Italian (IT), Japanese (JA), Kazakh (KK), Korean (KO), Latvian (LV), Lithuanian (LT), Norwegian (NO), Polish (PL), Portuguese, Brazilian (BR), Portuguese, Iberian (PT), Romanian (RO), Russian (RU), Serbian (SR), Slovak (SK), Slovenian (SL), Spanish, Castilian (ES-ES), Spanish, Latin America (ES-MX), Swedish (SV), Thai (TH) Turkish (TR), Ukrainian (UK), Vietnamese (VI)

### **Technical Specifications**

#### **ENVIRONMENTAL DATA**

ENVIRONMENTAL DATA	l .		
<b>Eco-Label Certifications</b>			g certified to the following approvals and may be
& declarations	labeled with one or more of these marks:		
	IT ECO declaration		
	US ENERGY STAR®		
	US Federal Energy Management Program (FEMP)		
	<ul> <li>EPEAT® Gold registered in the United States. See http://www.epeat.net for registration</li> </ul>		
	status in your cou	-	
	TCO Certified Edg		
		servation Program (CECP)	oisturation (CEDA)
China State Environmental Protection Administration (SEPA			nistration (SEPA)
	Taiwan Green Mark		
<ul> <li>Korea Eco-label</li> <li>Japan PC Green label*</li> </ul>			
	·		
Sustainable Impact	• 85% ITE – derived closed	loop plastic	
Specifications	<ul> <li>Low halogen</li> <li>Outside Box and corrugated cushions are 100% sustainably sourced and recyclable</li> </ul>		
			ainably sourced and recyclable
	Recycled Plastic cushions		amably sourced and recyclable
System Configuration			and Declared Noise Emissions data for the
<b>3</b>	Notebook model is based on a "Typically Configured Notebook".		
Energy Consumption			
(in accordance with US			
ENERGY STAR® test			
method)	115VAC, 60Hz	230VAC, 50Hz	100VAC, 50Hz
Normal Operation (Short idle)	14.97 W	15.04 W	15.1 W
Normal Operation (Long idle)	14.97 W	15.04 W	15.1 W
Sleep	0.13 W	0.15 W	0.13 W
Off	0.1 W	0.12 W	0.09 W
	family. HP computers mar Environmental Protection family does not offer ENER	ked with the ENERGY STAR Agency (EPA) ENERGY STA RGY STAR® compliant confi PC featuring a hard disk dri	compliant product if offered within the model Logo are compliant with the applicable U.S. Specifications for computers. If a model gurations, then energy efficiency data listed is ve, a high efficiency power supply, and a
Heat Dissipation*	115VAC, 60Hz	230VAC, 50Hz	100VAC, 50Hz
Normal Operation (Short idle)	51.2 BTU/hr	51.4 BTU/hr	51.6 BTU/hr
Normal Operation (Long idle)	51.2 BTU/hr	51.4 BTU/hr	51.6 BTU/hr
Sleep	0.4 BTU/hr	0.5 BTU/hr	51.6 BTU/hr
Off	0.3 BTU/hr	0.4 BTU/hr	51.6 BTU/hr
	*NOTE: Heat dissipation is attained for one hour.	calculated based on the m	easured watts, assuming the service level is

## **Technical Specifications**

Longevity and Upgrading	This product can be upgraded, possibly extending its useful life by several years. Upgradeable features and/or components contained in the		
	Spare parts are available throughout the warranty period and or for up to "5" years after the end of production.		
Additional Information	<ul> <li>This product is in compliance with the Restrictions of Hazardous Substances (RoHS) directive - 2011/65/EC.</li> <li>This HP product is designed to comply with the Waste Electrical and Electronic Equipment (WEEE) Directive – 2002/96/EC.</li> <li>This product is in compliance with California Proposition 65 (State of California; Safe Drinking Water and Toxic Enforcement Act of 1986).</li> <li>This product is in compliance with the IEEE 1680 (EPEAT) standard at the Gold level, see www.epeat.net</li> <li>Plastics parts weighing over 25 grams used in the product are marked per IS011469 and IS01043.</li> <li>This product is 98.9% recycle-able when properly disposed of at end of life.</li> </ul>		
Packaging Materials	External:	PAPER/Paperboard	793 g
		PAPER/Molded Pulp	1206 g
	Internal:	PLASTIC/EPE (Expanded Polyethylene)	30 g
	The plastic packaging material contains at least 0.0% recycled content.		t.
		ted paper packaging materials contains at least 90% recy	
ROHS Compliance	HP Inc. complies fully with materials regulations. We were among the first companies to extend the restrictions in the European Union (EU) Restriction of Hazardous Substances (RoHS) Directive to our products worldwide through the HP GSE. HP has contributed to the development of related legislation in Europe, as well as China, India, and Vietnam.  We believe the RoHS directive and similar laws play an important role in promoting industry-wide elimination of substances of concern. We have supported the inclusion of additional substances—including PVC, BFRs, and certain phthalates—in future RoHS legislation that pertains to electrical and electronics products.  We met our voluntary objective to achieve worldwide compliance with the new EU RoHS requirements for virtually all relevant products by July 2013, and we will continue to extend the scope of the commitment to include further restricted substances as regulations continue to evolve.  To obtain a copy of the HP RoHS Compliance Statement, see HP RoHS position statement.		
Material Usage	This product does not contain any of the following substances in excess of regulatory limits (refer to the HP General Specification for the Environment at http://www.hp.com/hpinfo/globalcitizenship/environment/supplychain/gen_specifications.html):		
	<ul> <li>Cert</li> <li>Cert</li> <li>Cadi</li> <li>Chlo</li> <li>Chlo</li> <li>Bis()</li> <li>Ben</li> <li>Dibt</li> </ul>	estos ain Azo Colorants ain Azo Colorants ain Brominated Flame Retardants – may not be used as fl mium orinated Hydrocarbons orinated Paraffins 2-Ethylhexyl) phthalate (DEHP) zyl butyl phthalate (BBP) utyl phthalate (DBP) obutyl phthalate (DBP)	ame retardants in plastics



## **Technical Specifications**

	<ul> <li>Formaldehyde</li> <li>Halogenated Diphenyl Methanes</li> <li>Lead carbonates and sulfates</li> <li>Lead and Lead compounds</li> <li>Mercuric Oxide Batteries</li> <li>Nickel – finishes must not be used on the external surface designed to be frequently handled or carried by the user.</li> <li>Ozone Depleting Substances</li> <li>Polybrominated Biphenyls (PBBs)</li> <li>Polybrominated Biphenyl Ethers (PBBEs)</li> <li>Polybrominated Biphenyl Oxides (PBBOs)</li> <li>Polychlorinated Biphenyl (PCB)</li> <li>Polychlorinated Terphenyls (PCT)</li> <li>Polyvinyl Chloride (PVC) – except for wires and cables, and certain retail packaging has been voluntarily removed from most applications.</li> <li>Radioactive Substances</li> <li>Tributyl Tin (TBT), Triphenyl Tin (TPT), Tributyl Tin Oxide (TBTO)</li> </ul>
Packaging Usage	<ul> <li>HP follows these guidelines to decrease the environmental impact of product packaging:</li> <li>Eliminate the use of heavy metals such as lead, chromium, mercury and cadmium in packaging materials.</li> <li>Eliminate the use of ozone-depleting substances (ODS) in packaging materials.</li> <li>Design packaging materials for ease of disassembly.</li> <li>Maximize the use of post-consumer recycled content materials in packaging materials.</li> <li>Use readily recyclable packaging materials such as paper and corrugated materials.</li> <li>Reduce size and weight of packages to improve transportation fuel efficiency.</li> <li>Plastic packaging materials are marked according to ISO 11469 and DIN 6120 standards.</li> </ul>
End-of-life Management and Recycling	HP offers end-of-life HP product return and recycling programs in many geographic areas. To recycle your product, please go to: http://www.hp.com/go/reuse-recycle or contact your nearest HP sales office. Products returned to HP will be recycled, recovered or disposed of in a responsible manner.  The EU WEEE directive (2002/95/EC) requires manufacturers to provide treatment information for each product type for use by treatment facilities. This information (product disassembly instructions) is posted on the Hewlett Packard web site at: http://www.hp.com/go/recyclers. These instructions may be used by recyclers and other WEEE treatment facilities as well as HP OEM customers who integrate and re-sell HP equipment.
HP, Inc. Corporate Environmental Information	For more information about HP's commitment to the environment:  Global Citizenship Report     http://www.hp.com/hpinfo/globalcitizenship/gcreport/index.html Eco-label certifications     http://www8.hp.com/us/en/hp-information/environment/ecolabels.html ISO 14001 certificates:     http://h20195.www2.hp.com/V2/GetDocument.aspx?docname=c04755842     and     http://www.hp.com/hpinfo/globalcitizenship/environment/pdf/cert.pdf



#### **Technical Specifications**

## footnotes

- Percentage of ocean-bound plastic contained in each component varies by product
- Recycled plastic content percentage is based on the definition set in the IEEE 1680.1-2018 standard.
- External power supplies, WWAN modules, power cords, cables and peripherals excluded.
- 100% outer box packaging and corrugated cushions made from sustainably sourced certified and recycled fibers.
- Fiber cushions made from 100% recycled wood fiber and organic materials.
- Plastic cushions are made from >90% recycled plastic.

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Microsoft and Windows are registered trademarks or trademarks of Microsoft Corporation in the U.S. and/or other countries. ENERGY STAR is a registered trademark owned by the U.S. Environmental Protection Agency.



Summary

Change Log			
	V1 to V2		

